

Coaxial


Precision Fixed Attenuator

50Ω 0.5W 20dB DC to 2000 MHz

Maximum Ratings

Operating Temperature	-45°C to 100°C
Storage Temperature	-55°C to 100°C

Outline Drawing



Outline Dimensions (inch/mm)

B	D	wt
.62	1.94	grams
15.75	49.28	30.0

Features

- excellent VSWR, 1.05:1 typ.
- excellent flatness, 0.25 dB typ. to 2000 MHz
- usable to 4000 MHz

Applications

- PCS
- instrumentation
- cellular



CASE STYLE: FF747

Connectors	Model	Price	Qty.
BNC Male-BNC Female	HAT-20(+)	9.95 ea.	(1-9)

+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.



Electrical Specifications

FREQ. RANGE (MHz)	ATTENUATION (dB)					VSWR (:1)			MAX. INPUT POWER (W)
	Flatness*					DC-0.5 GHz	DC-1 GHz	DC-2 GHz	
$f_L - f_U$	Nom.	Typ.	Typ.	Typ.	Total Band Max.	Typ.	Typ.	Typ.	
DC-2000	20±0.2	0.05	0.15	0.25	0.40	1.05	1.10	1.15	0.5

* Flatness = variation over band divided by 2.

Typical Performance Data

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
10.00	20.02	1.00
50.00	20.03	1.00
100.00	20.04	1.00
250.00	20.06	1.00
500.00	20.09	1.01
750.00	20.14	1.01
1000.00	20.21	1.03
1500.00	20.30	1.06
1750.00	20.34	1.09
2000.00	20.35	1.13



designers kit available

Kit No.	No. of Units in Kit	Description	Price \$ per Kit
K1-HAT	5	1 of ea. HAT-3(+), 6(+), 10(+), 20(+), 30(+)	48.95
K2-HAT	10	1 of ea. HAT-1(+), 2(+), 3(+), 4(+), 5(+), 6(+), 7(+), 8(+), 9(+), 10(+)	98.95

Mini-Circuits®

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

REV. E
M98898
EDR-5087/1-15
HAT-20
RVN/LC/CP/AM
060817
Page 1 of 1