





PRODUCT NUMBER  
SEE TABLE



## NOTES:

1. MADE IN ACCORDANCE WITH PRODUCT SPECIFICATION BUS-12-001 AND PURCHASE SPECIFICATION BUS-10-001.
2. COLOR: GRAY WITH CONTRASTING COLOR TRACER ON EDGE OF FIRST POSITION.
3. UL-LISTED STYLE 2651, CSA CERTIFIED.
4. ADD SUFFIX LF TO END OF PART NUMBER FOR LEAD FREE OPTION.
5. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
6. THIS PRODUCT IS NOT INTENDED FOR USE IN BOARD SOLDERING APPLICATION.

mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family IDC			
—													
ltr	ec'n no	dr	date	tolerances unless otherwise specified						title			
F	V05-0016	DAI	1/17/05	angles			XX ±.01		INCH/MM		1MM #28 AWG		
G	V05-0888	DAI	9/16/05				XXX ±.005				STRANDED DOUBLE SCALLOPED		
H	V06-0704	JRV	2006-07-20	0° ±2°			XXX ±.0020		scale 1:1		PVC ROUND CONDUCTOR CABLE		
				dr	J.MUSTARD		10/23/91			dwg no		sheet 1 of 2	size
				engr	M.SMYK		10/23/91			91820		A4	
				chr	M.SMYK		10/23/91						
				appd	M.SMYK		10/23/91			type		CUSTOMER Drawing	
sheet index		revision sheet		H	H								
				1	2								

PRODUCT NUMBER

91820-XXX

XXXXX-YXX LF

BASE NUMBER

LEAD FREE OPTION

SPECIFIES NUMBER OF POSITIONS

DASH #	NUMBER OF POS.	DIM A	DIM B
-Y06	6	.236/6.00	.197/5.00
-Y08	8	.315/8.00	.276/7.00
-Y10	10	.394/10.00	.354/9.00
-Y12	12	.472/12.00	.433/11.00
-Y14	14	.551/14.00	.512/13.00
-Y16	16	.630/16.00	.591/15.00
-Y18	18	.709/18.00	.669/17.00
-Y20	20	.787/20.00	.748/19.00
-Y24	24	.945/24.00	.906/23.00
-Y26	26	1.024/26.00	.984/25.00
-Y30	30	1.181/30.00	1.142/29.00
-Y34	34	1.339/34.00	1.299/33.00
-Y36	36	1.417/36.00	1.378/35.00
-Y40	40	1.575/40.00	1.535/39.00
-Y44	44	1.732/44.00	1.693/43.00
-Y48	48	1.890/48.00	1.850/47.00
-Y50	50	1.969/50.00	1.929/49.00
-Y60	60	2.362/60.00	2.323/59.00
-Y64	64	2.520/64.00	2.480/63.00
-Y68	68	2.677/68.00	2.638/67.00

OBSOLETE

OBSOLETE


Y	MIN LENGTH FT/M	TRACER COLOR NOTE 2
0	100/30.48	BLACK
1	100/30.48	BLACK
5	100/30.48	YELLOW
6	100/30.48	YELLOW

CUSTOMER SPECIAL

CUSTOMER SPECIAL

## TOLERANCE FOR DIMS

NO OF CONDUCTORS	DIM A±	DIM B±
6 THRU 18	.010/.25	.007/.18
20 THRU 36	.015/.38	.009/.23
38 THRU 68	.015/.38	.011/.28

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection 	product family IDC
litr	ecr no	dr	date	tolerances unless otherwise specified			title 1MM #28 AWG STRANDED DOUBLE SCALLOPED PVC ROUND CONDUCTOR CABLE
H				angles	XX ±.01	INCH/MM	
				0° ±2°	XXX ±.005	scale 1:1	
					XXX ±.0020		
				dr	J.MUSTARD	10/23/91	dwg no
				engr	M.SMYK	10/23/91	sheet 2 of 2
				chr	M.SMYK	10/23/91	size
				appd	M.SMYK	10/23/91	A4
sheet index	revision sheet						type CUSTOMER Drawing

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

91820-030