




10 9 8 7 6 5 4 3 2 1

2 AND 3 CIRCUIT PARTS HAVE
ONE LATCH DETAIL
POSITIONED ON THIS END.




NO. OF CIRC.	STD. MAT. NUMBER	OPTIONAL 10A IMPRINT	"A" IN/MM	"B" IN/MM	"C" IN/MM	"D" IN/MM
02	394220002	394222002	1.73/44.0	.472/12.00	.98/25.0	1.313/33.35
03	394220003	394222003	2.20/56.0	.945/24.00	1.46/37.0	1.785/45.35
04	394220004	394222004	2.68/68.0	1.417/36.00	1.93/49.0	2.258/57.35
05	394220005	394222005	3.15/80.0	1.890/48.00	2.40/61.0	2.730/69.35
06	394220006	394222006	3.62/92.0	2.362/60.00	2.87/73.0	3.203/81.35
07	394220007	394222007	4.09/104.0	2.835/72.00	3.35/85.0	3.675/93.35
08	394220008	394222008	4.57/116.0	3.307/84.00	3.82/97.0	4.148/105.35

Ⓚ




NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. PRODUCT SPECIFICATION: SEE PPS.42.002
4. IMPRINTING CHARACTER HEIGHT IS .170" Ⓚ
5. ROHS COMPLIANT BY EXEMPTION *



SECTION Z-Z



7	2	SCREW, MTG. END, M4, PHIL-SLOT	PHOS. BRONZE	TIN PLATE	ADD 10A OPTION EC NO: WNA2009-0615 DRWN: JENCINAS 2009/04/09 CHKD: CYORK 2009/04/09 APPR: JMAGNELL 2009/04/13	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± .005</td></tr><tr><td>2 PLACES</td><td>± 0.13</td><td>± .01</td></tr><tr><td>1 PLACE</td><td>± 0.3</td><td>± ---</td></tr><tr><td colspan="3">ANGULAR ±1/2°</td></tr></table>		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± .005	2 PLACES	± 0.13	± .01	1 PLACE	± 0.3	± ---	ANGULAR ±1/2°			DIMENSION STYLE IN/MM <table><tr><td>DRAWN BY</td><td>DATE</td></tr><tr><td>RKEMP</td><td>04/10/13</td></tr><tr><td>CHECKED BY</td><td>DATE</td></tr><tr><td>RSTONE</td><td>04/12/07</td></tr><tr><td>APPROVED BY</td><td>DATE</td></tr><tr><td>G. ROBERTSON</td><td>04/12/10</td></tr><tr><td>MATERIAL NO.</td><td></td></tr></table>	DRAWN BY	DATE	RKEMP	04/10/13	CHECKED BY	DATE	RSTONE	04/12/07	APPROVED BY	DATE	G. ROBERTSON	04/12/10	MATERIAL NO.		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
	mm	INCH																																									
4 PLACES	± ---	± ---																																									
3 PLACES	± ---	± .005																																									
2 PLACES	± 0.13	± .01																																									
1 PLACE	± 0.3	± ---																																									
ANGULAR ±1/2°																																											
DRAWN BY	DATE																																										
RKEMP	04/10/13																																										
CHECKED BY	DATE																																										
RSTONE	04/12/07																																										
APPROVED BY	DATE																																										
G. ROBERTSON	04/12/10																																										
MATERIAL NO.																																											
6	XX	BACK PLATE	PHOS. BRONZE	TIN PLATE	TITLE PLUG, MTG, ENDS 12MM, 85A, 600V #10-#3 AWG																																						
5	XX	PRESSURE CLAMP *	BRASS	NICKEL PLATE																																							
4	XX	TERMINAL	COPPER ALLOY	TIN PLATE																																							
3	XX	SCREW, M5 PAN HEAD, POZI-SLOT	STAINLESS STEEL	TIN PLATE																																							
2	1	MOLDING COVER	POLYESTER (PBT)	BLACK	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE B	SEE CHART	DOCUMENT NO. SD-39422-001	SHEET NO. 1 OF 1	MOLEX MOLEX INCORPORATED THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																	
1	1	MOLDING, BODY, WITH MTG ENDS	POLYESTER (PBT)	BLACK																																							
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH	REV																																						