

|                                                                                   |                             |                                                                  |
|-----------------------------------------------------------------------------------|-----------------------------|------------------------------------------------------------------|
|  | <b>Final Datasheet V1.0</b> | <b>TS</b> 1378<br><b>Rev.</b> 2<br><b>Page</b> 1<br><b>of</b> 13 |
|                                                                                   | <b>TPM Sensor SP30T</b>     |                                                                  |



# **Final Datasheet V1.0** **Tire Pressure Monitoring Sensor SP30T**

Revisions dates:

|    |            |
|----|------------|
| 00 | 2007-06-11 |
| 1  | 2007-12-20 |
| 2  | 2008-05-29 |

Document history: See end of document

|          | Date   | Sign | Rev | Reference     | Date   | Dok | Stamp |
|----------|--------|------|-----|---------------|--------|-----|-------|
| Prepared | 070611 | ML   | 0   | Archive 11843 | 070813 | HKW |       |
| Checked  | 070613 | NPH  | 1   | EM 11866      | 080616 | HKW |       |
| Approved | 070716 | RH   | 2   | EM 12044      | 080616 |     |       |

|                                                                                   |                             |                                                                  |
|-----------------------------------------------------------------------------------|-----------------------------|------------------------------------------------------------------|
|  | <b>Final Datasheet V1.0</b> | <b>TS</b> 1378<br><b>Rev.</b> 2<br><b>Page</b> 2<br><b>of</b> 13 |
|                                                                                   | <b>TPM Sensor SP30T</b>     |                                                                  |

## Table of Contents

|          |                                       |           |
|----------|---------------------------------------|-----------|
| <b>1</b> | <b>PRODUCT DESCRIPTION.....</b>       | <b>4</b>  |
| 1.1      | Overview.....                         | 4         |
| 1.2      | Features .....                        | 4         |
| 1.3      | Ordering Information .....            | 4         |
| <b>2</b> | <b>PRODUCT CHARACTERISTICS .....</b>  | <b>5</b>  |
| 2.1      | Measurement Performance.....          | 5         |
| 2.1.1    | Pressure Measurement.....             | 5         |
| 2.1.2    | Acceleration Measurement .....        | 6         |
| 2.1.3    | Temperature Measurement .....         | 6         |
| 2.1.4    | Supply Voltage Measurement.....       | 6         |
| 2.2      | Current Consumption .....             | 7         |
| 2.3      | Tmax.....                             | 7         |
| 2.4      | Vmin .....                            | 7         |
| 2.5      | Clock Sources .....                   | 8         |
| 2.5.1    | System Clock (MCLK).....              | 8         |
| 2.5.2    | Low Power (LP) Oscillator .....       | 8         |
| 2.5.3    | External Clock .....                  | 8         |
| 2.6      | LF Input .....                        | 8         |
| 2.7      | Power-on Reset.....                   | 9         |
| 2.8      | Digital I/O.....                      | 9         |
| <b>3</b> | <b>OPERATING RANGE.....</b>           | <b>9</b>  |
| <b>4</b> | <b>ABSOLUTE MAXIMUM RATINGS .....</b> | <b>10</b> |
| <b>5</b> | <b>PHYSICAL DIMENSIONS .....</b>      | <b>11</b> |
| <b>6</b> | <b>PIN CONFIGURATION.....</b>         | <b>12</b> |
| <b>7</b> | <b>DOCUMENT HISTORY .....</b>         | <b>13</b> |

|                                                                                   |                             |                                                                  |
|-----------------------------------------------------------------------------------|-----------------------------|------------------------------------------------------------------|
|  | <b>Final Datasheet V1.0</b> | <b>TS</b> 1378<br><b>Rev.</b> 2<br><b>Page</b> 3<br><b>of</b> 13 |
|                                                                                   | <b>TPM Sensor SP30T</b>     |                                                                  |

**Edition 2008-05-29**  
**Published by Infineon Technologies AG,**  
**Am Campeon 1-12**  
**85579 Neubiberg, Germany**  
**© Infineon Technologies AG 2006-03-20.**  
**All Rights Reserved.**  
**Attention please!**

The information herein is given to describe certain components and shall not be considered as a guarantee of characteristics.

Terms of delivery and rights to technical change reserved.

We hereby disclaim any and all warranties, including but not limited to warranties of non-infringement, regarding circuits, descriptions and charts stated herein.

#### **Information**

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office in Germany or the Infineon Technologies Companies and our Infineon Technologies Representatives worldwide ([www.infineon.com](http://www.infineon.com)).

#### **Warnings**

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies Office.

Infineon Technologies Components may only be used in life-support devices or systems with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

|                                                                                   |                             |                                                                  |
|-----------------------------------------------------------------------------------|-----------------------------|------------------------------------------------------------------|
|  | <b>Final Datasheet V1.0</b> | <b>TS</b> 1378<br><b>Rev.</b> 2<br><b>Page</b> 4<br><b>of</b> 13 |
|                                                                                   | <b>TPM Sensor SP30T</b>     |                                                                  |

# 1 Product Description

## 1.1 Overview

The SP30T Tire Pressure Monitoring (TPM) Sensor represents Infineon's high pressure range TPM sensor for SUV and Truck application. The SP30T combines a high pressure range with a high level of integration by including a microcontroller and LF-input stage to meet market demands for flexible, customer specific solutions and overall system cost reduction.

The sensor design is based upon Infineon's proprietary and patented solutions for high reliability measurements in harsh automotive environments, with a predictable and stable quality in high volume applications.

The SP30T measures pressures up to 1600kPa, temperature, supply voltage and acceleration (optional), and by integrating these functions with an ASIC in one package, Infineon has developed the ideal product for high pressure TPM applications.

## 1.2 Features

- Integrated Sensors
  - High pressure range
  - Acceleration
  - Temperature
  - Voltage
- Integrated Peripherals
  - Microcontroller
  - On board EEPROM
  - GPIOs
  - ADC for signal conditioning
  - 2x LF Receiver for triggering
- Measurement Ranges
  - Pressure Sensor 100 to 1600 kPa
  - Temperature Sensor -40 to +125°C
  - Supply Voltage Sensor 2.1 to 3.6 V
  - Acceleration Sensor -12 to 115 g

## 1.3 Ordering Information

| Product Name    | Product Type                    | Ordering Code | Package      |
|-----------------|---------------------------------|---------------|--------------|
| SP30T-00E00-06B | Tire Pressure Monitoring Sensor | SP000411794   | P-DSOSP-14-6 |

## 2 Product Characteristics

The max and min numbers are to be understood as + and – 5 $\sigma$  values (Cpk = 1.67) unless otherwise specified.

### 2.1 Measurement Performance

#### 2.1.1 Pressure Measurement

The presented performance reflects the use of 11-bit measurement of pressure signal and 10-bit measurement of temperature.

Table 1 Pressure measurement specifications

| PARAMETER             | SPECIFICATION |     |      |      | AMBIENT CONDITIONS |            |                | COMMENTS                                                            |
|-----------------------|---------------|-----|------|------|--------------------|------------|----------------|---------------------------------------------------------------------|
|                       | Min           | Typ | Max  | Unit | Temp [°C]          | VDD [V]    | Pressure [kPa] |                                                                     |
| Input pressure range* | 100           |     | 1600 | kPa  | -40 to 125         | 2.1 to 3.6 |                |                                                                     |
| Measurement error     | -25           |     | 25   | kPa  | 0 to 50            | 2.1 to 3.6 | 100 to 1000    | Linear behavior between 1000 kPa and 1600 kPa according to Figure 1 |
|                       | -30           |     | 30   | kPa  | -40 to 125         | 2.1 to 3.6 |                |                                                                     |
|                       | -45           |     | 45   | kPa  | 0 to 50            | 2.1 to 3.6 | 1000 to 1600   |                                                                     |
|                       | -50           |     | 50   | kPa  | -40 to 125         | 2.1 to 3.6 |                |                                                                     |

Table 2 Pressures 100, 375, 657, 1000, 1300, 1600 kPa verified in qualification




Figure 1: Pressure measurement error

|                                                                                   |                             |  |      |      |
|-----------------------------------------------------------------------------------|-----------------------------|--|------|------|
|  | <b>Final Datasheet V1.0</b> |  | TS   | 1378 |
|                                                                                   | <b>TPM Sensor SP30T</b>     |  | Rev. | 2    |
| Page                                                                              |                             |  | 6    |      |
|                                                                                   |                             |  | of   | 13   |
|                                                                                   |                             |  |      |      |

### 2.1.2 Acceleration Measurement

The presented performance reflects the use of 12-bit measurement of acceleration signal and 10-bit measurement for temperature.

Table 2 Acceleration measurement specifications

| PARAMETER                | SPECIFICATION |     |       |      | AMBIENT CONDITIONS |            | COMMENTS |
|--------------------------|---------------|-----|-------|------|--------------------|------------|----------|
|                          | Min           | Typ | Max   | Unit | Temp [°C]          | VDD [V]    |          |
| Input acceleration range | -12           |     | 115   | g    | -40 to 125         | 2.1 to 3.6 |          |
| Sensitivity error        | -18.75        |     | 18.75 | %    | -40 to 90          | 2.1 to 3.6 |          |
|                          | -24           |     | 24    |      | 90 to 125          |            |          |
| Offset error@9g          | -6            |     | 6     | g    | -20 to 70          | 2.1 to 3.6 |          |
|                          | -8.5          |     | 8.5   |      | -40 to 90          |            |          |
|                          | -12           |     | 12    |      | 90 to 125          |            |          |

### 2.1.3 Temperature Measurement

The presented performance reflects the use of 10-bit measurement of temperature.

Table 3 Temperature measurement specifications

| PARAMETER         | SPECIFICATION |     |     |      | AMBIENT CONDITIONS |            | COMMENTS |
|-------------------|---------------|-----|-----|------|--------------------|------------|----------|
|                   | Min           | Typ | Max | Unit | Temp [°C]          | VDD [V]    |          |
| Measurement error | -3            |     | 3   | °C   | -20 to 70          | 2.1 to 3.6 |          |
|                   | -5            |     | 5   | °C   | -40 to 90          | 2.1 to 3.6 |          |
|                   | -3            |     | 7   | °C   | 90 to 125          | 2.1 to 3.6 |          |

### 2.1.4 Supply Voltage Measurement

The presented performance reflects the use of 9-bit measurement of supply voltage.

Table 4 Supply voltage measurement specifications

| PARAMETER         | SPECIFICATION |     |      |      | AMBIENT CONDITIONS |                         | COMMENTS |
|-------------------|---------------|-----|------|------|--------------------|-------------------------|----------|
|                   | Min           | Typ | Max  | Unit | TEMP [°C]          | VDD [V]                 |          |
| Measurement error | -100          |     | +100 | mV   | -40 to 125         | V <sub>THR</sub> to 3.6 |          |

|                                                                                   |                             |                |
|-----------------------------------------------------------------------------------|-----------------------------|----------------|
|  | <b>Final Datasheet V1.0</b> | <b>TS</b> 1378 |
|                                                                                   | <b>TPM Sensor SP30T</b>     | <b>Rev.</b> 2  |
|                                                                                   |                             | <b>Page</b> 7  |
|                                                                                   |                             | <b>of</b> 13   |

## 2.2 Current Consumption

Table 5 Current consumption

| PARAMETER                  | SPECIFICATION |      |     |      | AMBIENT CONDITIONS |            | COMMENTS                                                                                                       |
|----------------------------|---------------|------|-----|------|--------------------|------------|----------------------------------------------------------------------------------------------------------------|
|                            | Min           | Typ  | Max | Unit | Temp [°C]          | VDD [V]    |                                                                                                                |
| Power down current         |               | 0.4  | 0.6 | μA   | 25                 | 3.0        |                                                                                                                |
| Power down current         |               | 13   | 20  | μA   | 125                | 3.0        |                                                                                                                |
| IDLE current               |               | 30   | 50  | μA   | 25                 | 3.0        |                                                                                                                |
| IDLE current               |               | 50   | 75  | μA   | 125                | 3.0        |                                                                                                                |
| RUN current                |               | 0.53 | 0.8 | mA   | 25                 | 3.0        |                                                                                                                |
| RUN current                |               | 0.65 | 1.0 | mA   | 125                | 3.0        |                                                                                                                |
| Pressure measurement       |               | 4    | 12  | μAs  | -40 to 125         | 2.1 to 3.6 | 11 bit A/D conversion, excl. temperature meas                                                                  |
| Acceleration measurement   |               | 6    | 16  | μAs  | -40 to 125         | 2.1 to 3.6 | 12 bit A/D conversion, excl. temperature meas                                                                  |
| Temperature measurement    |               | 0.9  | 2.5 | μAs  | -40 to 125         | 2.1 to 3.6 | 10 bit A/D conversion                                                                                          |
| Supply voltage measurement |               | 0.3  | 2.5 | μAs  | -40 to 125         | 2.1 to 3.6 | 9 bit A/D conversion                                                                                           |
| Peak current               |               | 1.6  | 2.5 | mA   | 25                 | 3.0        | Pressure measurement and 1 LF channel on, duration is 1280μs for 11 bit measurement for the peak current only. |
| 1 channel LF current       |               | 2.6  | 4.6 | μA   | 25                 | 3.0        |                                                                                                                |
| 1 channel LF current       |               | 3.0  | 6.7 | μA   | 125                | 3.0        |                                                                                                                |
| 2 channel LF current       |               | 4.5  | 5.5 | μA   | 25                 | 3.0        | 2 <sup>nd</sup> LF channel is optional                                                                         |
| 2 channel LF current       |               | 6.5  | 11  | μA   | 125                | 3.0        | 2 <sup>nd</sup> LF channel is optional                                                                         |
| Thermal shutdown current   |               | 18   | 25  | μA   | 125                | 3.0        |                                                                                                                |
| Thermal shutdown current   |               | 30   | 50  | μA   | 150                | 3.0        |                                                                                                                |

## 2.3 Tmax

$\vartheta_{\text{SHTD}}$  represents the temperature at which the Thermal Shut-down function can be enabled and  $\vartheta_{\text{REL}}$  represents the temperature at which the Master Reset state is released. The  $\vartheta_{\text{SHTD}}$  is always higher than  $\vartheta_{\text{REL}}$ .

Table 6 Trigger temperatures for thermal shutdown

| PARAMETER                 | SPECIFICATION |     |     |      | AMBIENT CONDITIONS |            | COMMENTS                |
|---------------------------|---------------|-----|-----|------|--------------------|------------|-------------------------|
|                           | Min           | Typ | Max | Unit | TEMP [°C]          | VDD [V]    |                         |
| $\vartheta_{\text{SHTD}}$ | 102           |     | 123 | °C   | -40 to 175         | 2.1 to 3.6 | Thermal shutdown enable |
| $\vartheta_{\text{REL}}$  | 100           |     | 121 | °C   | -40 to 175         | 2.1 to 3.6 | Master Reset release    |

## 2.4 Vmin

The voltage at which the Vmin-circuit will return a low battery voltage status is specified in Table :

Table 7 Vmin specifications

| PARAMETER | SPECIFICATION |     |     |      | AMBIENT CONDITIONS |                         | COMMENTS |
|-----------|---------------|-----|-----|------|--------------------|-------------------------|----------|
|           | Min           | Typ | Max | Unit | TEMP [°C]          | VDD [V]                 |          |
| Vmin      | 2.0           | 2.1 | 2.2 | V    | -40 to 125         | V <sub>THR</sub> to 3.6 |          |



|                                                                                   |                             |  |             |      |
|-----------------------------------------------------------------------------------|-----------------------------|--|-------------|------|
|  | <b>Final Datasheet V1.0</b> |  | <b>TS</b>   | 1378 |
|                                                                                   | <b>TPM Sensor SP30T</b>     |  | <b>Rev.</b> | 2    |
| <b>Page</b>                                                                       |                             |  | 9           |      |
|                                                                                   |                             |  | <b>of</b>   | 13   |
|                                                                                   |                             |  |             |      |

Table 12 LF Carrier Detection

| PARAMETER                                               | SPECIFICATION |     |        |       | AMBIENT CONDITIONS |            | COMMENTS |
|---------------------------------------------------------|---------------|-----|--------|-------|--------------------|------------|----------|
|                                                         | Min           | Typ | Max    | Unit  | TEMP [°C]          | VDD [V]    |          |
| Carrier frequency                                       | 121.25        | 125 | 128.75 | kHz   | -40 to 125         | 2.1 to 3.6 |          |
| Maximum sensitivity not to detect, 2 amplifiers enabled | 4             |     |        | mVp-p | 0 to 90            | 2.1 to 3.6 |          |
|                                                         | 3.5           |     |        | mVp-p | 90 to 125          | 2.1 to 3.6 |          |
|                                                         | 3.5           |     |        | mVp-p | -40 to 0           | 2.1 to 3.0 |          |
|                                                         | 2.9           |     |        | mVp-p | -40 to 0           | 3.0 to 3.6 |          |
| Minimum sensitivity to detect, 2 amplifiers enabled     | 10            |     |        | mVp-p | 0 to 90            | 2.1 to 3.6 |          |
|                                                         | 12.2          |     |        | mVp-p | 90 to 125          | 2.1 to 3.6 |          |
|                                                         | 12.2          |     |        | mVp-p | -40 to 0           | 2.1 to 3.6 |          |
| Maximum sensitivity not to detect, 3 amplifiers enabled |               | 0.8 |        | mVp-p | -40                | 3.6        |          |
|                                                         | 0.25          |     |        | mVp-p | -40                | 2.1 to 3.0 |          |
|                                                         | 0.25          |     |        | mVp-p | 0 to 125           | 2.1 to 3.6 |          |
| Minimum sensitivity to detect, 3 amplifiers enabled     |               |     | 2.5    | mVp-p | -40 to 125         | 2.1 to 3.6 |          |

## 2.7 Power-on Reset

Table 13 Power-on reset level

| PARAMETER                       | SPECIFICATION |      |     |      | COMMENTS |
|---------------------------------|---------------|------|-----|------|----------|
|                                 | Min           | Typ  | Max | Unit |          |
| Power-on reset level, $V_{THR}$ | 1.8           | 1.85 | 1.9 | V    |          |

## 2.8 Digital I/O

Table 14 Digital I/O specifications

| PARAMETER           | SPECIFICATION      |     |                    |         | COMMENTS             |
|---------------------|--------------------|-----|--------------------|---------|----------------------|
|                     | Min                | Typ | Max                | Unit    |                      |
| Digital output high | $V_{DD}-0.3$       |     |                    | V       | At 1 mA load current |
| Digital output low  |                    |     | 0.3                | V       | At 1 mA load current |
| Digital input high  | $0.8 \cdot V_{DD}$ |     |                    | V       |                      |
| Digital input low   |                    |     | $0.2 \cdot V_{DD}$ | V       |                      |
| Input current       |                    |     | $\pm 1$            | $\mu A$ |                      |

# 3 Operating Range

Table 15 Operating range

| PARAMETER           | SPECIFICATION |     |     |      | COMMENTS                   |
|---------------------|---------------|-----|-----|------|----------------------------|
|                     | Min           | Typ | Max | Unit |                            |
| Supply voltage      | $V_{THR}$     |     | 3.6 | V    | Unless otherwise specified |
| Ambient temperature | -40           |     | 125 | °C   |                            |

|                                                                                   |                             |                                                                   |
|-----------------------------------------------------------------------------------|-----------------------------|-------------------------------------------------------------------|
|  | <b>Final Datasheet V1.0</b> | <b>TS</b> 1378<br><b>Rev.</b> 2<br><b>Page</b> 10<br><b>of</b> 13 |
|                                                                                   | <b>TPM Sensor SP30T</b>     |                                                                   |

## 4 Absolute Maximum Ratings

Table 16 Absolute maximum ratings


| PARAMETER                          | SPECIFICATION |     |         |      | COMMENTS                                         |
|------------------------------------|---------------|-----|---------|------|--------------------------------------------------|
|                                    | Min           | Typ | Max     | Unit |                                                  |
| Ambient temperature, operating     | -40           |     | 150     | °C   | Max 24 h accumulated over life time              |
| Ambient temperature, storage       | -40           |     | 150     | °C   | Max 1000 h                                       |
| Transient temperature <sup>1</sup> |               |     | 175     | °C   | Max 3 min                                        |
| Supply Voltage                     | -0.3          |     | 4.0     | V    |                                                  |
| Input voltage                      | -0.3          |     | Vdd+0.3 | V    |                                                  |
| Input current, any pin (DC)        | -10           |     | 10      | mA   |                                                  |
| Input current, any pin (transient) | -100          |     | 100     | mA   |                                                  |
| Input current, LF pins             | -1            |     | 1       | mA   |                                                  |
| Maximum input pressure             | 50            |     | 2000    | kPa  |                                                  |
|                                    |               |     | 2500    | kPa  | Max 2 s, 5 times over lifetime                   |
| Static acceleration                |               |     | 3000    | g    |                                                  |
| Mechanical shock                   |               |     | 4000    | g    | Half sine, 0.3ms                                 |
| ESD HBM                            | 2             |     |         | kV   | Human body model JESD22-A114                     |
| ESD CDM                            | 750           |     |         | V    | Charge Device Model ESD-STM5.3.1, Corner pins    |
|                                    | 500           |     |         |      | Charge Device Model ESD-STM5.3.1, All other pins |
| Latch Up                           | 100           |     |         | mA   | AEC-Q100                                         |

<sup>1</sup> Will withstand standard SnPb Eutectic reflow soldering process (JEDEC J-STD-020, J-STD-A113)

**Attention:** *Stresses above the max. values listed here may cause permanent damage to the device. Exposure to absolute maximum rating conditions for extended periods may affect device reliability. Maximum ratings are absolute ratings; exceeding only one of these values may cause irreversible damage to the device.*


|                                                                                   |                             |                                                                   |
|-----------------------------------------------------------------------------------|-----------------------------|-------------------------------------------------------------------|
|  | <b>Final Datasheet V1.0</b> | <b>TS</b> 1378<br><b>Rev.</b> 2<br><b>Page</b> 11<br><b>of</b> 13 |
|                                                                                   | <b>TPM Sensor SP30T</b>     |                                                                   |

## 5 Physical dimensions



|                                                                                   |                             |                                                                   |
|-----------------------------------------------------------------------------------|-----------------------------|-------------------------------------------------------------------|
|  | <b>Final Datasheet V1.0</b> | <b>TS</b> 1378<br><b>Rev.</b> 2<br><b>Page</b> 12<br><b>of</b> 13 |
|                                                                                   | <b>TPM Sensor SP30T</b>     |                                                                   |

## 6 Pin Configuration



**Figure 3: Pin Configuration. Top view, not to scale**

**Table 17 Pin Description**

| PIN | NAME | FUNCTION                                                             |
|-----|------|----------------------------------------------------------------------|
| 1   | IN4  | LF receiver channel 2, negative input                                |
| 2   | P10  | General purpose I/O with external wakeup, internal pull-up/pull-down |
| 3   | P11  | General purpose I/O with external wakeup, internal pull-up/pull-down |
| 4   | MSDA | Monitor Serial Data I/O, internal pull-up                            |
| 5   | MSCL | Monitor Serial Clock input                                           |
| 6   | VDD  | Supply pad VDD (battery, positive terminal)                          |
| 7   | VSS  | Common ground (battery, negative terminal)                           |
| 8   | VSS  | Common ground (battery, negative terminal)                           |
| 9   | P17  | General purpose I/O (or digital modulator output)                    |
| 10  | P15  | General purpose I/O or external clock                                |
| 11  | P14  | General purpose I/O (or digital modulator output)                    |
| 12  | IN1  | LF receiver channel 1, positive input                                |
| 13  | IN2  | LF receiver channel 1, negative input                                |
| 14  | IN3  | LF receiver channel 2, positive input                                |

|                                                                                   |                             |                                                                   |
|-----------------------------------------------------------------------------------|-----------------------------|-------------------------------------------------------------------|
|  | <b>Final Datasheet V1.0</b> | <b>TS</b> 1378<br><b>Rev.</b> 2<br><b>Page</b> 13<br><b>of</b> 13 |
|                                                                                   | <b>TPM Sensor SP30T</b>     |                                                                   |

## 7 Document history

| Rev | Paragraphs | Description                                                                                      |
|-----|------------|--------------------------------------------------------------------------------------------------|
| 00  |            | First issue of TS1378                                                                            |
| 1   | 1          | Disclaimer included                                                                              |
| 1   | 2.1.1      | Pressure range extended from max 1500kPa to max 1600kPa. Measurement error adjusted accordingly. |
| 1   | 2.1.1      | Footnote included displaying the Pressure values verified in qualification                       |
| 1   | 5          | Physical Drawing updated                                                                         |
| 2   | 1          | Added section "Product Description "                                                             |
| 2   | 5          | Physical Drawing updated                                                                         |
| 2   | 5          | Added wording to Figure title of figure 2                                                        |
| 2   | 6          | Added section "Pin Configuration"                                                                |
| 2   |            | Removed "Confidential" marking                                                                   |
| 2   | 2          | Updated fig. 1                                                                                   |