



+ RELAYS, CONTACTORS & SWITCHES

TIME DELAY RELAYS



✓ Active

TE CONNECTIVITY (TE)

E7024PF004=RLY,NUC,OFF,4P,125

Agastat | 7000 Electropneumatic Timing - Nuclear Qualified

E7024PF004

TE Internal Number: 1423175-5

Not EU RoHS Compliant

Not EU ELV Compliant

Type of Control Knob

Input Voltage (VDC) 125

Timing Range (Off-Time) (seconds) 60 – 600

Mode of Operation Off-Delay

Delay Time 1 – 10 minutes

DOCUMENTATION

Catalog Pages/Data Sheets

[5-1773450-5_sec12_E7000](#)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Product Category Electromechanical Relays

Relay Type Time Delay

Product Type Relay

Configuration Features

Multiple Timing Ranges Without

Electrical Characteristics

Input Voltage (VDC) 125

Timing Range (Off-Time) (seconds) 60 – 600

Actuating System DC

Contact Features

Type of Control Knob

Delay Time 1 – 10 minutes

Contact Arrangement 4 Form C, 4PDT, 4 C/O

Termination Features

Termination Type Screw Terminals

Mechanical Attachment

Mounting Type Mounting Holes, Panel Mount

Dimensions

Dimensions (L x W x H) (Approximate) 147.83 x 65.3 x 84.3 mm [5.82 x 2.57 x 3.32 in]

Usage Conditions

Operating Temperature Range (°C) 21 – 40

Operation/Application

Mode of Operation Off-Delay

Other

Repeatability (Max) ±10%

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
