





PC card drilling dimensions(after plating) _____
(thickness 1.60±0.20mm)



TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A.PX00
15	39.14	33.32	25.18	25.12	19.18	D15P24A.PX00
25	53.03	47.04	39.12	38.84	33.12	D25P24A.PX00
37	69.32	63.50	55.68	55.30	49.68	D37P24A.PX00

Plating: 4 ---> flash AU
Plating: 6 ---> 0.76 » AU

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A.PX00LF
15	39.14	33.32	25.18	25.12	19.18	D15P24A.PX00LF
25	53.03	47.04	39.12	38.84	33.12	D25P24A.PX00LF
37	69.32	63.50	55.68	55.30	49.68	D37P24A.PX00LF

Plating: 4 ---> flash AU
Plating: 6 ---> 0.76 » AU

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000

European Views

www.fciconnect.com			surface	ISO 1302	tolerance std	ISO 406	ISO 1101	projection	mm	Scale
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	LELEON	1992-09-10	ANGULAR		0.X		±0.1	size		
Eng	PESSON	1992-09-10	LINEAR		0.XX		±0.1	A3		2
Chr	NIRMAL GEORGE	2009-11-24	0.XX' ±2°		0.XXX		±0.1	ECN		I09-0268
Appr	SUDHIR VARMA	2009-11-24	Product family			D-SUB			Spec ref -	
FCI			MALE CONNECTOR DELTA D ST			straight,solder type for			C01-8646-0097	
catalog no						CUSTOMER			sheet 1 of 1	

