

C106 Series

Preferred Devices

Sensitive Gate Silicon Controlled Rectifiers

Reverse Blocking Thyristors

Glassivated PNP devices designed for high volume consumer applications such as temperature, light, and speed control; process and remote control, and warning systems where reliability of operation is important.

Features

- Glassivated Surface for Reliability and Uniformity
- Power Rated at Economical Prices
- Practical Level Triggering and Holding Characteristics
- Flat, Rugged, Thermopad Construction for Low Thermal Resistance, High Heat Dissipation and Durability
- Sensitive Gate Triggering
- Pb-Free Packages are Available*




ON Semiconductor®

<http://onsemi.com>

SCRs

4 A RMS, 200 – 600 Volts



**TO-225AA
CASE 077
STYLE 2**

MARKING DIAGRAM & PIN ASSIGNMENT



Y	= Year
WW	= Work Week
C106xx	= Device Code
xx	= B, D, D1, M, M1
G	= Pb-Free Package

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

C106 Series

MAXIMUM RATINGS ($T_J = 25^\circ\text{C}$ unless otherwise noted)

Characteristic	Symbol	Max	Unit
Peak Repetitive Off-State Voltage (Note 1) (Sine Wave, 50–60 Hz, $R_{GK} = 1\text{ k}\Omega$, $T_C = -40^\circ$ to 110°C)	V_{DRM} , V_{RRM}	200 400 600	V
On-State RMS Current (180° Conduction Angles, $T_C = 80^\circ\text{C}$)	$I_{T(RMS)}$	4.0	A
Average On-State Current (180° Conduction Angles, $T_C = 80^\circ\text{C}$)	$I_{T(AV)}$	2.55	A
Peak Non-Repetitive Surge Current (1/2 Cycle, Sine Wave, 60 Hz, $T_J = +110^\circ\text{C}$)	I_{TSM}	20	A
Circuit Fusing Considerations ($t = 8.3\text{ ms}$)	I^2t	1.65	A^2s
Forward Peak Gate Power (Pulse Width $\leq 1.0\text{ }\mu\text{sec}$, $T_C = 80^\circ\text{C}$)	P_{GM}	0.5	W
Forward Average Gate Power (Pulse Width $\leq 1.0\text{ }\mu\text{sec}$, $T_C = 80^\circ\text{C}$)	$P_{G(AV)}$	0.1	W
Forward Peak Gate Current (Pulse Width $\leq 1.0\text{ }\mu\text{sec}$, $T_C = 80^\circ\text{C}$)	I_{GM}	0.2	A
Operating Junction Temperature Range	T_J	-40 to $+110$	$^\circ\text{C}$
Storage Temperature Range	T_{stg}	-40 to $+150$	$^\circ\text{C}$
Mounting Torque (Note 2)	–	6.0	in. lb.

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

- V_{DRM} and V_{RRM} for all types can be applied on a continuous basis. Ratings apply for zero or negative gate voltage; however, positive gate voltage shall not be applied concurrent with negative potential on the anode. Blocking voltages shall not be tested with a constant current source such that the voltage ratings of the devices are exceeded.
- Torque rating applies with use of compression washer (B52200F006). Mounting torque in excess of 6 in. lb. does not appreciably lower case-to-sink thermal resistance. Anode lead and heatsink contact pad are common.

THERMAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted.)

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	3.0	$^\circ\text{C/W}$
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	75	$^\circ\text{C/W}$
Maximum Lead Temperature for Soldering Purposes 1/8 in. from Case for 10 Seconds	T_L	260	$^\circ\text{C}$

ORDERING INFORMATION

Device	Package	Shipping [†]
C106B	TO-225AA	500 Units / Box
C106BG	TO-225AA (Pb-Free)	500 Units / Box
C106D	TO-225AA	500 Units / Box
C106DG	TO-225AA (Pb-Free)	500 Units / Box
C106D1*	TO-225AA	500 Units / Box
C106D1G*	TO-225AA (Pb-Free)	500 Units / Box
C106M	TO-225AA	500 Units / Box
C106MG	TO-225AA (Pb-Free)	500 Units / Box
C106M1*	TO-225AA	500 Units / Box
C106M1G*	TO-225AA (Pb-Free)	500 Units / Box

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

*D1 signifies European equivalent for D suffix and M1 signifies European equivalent for M suffix.

C106 Series

ELECTRICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted.)

Characteristic	Symbol	Min	Typ	Max	Unit
----------------	--------	-----	-----	-----	------

OFF CHARACTERISTICS

Peak Repetitive Forward or Reverse Blocking Current ($V_{AK} = \text{Rated } V_{DRM} \text{ or } V_{RRM}, R_{GK} = 1 \text{ k}\Omega$)	I_{DRM}, I_{RRM}	–	–	10	μA
$T_J = 25^\circ\text{C}$		–	–	100	μA
$T_J = 110^\circ\text{C}$		–	–		

ON CHARACTERISTICS

Peak Forward On-State Voltage (Note 3) ($I_{TM} = 4 \text{ A}$)	V_{TM}	–	–	2.2	V
Gate Trigger Current (Continuous dc) (Note 4) ($V_{AK} = 6 \text{ Vdc}, R_L = 100 \Omega$)	I_{GT}	–	15	200	μA
		–	35	500	
Peak Reverse Gate Voltage ($I_{GR} = 10 \mu\text{A}$)	V_{GRM}	–	–	6.0	V
Gate Trigger Voltage (Continuous dc) (Note 4) ($V_{AK} = 6 \text{ Vdc}, R_L = 100 \Omega$)	V_{GT}	0.4	0.60	0.8	V
		0.5	0.75	1.0	
Gate Non-Trigger Voltage (Continuous dc) (Note 4) ($V_{AK} = 12 \text{ V}, R_L = 100 \Omega, T_J = 110^\circ\text{C}$)	V_{GD}	0.2	–	–	V
Latching Current ($V_{AK} = 12 \text{ V}, I_G = 20 \text{ mA}, R_{GK} = 1 \text{ k}\Omega$)	I_L	–	0.20	5.0	mA
		–	0.35	7.0	
Holding Current ($V_D = 12 \text{ Vdc}$) (Initiating Current = 20 mA, $R_{GK} = 1 \text{ k}\Omega$)	I_H	–	0.19	3.0	mA
		–	0.33	6.0	
		–	0.07	2.0	


DYNAMIC CHARACTERISTICS

Critical Rate-of-Rise of Off-State Voltage ($V_{AK} = \text{Rated } V_{DRM}$, Exponential Waveform, $R_{GK} = 1 \text{ k}\Omega$, $T_J = 110^\circ\text{C}$)	dv/dt	–	8.0	–	V/ μs
--	---------	---	-----	---	------------------

- Pulse Test: Pulse Width $\leq 2.0 \text{ ms}$, Duty Cycle $\leq 2\%$.
- R_{GK} is not included in measurement.

Voltage Current Characteristic of SCR

Symbol	Parameter
V_{DRM}	Peak Repetitive Off State Forward Voltage
I_{DRM}	Peak Forward Blocking Current
V_{RRM}	Peak Repetitive Off State Reverse Voltage
I_{RRM}	Peak Reverse Blocking Current
V_{TM}	Peak On State Voltage
I_H	Holding Current



C106 Series




Figure 1. Average Current Derating




Figure 2. Maximum On-State Power Dissipation




Figure 3. Typical Gate Trigger Current versus Junction Temperature




Figure 4. Typical Holding Current versus Junction Temperature




Figure 5. Typical Gate Trigger Voltage versus Junction Temperature





Figure 6. Typical Latching Current versus Junction Temperature


C106 Series

PACKAGE INTERCHANGEABILITY

The dimensional diagrams below compare the critical dimensions of the ON Semiconductor C-106 package with competitive devices. It has been demonstrated that the smaller dimensions of the ON Semiconductor package make it compatible in most lead-mount and chassis-mount applications. The user is advised to compare all critical dimensions for mounting compatibility.



ON Semiconductor C-106 Package




Competitive C-106 Package

C106 Series

PACKAGE DIMENSIONS

TO-225
CASE 77-09
ISSUE Z



NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. 077-01 THRU -08 OBSOLETE, NEW STANDARD 077-09.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.425	0.435	10.80	11.04
B	0.295	0.305	7.50	7.74
C	0.095	0.105	2.42	2.66
D	0.020	0.026	0.51	0.66
F	0.115	0.130	2.93	3.30
G	0.094 BSC		2.39 BSC	
H	0.050	0.095	1.27	2.41
J	0.015	0.025	0.39	0.63
K	0.575	0.655	14.61	16.63
M	5° TYP		5° TYP	
Q	0.148	0.158	3.76	4.01
R	0.045	0.065	1.15	1.65
S	0.025	0.035	0.64	0.88
U	0.145	0.155	3.69	3.93
V	0.040	---	1.02	---

STYLE 2:

1. CATHODE
2. ANODE
3. GATE

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada

Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910

Japan Customer Focus Center
Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local
Sales Representative