

SmartPro 1.05kVA Line Interactive Sine Wave UPS, SNMPWEBCARD option, Tower, USB, Serial, 100/110/120V

MODEL NUMBER: **SMART1050SLT**



Highlights

- 1.05kVA / 1050VA line interactive tower UPS, Sine wave output
- 100/110/120V nominal output during brownouts and overvoltages
- USB, RS232 and slot for optional SNMP/Web card
- Detailed status LEDs, Single line TEL / DSL surge suppression
- NEMA 5-15P input, 8 NEMA 5-15R outlets

Package Includes

- SMART1050SLT UPS System
- PowerAlert Software CD
- USB and serial cabling

Description

1050VA line-interactive tower UPS system for server, networking and telecommunications equipment. Upright tower form factor. Offers sine wave 100V, 110V or 120V nominal output in both AC and battery modes. Switches to battery-derived AC output during power failures and extreme voltage variations. Line-interactive automatic voltage regulation (AVR) provides voltage boost during brownouts and voltage cut during overvoltages to maintain regulated 100V, 110V or 120V nominal output over an input voltage range of 95-145V. Features NEMA 5-15P input plug and 8 NEMA 5-15R output receptacles. Network-grade AC surge and noise suppression. Network management interfaces support simultaneous communications via USB port, DB9 serial port and SNMPWEBCARD slot. HID-compliant USB interface enables full integration with built-in power management and auto shutdown features of Windows and Mac OS X. Supports simultaneous detailed monitoring of equipment load levels, self-test data and utility power conditions via all 3 network interfaces. Includes PowerAlert monitoring software and complete cabling. Features 3-stage metered current monitoring and battery charge status LEDs. Dataline surge suppression for dialup, DSL or network Ethernet connection. Utility power and voltage regulation LEDs. Audible alarm. Self-test. Field replaceable, hot-swappable internal batteries and external battery packs. Attractive all-black color scheme.

Features

- SmartPro line-interactive UPS system is ideal for voice, data, medical and industrial networking applications
- Line-interactive automatic voltage regulation (AVR) maintains selectable 100V, 110V or 120V nominal output during brownouts as low as 83V and overvoltages to 145V
- Enables continuous operation through blackouts, voltage fluctuations and surges
- Line-interactive AVR provides a 14% boost during brownouts and a 12% voltage cut during overvoltages
- Standard internal battery set offers 19 min. runtime at half load (325W) and 7 min. at full load (650W)
- Space-saving upright tower format
- Network interfaces support simultaneous communications via built-in USB port, DB9 serial port and SNMPWEBCARD slot
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X.
- Included PowerAlert UPS monitoring software supports safe unattended shutdown, monitoring and control via local connected servers, plus any number of additional servers over IP
- UPS interface supports on-battery, low-battery, power-restored, AC-voltage, DC-voltage, output current monitoring, battery charge current, battery



- capacity, timed inverter shutoff, activate self-test and output power control
- NEMA 5-15P input plug; 8 x battery-supported NEMA 5-15R output receptacles
- Front panel LEDs offer current monitoring, voltage regulation and battery charge level information
- UPS ships fully assembled in full compliance with DOT regulations; no time-consuming connection of internal batteries by user required
- Single-line tel/DSL or network Ethernet line surge suppression

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	1050
Output kVA capacity (kVA)	1
Output Watt Capacity (watts)	650
Output power factor	0.6
Nominal Output Voltage(s) Supported	100V; 110V; 120V
Nominal Voltage details	120V default (voltage selection via back panel switches)
Frequency compatibility	50 / 60 Hz
Output voltage regulation (line mode)	-13%, + 15%
Output voltage regulation (Battery mode)	+/- 5%
Built-in UPS output receptacles	8 5-15R outlet(s)
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	Pure Sine wave
INPUT	
Rated input current (at maximum load)	6.1A (120V), 6.6A (110V), 7.2A (100V)
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 120V AC
UPS input connection type	5-15P
UPS Input cord length (ft.)	6
UPS Input cord length (m)	1.8
Recommended Electrical Service	15A 120V
Phase	Single-Phase
BATTERY	
Full load runtime (minutes)	7 min. (650w)
Half load runtime (minutes)	19 min. (325w)
DC system voltage (VDC)	24



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Battery recharge rate (included batteries)	Less than 6 hours from 10% to 90%
Replacement battery cartridge (internal UPS battery replacement)	RBC24-SLT
Battery Access	Battery access door
Battery replacement description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage regulation description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 95 to 145 (120v), 87 to 133 (110v), 83 to 121 (100v)
Overvoltage correction	Voltage reduction of 12% applies when input is 127 to 145 (120v), 116 to 133 (110v), 111 to 121 (100v)
Undervoltage correction	Voltage boost of 14% applies when input is 95 to 108 (120v), 87 to 99 (110v), 83 to 90 (100v)
LEDS ALARMS & SWITCHES	
LED Indicators	Status LEDs indicate line power, battery power, AVR, overload and replace battery status - with a 3-LED level meter for load and battery charge level
Site wiring fault indication	Rear panel site wiring fault LED
Alarms	Audible alarm indicates power failure and overload conditions
Alarm cancel operation	Power-fail alarm can be silenced using alarm-cancel switch
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; rear panel protected switches support nominal voltage selection
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	690
UPS AC suppression response time	Instantaneous
UPS Dataline suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC noise suppression	Yes
PHYSICAL	
Installation form factors supported with included accessories	Tower
Primary form factor	Tower
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	10.2 x 6.8 x 13.2
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	26 x 17.1 x 33.7
UPS / Power Module weight (lbs)	36
UPS / Power Module weight (kg)	16.3
UPS Shipping dimensions (height x width x depth / inches)	14 x 9.8 x 18.5



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPS Shipping dimensions (height x width x depth / cm)	35.6 x 24.8 x 47
Shipping weight (lbs)	39.6
Shipping weight (kg)	18
Cooling method	Fan
UPS housing material	Steel
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius.
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius.
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	141.1
Battery mode BTU / hr. (full load)	452.7
AC mode efficiency rating (100% load)	94%
Audible Noise	Audible Noise < 50 dBA at Front Side 1 Meter
COMMUNICATIONS	
Communications interface	USB; DB9 Serial; Slot for SNMP/Web interface
Network monitoring port description	Supports detailed monitoring of UPS and site power conditions
PowerAlert software	Included
Communications cable	USB and DB9 cabling included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications.
LINE / BATTERY TRANSFER	
Transfer time	4-6 milliseconds
Low voltage transfer to battery power (setpoint)	95V (120V), 87V (110V), 83V (100V)
High voltage transfer to battery power (setpoint)	145V (120V), 133V (110V), 121V (100V)
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
High availability UPS features	Hot swappable batteries
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	2-year warranty, 3 year with registration. Note: Registration is required for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

Related Items

Optional Products

Model Number	Description	Qty.
SNMPWEBCARD	For remote monitoring and control via SNMP, Web, or Telnet.	1
ENVIROSENSE	Monitors temperature, humidity and contact-closure inputs. (Requires SNMPWEBCARD or switched PDU.)	1
MODBUSCARD	For remote monitoring and control via MODBUS protocol	1
WEXT5-500-1500	5-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 1500VA or less	1
RBC24-SLT	UPS Replacement Battery Cartridge for select Tripp Lite SLT UPS	1
WATCHDOGSW	WatchDog Service Monitoring / Reboot Software	1
PDUB15	Dual source Power Distribution Unit / PDU with Manual Transfer Switch enables Hot-swappable UPS Replacement in Critical Network Applications	1
PDU1215	Basic PDU / Power Distribution Unit - Safe, reliable power distribution for critical networking equipment	1
PDUNV	Basic PDU / Power Distribution Unit - Safe, reliable power distribution for critical networking equipment	1
PDUMH15	Metered PDU / Power Distribution Unit - Safe, reliable power distribution with digital current meter	1
PDUMH15AT	Metered PDU with ATS - Power Distribution Unit with dual-input Auto Transfer Switching	1
PDUMNH15	Monitored PDU / Power Distribution Unit supports real-time remote monitoring of load level, voltage and frequency with options for remote environmental and security monitoring	1
PDUMNV15	Monitored PDU / Power Distribution Unit supports real-time remote monitoring of load level, voltage and frequency with options for remote environmental and security monitoring	1
PDUMH15ATNET	Switched, Metered PDU with ATS - Power Distribution Unit with dual-input Auto Transfer Switching, individual outlet control and remote network interface	1
PDUMV15NET	Switched, Metered PDU with Remote Monitoring - 0U Vertical Rackmount Power Distribution Unit for Networks with Individually Switchable Outlets, Current Metering, Remote Monitoring and Control	1
P007-002	2-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P007-006	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P007-010	10-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P010-012	12-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

P022-001	1-ft. 18AWG Power Extension cord (NEMA 5-15R to NEMA 5-15P)	1
P023-001	1-ft. 14AWG Power Adapter cord (NEMA L5-15R to NEMA 5-15P)	1
P034-010	10-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to NEMA 5-15P)	1
RELAYIOCARD	Programmable Relay I/O Card	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at:
<http://www.tripplite.com/sku/SMART1050SLT>.

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement.
Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SMART1050SLT](#)