






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		A	REV PER EC 0S12-0647-04	09MAY05	JA	SF
			A1	REVISED PER ECO-10-000444	19JAN10	KK	HMR

1. WIRE RANGE 22-26 AWG.
2. INSULATION RANGE 0.91-1.37 [.036-.054] DIA.
3. 0.00254 [.000100] MIN MATTE TIN OVER 0.000762 [.000030] MIN NICKEL.
4. PREPLATED 0.00127 [.000050] MIN MATTE TIN IN ZONES I & II, 0.000762 [.000030] MIN GOLD OVER 0.000762 [.000030] MIN NICKEL INLAY IN ZONE III.
5. PREPLATED 0.00127 [.000050] MIN MATTE TIN IN ZONES I & II, 0.00127 [.000050] MIN GOLD OVER 0.000762 [.000030] MIN NICKEL INLAY IN ZONE III.
6. PHOSPHOR BRONZE.
7. ZONE I (OUTSIDE SURFACES).
8. ZONE II (INSIDE SURFACES).
9. ZONE III (INSIDE SURFACES).
10. MAXIMUM CUTOFF.
11. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SECTION Y-Y



SECTION Z-Z

5	5	5530553-9	1	5530553-8	1
5		-		5530553-6	
	4	-		5530553-4	
	3	-		5530553-2	
FINISH		LOOSE PIECE PART NO		STRIP PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ALCORTA - DOCK5 CHK A. FRANTUM APVD S. FLICKINGER	09MAY05 09MAY05 09MAY05	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm[INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-25031 APPLICATION SPEC 114-25021	NAME	CONTACT, RECEPTACLE, STANDARD PRESSURE, MINI-TANDEM SPRING	
MATERIAL 6	FINISH 3 4 5	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=5530553
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1	REV A1