





LOC AF	DIST 50	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
					O 1	REVISED PER ECO-09-021826	21AUG09	KK/AEG
					O	DRAWN PER 0266-94	5/26/94	JR/PD




VIEW A-A
SCALE 8:1

- 1 CONTINUOUS STRIP ON REELS.
- 2 TIN PLATE 0.002032 [.000080] MIN THK.
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SECTION B-B
SCALE 8:1



SECTION C-C
SCALE 8:1

3 OBSOLETE	3.05—4.32 DIA [.120—.170] DIA	[#18—#14] AWG	0.81 [.032]	TIN 2	60713—2—
				—	60713—1
	INSULATION RANGE	WIRE SIZE	MATING TAB THK ±0.025 [.001]	FINISH	PART NO
	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.25 [.010] 3 PLC DEC ± — ANGLES ± —	DR 5/26/94 JR RUTH	AMP AMP Incorporated Harrisburg, PA 17105—3608		
		CHK 5/26/94 MS FEHER			
		APPD 5/26/94 P DESANTIS	NAME RECEPTACLE, FASTON, 6.35 [.250] SERIES		
		APPD 5/26/94 R REINER			
	PRODUCT SPEC —				
	MATERIAL H04 BRASS	APPLICATION SPEC —	SIZE B	CAGE CODE 00779	DRAWING NO C —60713
	FINISH SEE TABLE	WEIGHT —	SCALE 4:1		SHEET 1 OF 1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.