

INTRODUCTION:

Adam Tech ADC Series DC Power Jacks are a complete line of miniature and sub-miniature power jacks primarily used for the transmission of wall current transformed to DC power, for detached and hand held instruments. Adam Tech power jacks are manufactured with a variety of center pin sizes for all standard applications including 1.00mm, 1.30mm, 2.00mm and 2.50mm. Our contact is designed using a wide spring grade plated copper alloy for exceptional plug retention and low contact resistance.

FEATURES:

- Low Profile designs
- Superior contact system
- Exceptional plug retention
- Choice of Center pin sizes
- Hi Temp Versions
- Hi Current Versions

MATING PLUGS:

All industry standard 1.00mm, 1.30mm, 2.00mm, 2.35mm and 2.50mm Plugs.

SPECIFICATIONS:

Material:

Standard insulator: PBT Glass reinforced, rated UL94V-0
Optional Hi-Temp insulator: Nylon 6T, rated UL94V-0
Insulator Color: Black
Center Pin: Brass, Nickel plated
Contacts: Copper alloy

Contact Plating:

Silver over nickel underplate

Electrical:

Operating voltage: 12V DC max.
Current rating: 1 Amp max.
Contact resistance: 30 mΩ max. initial
Insulation resistance: 50 MΩ min.
Dielectric withstanding voltage: 250V AC for 1 minute

Mechanical:

Insertion force: 3 kg max.
Withdrawal force: 0.3 kg min
Mating durability: 5000 cycles min.

Temperature Rating:

Operating temperature: -25°C to +85°C
Soldering process temperature:
Standard insulator: 235°C
Hi-Temp insulator: 260°C

PACKAGING:

Anti-ESD plastic bags or Tape and Reel

APPROVALS AND CERTIFICATIONS:

UL Recognized & CSA Certified, File no. E224053

**HI-TEMP
INSULATOR
AVAILABLE**





DC POWER JACKS

PC BOARD AND PANEL MOUNT

ADC SERIES



ORDERING INFORMATION



OPTIONS:

Add designator(s) to end of part number

RT = PC Board Retention Feature
(Type 007 & 009 only)

HT = Hi-Temp insulator for Hi-Temp soldering processes up to 260°C




N = Notch option, (ADC-002 only)

ADCH = DC Power Jack Hi-Current 5 Amp Version

ADC-007



ADC-007-3






Recommended PCB Layout

ADC-009




ADC-009-3






Recommended PCB Layout

ADC-011



ADC-011-3






Recommended PCB Layout

ADC-021



ADC-021-3






Recommended PCB Layout

ADC-029



ADC-029-1






Recommended PCB Layout

ADC-002



ADC-002-2






Recommended PCB Layout

ADC-024



ADC-024-8






Recommended PCB Layout

ADC-028



ADC-028-2





Recommended PCB Layout

ADC-027

ADC-027






ADC-027-M8



ADC-085






ADC-085-1



Recommended PCB Layout




ADC-086

ADC-085-2



Recommended PCB Layout

ADC-087


**ADC-087**

Recommended PCB Layout

ADC-010



ADC-010-1




Recommended PCB Layout

ADC-015



ADC-015-2




Recommended PCB Layout

ADC-045A




ADC-045A-1




Recommended PCB Layout

ADP-PLUG WITH STRAIN RELIEF



ADP-PLUG WITHOUT STRAIN RELIEF



PLUG WITH STRAIN RELIEF	X	Y	Z
ADP-X/Y/Z-SR	$\phi .039$ [1.00]	$\phi .137$ [3.50]	.374 [9.50]
ADP-X/Y/Z-SR	$\phi .082$ [2.10]	$\phi .216$ [5.50]	.374 [9.50]
ADP-X/Y/Z-SR	$\phi .098$ [2.50]	$\phi .216$ [5.50]	.374 [9.50]

PLUG WITHOUT STRAIN RELIEF	X	Y	Z
ADP-X/Y/Z	$\phi .039$ [1.00]	$\phi .137$ [3.50]	.374 [9.50]
ADP-X/Y/Z	$\phi .082$ [2.10]	$\phi .216$ [5.50]	.374 [9.50]
ADP-X/Y/Z	$\phi .098$ [2.50]	$\phi .216$ [5.50]	.374 [9.50]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ADAM TECH:

[ADC-027-1-M8](#) [ADC-002A-1](#) [ADC-002A-2](#) [ADC-003-1](#) [ADC-005-1](#) [ADC-007-3](#) [ADC-007-4](#) [ADC-010-1](#)