

TMP type

PCB type

RoHS compliant

### FEATURES

#### 1. Ideal for compressor and inverter loads

- 1) Compressor load: 20A 250V AC
- 2) Inverter load: 20A 100V AC,  
10A 200V AC

#### 2. High insulation resistance

- Creepage distance and clearances between contact and coil;  
Creepage Min. 9.5mm .374inch/  
Clearance Min. 8mm .315inch
- Surge withstand voltage: 10,000V

#### 3. "PCB" and "TMP" types available


#### 4. Conforms to the various safety standards:

UL/C-UL, TÜV and VDE approved

### TYPICAL APPLICATIONS

- Air conditioner
- Refrigerators
- OA equipment

### ORDERING INFORMATION



Note: Certified by UL/C-UL, VDE and TÜV

### TYPES

| Contact arrangement | Nominal coil voltage | Part No. |          |
|---------------------|----------------------|----------|----------|
|                     |                      | TMP type | PCB type |
| 1 Form A            | 5V DC                | ALF1T05  | ALF1P05  |
|                     | 6V DC                | ALF1T06  | ALF1P06  |
|                     | 9V DC                | ALF1T09  | ALF1P09  |
|                     | 12V DC               | ALF1T12  | ALF1P12  |
|                     | 18V DC               | ALF1T18  | ALF1P18  |
|                     | 24V DC               | ALF1T24  | ALF1P24  |

Standard packing: Carton 50 pcs., Case 200 pcs.

### RATING

#### 1. Coil data

| Nominal coil voltage | Pick-up voltage<br>(at 20°C 68°F)         | Drop-out voltage<br>(at 20°C 68°F)        | Nominal operating current<br>[±10%] (at 20°C 68°F) | Coil resistance<br>[±10%] (at 20°C 68°F) | Nominal operating power<br>(at 20°C 68°F) | Max. applied voltage<br>(at 20°C 68°F) |
|----------------------|-------------------------------------------|-------------------------------------------|----------------------------------------------------|------------------------------------------|-------------------------------------------|----------------------------------------|
| 5V DC                | 70%V or less of nominal voltage (Initial) | 10%V or more of nominal voltage (Initial) | 180 mA                                             | 27.8Ω                                    | 900mW                                     | 110%V of nominal voltage               |
| 6V DC                |                                           |                                           | 150 mA                                             | 40 Ω                                     |                                           |                                        |
| 9V DC                |                                           |                                           | 100 mA                                             | 90 Ω                                     |                                           |                                        |
| 12V DC               |                                           |                                           | 75 mA                                              | 160 Ω                                    |                                           |                                        |
| 18V DC               |                                           |                                           | 50 mA                                              | 360 Ω                                    |                                           |                                        |
| 24V DC               |                                           |                                           | 37.5mA                                             | 640 Ω                                    |                                           |                                        |

# LF (ALF)

## 2. Specifications

| Characteristics            | Item                                                           |                          | Specifications                                                                                                                |
|----------------------------|----------------------------------------------------------------|--------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Contact                    | Contact material                                               |                          | AgSnO <sub>2</sub> type                                                                                                       |
|                            | Arrangement                                                    |                          | 1 Form A                                                                                                                      |
|                            | Contact resistance (Initial)                                   |                          | Max. 100 mΩ (By voltage drop 6 V DC 1A)                                                                                       |
| Rating                     | Nominal switching capacity (resistive load)                    |                          | 20A 250V AC                                                                                                                   |
|                            | Max. switching power (resistive load)                          |                          | 6,250VA                                                                                                                       |
|                            | Max. switching voltage                                         |                          | 250V AC                                                                                                                       |
|                            | Max. switching current                                         |                          | 25A                                                                                                                           |
|                            | Nominal operating power                                        |                          | 900mW                                                                                                                         |
| Electrical characteristics | Min. switching capacity (reference value)*1                    |                          | 100mA, 5V DC                                                                                                                  |
|                            | Insulation resistance (Initial)                                |                          | Min. 1,000MΩ (at 500V DC) Measurement at same location as "Breakdown voltage" section.                                        |
|                            | Breakdown voltage (Initial)                                    | Between open contacts    | 1,000 Vrms for 1 min. (Detection current: 10 mA)                                                                              |
|                            |                                                                | Between contact and coil | 5,000 Vrms for 1 min. (Detection current: 10 mA)                                                                              |
|                            | Temperature rise (coil)                                        |                          | Max. 45°C 113°F (By resistive method, nominal coil voltage applied to the coil; contact carrying current: 20A, at 60°C 140°F) |
|                            | Surge breakdown voltage*2 (Between contact and coil) (Initial) |                          | 10,000 V                                                                                                                      |
|                            | Operate time (at nominal voltage) (at 20°C 68°F)               |                          | Max. 20 ms (excluding contact bounce time.)                                                                                   |
| Mechanical characteristics | Release time (at nominal voltage) (at 20°C 68°F)               |                          | Max. 15 ms (excluding contact bounce time) (With diode)                                                                       |
|                            | Shock resistance                                               | Functional               | 100 m/s <sup>2</sup> (Half-wave pulse of sine wave: 11 ms; detection time: 10μs.)                                             |
|                            |                                                                | Destructive              | 1,000 m/s <sup>2</sup> (Half-wave pulse of sine wave: 6 ms.)                                                                  |
|                            | Vibration resistance                                           | Functional               | 10 to 55 Hz at double amplitude of 1.5 mm (Detection time: 10μs.)                                                             |
|                            |                                                                | Destructive              | 10 to 55 Hz at double amplitude of 1.5 mm                                                                                     |
| Expected life              | Mechanical (at 180 times/min.)                                 |                          | Min. 2×10 <sup>6</sup>                                                                                                        |
|                            | Electrical (at 20 times/min.)                                  |                          | Min. 10 <sup>5</sup> (resistive load)                                                                                         |
| Conditions                 | Conditions for operation, transport and storage*3              |                          | Ambient temperature: -40°C to +60°C -40°F to +140°F, Humidity: 5 to 85% R.H. (Not freezing and condensing at low temperature) |
|                            | Max. operating speed                                           |                          | 20 times/min. (at nominal switching capacity)                                                                                 |
| Unit weight                |                                                                |                          | Approx. 23 g .81 oz                                                                                                           |

\* Specifications will vary with foreign standards certification ratings.

Notes: \*1. This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.

\*2. Wave is standard shock voltage of ±1.2×50μs according to JEC-212-1981

\*3. The upper limit of the ambient temperature is the maximum temperature that can satisfy the coil temperature rise value. Refer to Usage, transport and storage conditions in NOTES.

## 3. Switching capacity

|                 |                 |                                                                |                                              |
|-----------------|-----------------|----------------------------------------------------------------|----------------------------------------------|
| Electrical Life | Resistive load  | 20 A, 250 V AC (cosφ = 1)                                      | Min. 10 <sup>5</sup><br>(at 20 times/min.)   |
|                 |                 | 25 A, 250 V AC (cosφ = 1)                                      | Min. 10 <sup>4</sup><br>(at 20 times/min.)   |
|                 | Compressor load | Inrush 70 A (cosφ = 0.7), Steady 20 A (cosφ = 0.9)<br>250 V AC | Min. 10 <sup>5</sup><br>(at 20 times/min.)   |
|                 |                 | Inrush 200 A, Steady 20 A<br>100 V AC                          | Min. 3×10 <sup>4</sup><br>(at 10 times/min.) |
|                 | Inverter load   | Inrush 100 A, Steady 10 A<br>200 V AC                          | Min. 3×10 <sup>4</sup><br>(at 10 times/min.) |
|                 |                 |                                                                |                                              |

## REFERENCE DATA


### 1. Coil temperature rise

Sample: ALF1T12, 6 pcs.

Point measured: coil inside

Contact current: 20A

Ambient temperature: 25°C 77°F, 60°C 140°F



### 2-(1). 200V AC electrical life test

(200V AC, inverter load)



Sample: ALF1T12, 6 pcs.

Load: Inrush 102A (wave peak value),  
Steady 14.4A (wave peak value)



Inverter dummy 200V AC

Switching frequency: ON 1s, OFF 5s



Circuit:




2-(2). 100V AC electrical life test  
(100V AC, inverter load)  
Sample: ALF1T12, 6 pcs.  
Load: Inrush 224A (wave peak value),  
Steady 30.5A (wave peak value)  
Inverter dummy 100V AC  
Switching frequency: ON 1s, OFF 5s  
Circuit:



2-(3). Inrush 70.7A, Steady 20A, 250V AC  
electrical life test (Compressor dummy load)  
Sample: ALF1T12, 3 pcs.  
Load: Inrush 70.7A,  $\cos\phi = 0.7$   
Steady 20A,  $\cos\phi = 0.9$   
250V AC compressor dummy  
Switching frequency: ON 1.5s, OFF 1.5s  
Circuit:



2-(4). Electrical life test  
(20A 250V AC, resistive load)  
Sample: ALF1T12, 6 pcs.  
Switching frequency: ON 1.5s, OFF 1.5s



LF (ALF)


DIMENSIONS (mm inch)

1. TMP type


CAD Data



External dimensions




PC board pattern (Bottom view)



Tolerance: ±0.1 ±.004

Schematic (Bottom view)



**Dimension:**  
Less than 1mm .039inch:  
Min. 1mm .039inch less than 3mm .118 inch:  
Min. 3mm .118 inch:


**Tolerance**  
±0.1 ±.004  
±0.2 ±.008  
±0.3 ±.012

2. PCB type


CAD Data



External dimensions




PC board pattern (Bottom view)



Tolerance: ±0.1 ±.004

Schematic (Bottom view)



**Dimension:**  
Less than 1mm .039inch:  
Min. 1mm .039inch less than 3mm .118 inch:  
Min. 3mm .118 inch:

**Tolerance**  
±0.1 ±.004  
±0.2 ±.008  
±0.3 ±.012

SAFETY STANDARDS

| UL/C-UL (Recognized) |                            | VDE (Certified) |                        | TV rating (UL/CSA) |        | TÜV (Certified)      |                        |
|----------------------|----------------------------|-----------------|------------------------|--------------------|--------|----------------------|------------------------|
| File No.             | Contact rating             | File No.        | Contact rating         | File No.           | Rating | File No.             | Rating                 |
| E43028               | 25A 277V AC<br>20A 277V AC | 40009169        | 20A 250V AC (cosφ=1.0) | UL E43028          | TV-8   | B 11 04<br>13461 295 | 20A 250V AC (cosφ=1.0) |

\* CSA standard: Certified by C-UL

For Cautions for Use.