








LOC		DIST		REVISIONS				
DY	-	P	LTR	DESCRIPTION		DATE	DWN	APVD
			K	REVISED ECR-05-012431		05OCT05	SYJ	LSF



- △ MATERIAL, HOUSING, HIGH TEMP. PLASTIC, UL94V-0
CONTACT: COPPER ALLOY
LOCK LEVER: SUS301 TIN PLATING.
- △ FINISH; CONTACT AREA: 0.00025 MIN GOLD PLT ON
0.001 MIN ALL OVER NICKEL
SOLDERING AREA: 0.00005 MIN TO 0.00030 MAX GOLD PLATE
- 3. TOLERANCES NON-ACCUMULATIVE.
- △ DIMENSIONING TO MODULE CENTER LINE.
- △ PART PACKAGING PER EIA-18-704 STANDARD REEL
DIAMETER SHALL BE 330mm. TAPE WIDTH SHALL
BE 88mm AND TAPE PITCH SHALL BE 36mm

AVAILABLE	SDRAM 3.3V	144	6-390322-1
AVAILABLE	SDRAM 3.3V	144	390322-1
REMARKS	POWER SUPPLY	POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS THE PROPERTY OF AMP INCORPORATED. IT IS TO BE USED ONLY FOR THE PURPOSES FOR WHICH IT WAS ISSUED. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT PERMISSION IN WRITING FROM AMP INCORPORATED.		DWN J. BURWELL 8NOV99	AMP MANUFACTURING (SINGAPORE) PTE. LTD.	
DIMENSIONS: mm		CHK K. KREIDLER 22JUL99	NAME S.O.DIM SOCKET ASSY, 0.8mm PITCH 144 POS., 8mm PROFILE FOR SDRAM TYPE MODULE	
TOLERANCES, UNLESS OTHERWISE SPECIFIED: 9 PLC ±0.2 1 PLC ±0.2 5 PLC ±0.2 4 PLC ±0.2 ANGLES ±		APVD SE LEONG	SIZE A1	
MATERIAL - △		FINISH - △	CAGE CODE 00779	
CUSTOMER DRAWING		WEIGHT -	DRAWING NO. C-390322	
		SCALE 4:1	SHEET 1 OF 2	
			REV K	

AMP 4805 REV 09MAY94