




All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to

IEC 61169-4, EN 122190, DIN 47223

Documents

Application note

AN001 "Calibration Services"

Material and plating

Connector parts

Center conductor plug side
Center conductor plug side
Outer conductor
Coupling nut
Gasket

Material

Brass
CuBe
Brass
Stainless steel
NBR

Plating

Gold, min. 1.27 µm, over nickel
Gold, min. 1.27 µm, over nickel
Gold, min. 1.27 µm, over nickel
Passivated

Electrical data

Insertion loss ≤ 0.06 dB at 8 GHz

Mechanical data

Mating cycles ≥ 500
 Maximum torque 35 Nm
 Recommended torque 2.26 Nm
 Airline dimensions at 23 °C:
 - Diameter outer conductor 16.060 mm $\pm$ 0.010 mm
 - Diameter inner conductor 6.975 mm $\pm$ 0.005 mm
 - Length outer conductor 66.00 mm $\pm$ 0.02 mm
 - Length inner conductor 65.98 mm $\pm$ 0.02 mm
 - Length difference ≤ 0.06 mm
 (outer conductor – inner conductor)

Calculated data (non warranted)

Lossless characteristic impedance¹ 50 Ω $\pm$ 0.10 Ω
 Return loss² ≥ 45 dB, 0.2 GHz to 4 GHz
 ≥ 40 dB, 4 GHz to 8 GHz

1. The lossless characteristic impedance is calculated from the specified diameters of the inner and outer conductor.
2. The return loss is calculated from the characteristic impedance, the skin depth and the connector interface.

General standard definitions

For proper work the vector network analyzer (VNA) used needs a model describing the electrical behaviour of this calibration standard. Depending on the VNA type different models, units and terms are used and have to be entered into the VNA. All values are based on typical geometry and plating.

- Offset Z_o / Impedance / Z_o 50 Ω
 - Offset Delay 220.257 ps
 - Length (electrical) / Offset Length 66.031 mm
 - Offset Loss 0.70 G Ω /s
 - Loss 0.0134 dB/ $\sqrt{\text{GHz}}$

Environmental data

Operating temperature range³ +20 °C to +26 °C
 Storage temperature range 0 °C to +50 °C
 RoHS compliant

3. This range is a recommendation. However, the airline can be used in a wider range.
 Any temperature change from 23 °C results in dimensional changes.

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG
RF_35/09.14/6.2

Technical Data Sheet				Rosenberger											
7-16		Airline Plug / Jack		60S101-K066											
Declaration of calibration options Factory Calibration Standard delivery for this calibration standard includes a Factory Calibration. The Calibration Certificate issued reports individual mechanical calibration results, traceable to national / international standards. Model based standard definitions are reported in an Agilent/Keysight, Rohde & Schwarz and Anritsu compatible VNA format. Accredited Calibration Not available. For further, more detailed information see application note AN001 on the Rosenberger homepage. Calibration interval Recommendation12 months Packing Standard1 pce in box Weight187.2 g/pce Center conductorloose in an acrylic glass tube															
While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.															
Draft		Date		Rev.		Engineering change number		Name		Date					
Herbert Babinger		14.03.05		Martin Moder		09.11.15		f00		14-1492		Maik Knoll		09.11.15	
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de								Tel. : +49 8684 18-0 Email : info@rosenberger.de				Page 3 / 3			