

BF1216

Dual N-channel dual gate MOSFET

Rev. 01 — 29 April 2010

Product data sheet

1. Product profile

1.1 General description

The BF1216 is a combination of two dual gate MOSFET amplifiers with shared source and gate2 leads.

The source and substrate are interconnected. Internal bias circuits enable DC stabilization and very good cross modulation performance during AGC. Integrated diodes between the gates and source protect against excessive input voltage surges. The transistor is available as a SOT363 micro-miniature plastic package.

CAUTION



This device is sensitive to ElectroStatic Discharge (ESD). Therefore care should be taken during transport and handling.

1.2 Features and benefits

- Two low noise gain controlled amplifiers in a single package; both with a partly integrated bias
- Superior cross modulation performance during AGC
- High forward transfer admittance
- High forward transfer admittance to input capacitance ratio

1.3 Applications

- Gain controlled low noise amplifiers for VHF and UHF applications running on a 5 V supply voltage
 - ◆ digital and analog television tuners
 - ◆ professional communication equipment



1.4 Quick reference data

Table 1. Quick reference data for amplifier A and B

| Symbol | Parameter | Conditions | Min | Typ | Max | Unit | |
|---------------|------------------------------|--|-----|-----|-----|--------------------|------------|
| V_{DS} | drain-source voltage | DC | - | - | 6 | V | |
| I_D | drain current | DC | - | - | 30 | mA | |
| P_{tot} | total power dissipation | $T_{sp} \leq 107 \text{ }^{\circ}\text{C}$ | [1] | - | - | 180 mW | |
| $ Y_{fs} $ | forward transfer admittance | $f = 100 \text{ MHz}; T_j = 25 \text{ }^{\circ}\text{C}; I_D = 18 \text{ mA}$ | 23 | 27 | 38 | mS | |
| $C_{iss(G1)}$ | input capacitance at gate1 | $f = 100 \text{ MHz}$ | [2] | - | 2.5 | - | pF |
| C_{rss} | reverse transfer capacitance | $f = 100 \text{ MHz}$ | [2] | - | 25 | - | fF |
| NF | noise figure | $f = 400 \text{ MHz}; Y_S = Y_{S(opt)}$ | - | 1.0 | - | dB | |
| | | $f = 800 \text{ MHz}; Y_S = Y_{S(opt)}$ | - | 1.5 | - | dB | |
| Xmod | cross modulation | input level for $k = 1 \text{ \%}$ at 40 dB AGC; $f_w = 50 \text{ MHz}$; $f_{unw} = 60 \text{ MHz}$ | [3] | 105 | 107 | - | dB μ V |
| T_j | junction temperature | | - | - | 150 | $^{\circ}\text{C}$ | |

[1] T_{sp} is the temperature at the soldering point of the source lead.


[2] Calculated from S-parameters.

[3] Measured in [Figure 17](#) test circuit.

2. Pinning information

Table 2. Discrete pinning

| Pin | Description | Simplified outline | Graphic symbol |
|-----|---------------------|--------------------|----------------|
| 1 | gate1 (amplifier A) | | |
| 2 | gate2 | | |
| 3 | gate1 (amplifier B) | | |
| 4 | drain (amplifier B) | | |
| 5 | source | | |
| 6 | drain (amplifier A) | | |



3. Ordering information

Table 3. Ordering information

| Type number | Package | | | Version |
|-------------|---------|--|--|---------|
| | Name | Description | | |
| BF1216 | - | plastic surface-mounted package; 6 leads | | SOT363 |

4. Marking

Table 4. Marking

| Type number | Marking | Description |
|-------------|---------|-------------------|
| BF1216 | M5p | made in Hong Kong |
| | M5t | made in Malaysia |
| | M5w | made in China |

5. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

| Symbol | Parameter | Conditions | Min | Max | Unit |
|-------------------|-------------------------|---------------------------------|-----|----------|------------------|
| Per MOSFET | | | | | |
| V_{DS} | drain-source voltage | | - | 6 | V |
| I_D | drain current | DC | - | 30 | mA |
| I_{G1} | gate1 current | | - | ± 10 | mA |
| I_{G2} | gate2 current | | - | ± 10 | mA |
| P_{tot} | total power dissipation | $T_{sp} \leq 107^\circ\text{C}$ | [1] | - | mW |
| T_{stg} | storage temperature | | -65 | +150 | $^\circ\text{C}$ |
| T_j | junction temperature | | - | 150 | $^\circ\text{C}$ |

[1] T_{sp} is the temperature at the soldering point of the source lead.




Fig 1. Power derating curve

6. Thermal characteristics

Table 6. Thermal characteristics

| Symbol | Parameter | Conditions | Typ | Unit |
|----------------|--|------------|-----|------|
| $R_{th(j-sp)}$ | thermal resistance from junction to solder point | | 240 | K/W |

7. Static characteristics

Table 7. Static characteristics

$T_j = 25^\circ\text{C}$.

| Symbol | Parameter | Conditions | Min | Typ | Max | Unit |
|---|--------------------------------|--|-----|-----|-----|------|
| Per MOSFET; unless otherwise specified | | | | | | |
| $V_{(BR)DSS}$ | drain-source breakdown voltage | $V_{G1-S} = V_{G2-S} = 0\text{ V}$; $I_D = 10\text{ }\mu\text{A}$ | | | | |
| | | amplifier A | 6 | - | - | V |
| | | amplifier B | 6 | - | - | V |
| $V_{(BR)G1-SS}$ | gate1-source breakdown voltage | $V_{G2-S} = V_{DS} = 0\text{ V}$; $I_{G1-S} = 10\text{ mA}$ | 6 | - | 10 | V |
| $V_{(BR)G2-SS}$ | gate2-source breakdown voltage | $V_{G1-S} = V_{DS} = 0\text{ V}$; $I_{G2-S} = 10\text{ mA}$ | 6 | - | 10 | V |
| $V_{F(S-G1)}$ | forward source-gate1 voltage | $V_{G2-S} = V_{DS} = 0\text{ V}$; $I_{S-G1} = 10\text{ mA}$ | 0.5 | - | 1.5 | V |
| $V_{F(S-G2)}$ | forward source-gate2 voltage | $V_{G1-S} = V_{DS} = 0\text{ V}$; $I_{S-G2} = 10\text{ mA}$ | 0.5 | - | 1.5 | V |
| $V_{G1-S(th)}$ | gate1-source threshold voltage | $V_{DS} = 5\text{ V}$; $V_{G2-S} = 4\text{ V}$; $I_D = 100\text{ }\mu\text{A}$ | 0.3 | - | 1.0 | V |
| $V_{G2-S(th)}$ | gate2-source threshold voltage | $V_{DS} = 5\text{ V}$; $V_{G1-S} = 5\text{ V}$; $I_D = 100\text{ }\mu\text{A}$ | 0.4 | - | 1.0 | V |
| I_{DS} | drain-source current | $V_{G2-S} = 4\text{ V}$ | [1] | | | |
| | | amplifier A; $V_{DS(A)} = 5\text{ V}$; $R_{G1(A)} = 39\text{ k}\Omega$ | - | - | 24 | mA |
| | | amplifier B; $V_{DS(B)} = 5\text{ V}$; $R_{G1(B)} = 39\text{ k}\Omega$ | - | - | 24 | mA |
| I_{G1-S} | gate1 cut-off current | $V_{G2-S} = 0\text{ V}$; $V_{DS(A)} = V_{DS(B)} = 0\text{ V}$ | | | | |
| | | amplifier A; $V_{G1-S(A)} = 5\text{ V}$ | - | - | 50 | nA |
| | | amplifier B; $V_{G1-S(B)} = 5\text{ V}$ | - | - | 50 | nA |
| I_{G2-S} | gate2 cut-off current | $V_{G2-S} = 4\text{ V}$; $V_{DS(A)} = V_{DS(B)} = 0\text{ V}$; $V_{G1-S(A)} = V_{G1-S(B)} = 0\text{ V}$ | - | - | 20 | nA |

[1] R_{G1} connects gate1 to $V_{GG} = 5\text{ V}$; see [Figure 17](#).

8. Dynamic characteristics

Table 8. Dynamic characteristics for amplifier A and B


Common source; $T_{amb} = 25^\circ\text{C}$; $V_{G2-S} = 4\text{ V}$; $V_{DS} = 5\text{ V}$; $I_D = 19\text{ mA}$.

| Symbol | Parameter | Conditions | Min | Typ | Max | Unit | |
|---------------|------------------------------|---|-----|-----|-----|------------------------|-------------|
| $ y_{fs} $ | forward transfer admittance | $f = 100\text{ MHz}$; $T_j = 25^\circ\text{C}$; $I_D = 18\text{ mA}$ | 23 | 27 | 38 | mS | |
| $C_{iss(G1)}$ | input capacitance at gate1 | $f = 100\text{ MHz}$ | [1] | - | 2.5 | - | pF |
| $C_{iss(G2)}$ | input capacitance at gate2 | $f = 100\text{ MHz}$ | [1] | - | 2.4 | - | pF |
| C_{oss} | output capacitance | $f = 100\text{ MHz}$ | [1] | - | 0.8 | - | pF |
| C_{rss} | reverse transfer capacitance | $f = 100\text{ MHz}$ | [1] | - | 25 | - | fF |
| G_{tr} | transducer power gain | amplifier A; $B_S = B_{S(\text{opt})}$; $B_L = B_{L(\text{opt})}$ | [1] | | | | |
| | | $f = 200\text{ MHz}$; $G_S = 2\text{ mS}$; $G_L = 0.5\text{ mS}$ | - | 34 | - | dB | |
| | | $f = 400\text{ MHz}$; $G_S = 2\text{ mS}$; $G_L = 1\text{ mS}$ | - | 30 | - | dB | |
| | | $f = 800\text{ MHz}$; $G_S = 3.3\text{ mS}$; $G_L = 1\text{ mS}$ | - | 26 | - | dB | |
| | | amplifier B; $B_S = B_{S(\text{opt})}$; $B_L = B_{L(\text{opt})}$ | [1] | | | | |
| | | $f = 200\text{ MHz}$; $G_S = 2\text{ mS}$; $G_L = 0.5\text{ mS}$ | - | 34 | - | dB | |
| | | $f = 400\text{ MHz}$; $G_S = 2\text{ mS}$; $G_L = 1\text{ mS}$ | - | 30 | - | dB | |
| | | $f = 800\text{ MHz}$; $G_S = 3.3\text{ mS}$; $G_L = 1\text{ mS}$ | - | 26 | - | dB | |
| NF | noise figure | $f = 11\text{ MHz}$; $G_S = 20\text{ mS}$; $B_S = 0\text{ S}$ | - | - | 5 | dB | |
| | | $f = 400\text{ MHz}$; $Y_S = Y_{S(\text{opt})}$ | - | 1.0 | - | dB | |
| | | $f = 800\text{ MHz}$; $Y_S = Y_{S(\text{opt})}$ | - | 1.5 | - | dB | |
| Xmod | cross modulation | input level for $k = 1\%$ at 40 dB AGC; $f_w = 50\text{ MHz}$; $f_{unw} = 60\text{ MHz}$ | [2] | | | | |
| | | at 0 dB AGC | 90 | 104 | - | $\text{dB}\mu\text{V}$ | |
| | | at 10 dB AGC | - | 100 | - | $\text{dB}\mu\text{V}$ | |
| | | at 20 dB AGC | - | 104 | - | $\text{dB}\mu\text{V}$ | |
| | | at 40 dB AGC | 105 | 107 | - | $\text{dB}\mu\text{V}$ | |


[1] Calculated from S-parameters.

[2] Measured in [Figure 17](#) test circuit.

8.1 Graphs for amplifiers A and B




$V_{DS} = 5$ V; $T_j = 25$ °C.



$V_{G2-S} = 4$ V; $T_j = 25$ °C.


Fig 2. Transfer characteristics; typical values

Fig 3. Output characteristics; typical values




(1) $V_{G2-S} = 4.0$ V.
 (2) $V_{G2-S} = 3.5$ V.
 (3) $V_{G2-S} = 3.0$ V.
 (4) $V_{G2-S} = 2.5$ V.
 (5) $V_{G2-S} = 2.0$ V.
 (6) $V_{G2-S} = 1.5$ V.
 (7) $V_{G2-S} = 1.0$ V.
 $V_{DS} = 5$ V; $T_j = 25$ °C.

Fig 4. Gate1 current as a function of gate1 voltage; typical values




(1) $V_{G2-S} = 4.0$ V.
 (2) $V_{G2-S} = 3.5$ V.
 (3) $V_{G2-S} = 3.0$ V.
 (4) $V_{G2-S} = 2.5$ V.
 (5) $V_{G2-S} = 2.0$ V.
 (6) $V_{G2-S} = 1.5$ V.
 (7) $V_{G2-S} = 1.0$ V.
 $V_{DS} = 5$ V; $T_j = 25$ °C.

Fig 5. Forward transfer admittance as a function of drain current; typical values




$V_{DS} = 5$ V; $V_{G2-S} = 4$ V; $T_j = 25$ °C.

Fig 6. Drain current as a function of gate1 current; typical values



$V_{DS} = 5$ V; $V_{G2-S} = 4$ V; $R_{G1} = 39$ kΩ; $T_j = 25$ °C.


Fig 7. Drain current as a function of gate1 supply voltage (V_{GG}); typical values



- (1) $R_{G1} = 10 \text{ k}\Omega$.
- (2) $R_{G1} = 20 \text{ k}\Omega$.
- (3) $R_{G1} = 40 \text{ k}\Omega$.
- (4) $R_{G1} = 60 \text{ k}\Omega$.
- (5) $R_{G1} = 80 \text{ k}\Omega$.

$V_{G2-S} = 4 \text{ V}$; $T_j = 25 \text{ }^\circ\text{C}$.


Fig 8. Drain current as a function of V_{DS} and V_{GG} ; typical values



- (1) $V_{GG} = 5.0 \text{ V}$.
- (2) $V_{GG} = 4.5 \text{ V}$.
- (3) $V_{GG} = 4.0 \text{ V}$.
- (4) $V_{GG} = 3.5 \text{ V}$.
- (5) $V_{GG} = 3.0 \text{ V}$.


$T_j = 25 \text{ }^\circ\text{C}$; $R_{G1} = 39 \text{ k}\Omega$ (connected to V_{GG}).

Fig 9. Drain current as a function of gate2 voltage; typical values




$V_{DS} = 5$ V; $V_{GG} = 5$ V; nominal $I_D = 19$ mA; $R_{G1} = 39$ k Ω ; $f = 50$ MHz; $T_j = 25$ °C; see [Figure 17](#).

Fig 10. Typical gain reduction as a function of the AGC voltage; typical values




$V_{DS} = 5$ V; $V_{GG} = 5$ V; nominal $V_{G2-S} = 4$ V; $R_{G1} = 39$ k Ω ; $f_w = 50$ MHz; $f_{unw} = 60$ MHz; nominal $I_D = 19$ mA; $T_j = 25$ °C; see [Figure 17](#).

Fig 11. Unwanted voltage for 1 % cross modulation as a function of gain reduction; typical values




$V_{DS} = 5$ V; $V_{GG} = 5$ V; nominal $V_{G2-S} = 4$ V; $R_{G1} = 39$ k Ω ; $f_w = 50$ MHz; nominal $I_D = 19$ mA; $T_j = 25$ °C; see [Figure 17](#).

Fig 12. Typical drain current as a function of gain reduction; typical values




$V_{DS(A)} = 5$ V; $V_{G2-S} = 4$ V; $V_{DS(B)} = 0$ V; $I_{D(A)} = 19$ mA; and vice versa.

Fig 13. Input admittance as a function of frequency; typical values




$V_{DS(A)} = 5$ V; $V_{G2-S} = 4$ V; $V_{DS(B)} = 0$ V; $I_{D(A)} = 19$ mA; and vice versa.

Fig 14. Forward transfer admittance and phase as a function of frequency; typical values



$V_{DS(A)} = 5$ V; $V_{G2-S} = 4$ V; $V_{DS(B)} = 0$ V; $I_{D(A)} = 19$ mA; and vice versa.

Fig 15. Reverse transfer admittance and phase as a function of frequency; typical values



$V_{DS(A)} = 5$ V; $V_{G2-S} = 4$ V; $V_{DS(B)} = 0$ V; $I_{D(A)} = 19$ mA; and vice versa.

Fig 16. Output admittance as a function of frequency; typical values

8.2 Scattering parameters for amplifiers A and B

Table 9. Scattering parameters for amplifiers A and B

$V_{DS(A)} = 5$ V; $V_{G2-S} = 4$ V; $I_{D(A)} = 19$ mA; $V_{DS(B)} = 0$ V; $V_{G1-S(B)} = 0$ V; $T_{amb} = 25$ °C; $Z_0 = 50$ Ω; typical values.

| f (MHz) | s_{11} | | s_{21} | | s_{12} | | s_{22} | |
|---------|-------------------|----------------|-------------------|----------------|-------------------|----------------|-------------------|----------------|
| | Magnitude (ratio) | Angle (degree) |
| 40 | 0.9910 | -4.73 | 2.76 | 175.80 | 0.00074 | 99.46 | 0.9946 | -1.29 |
| 100 | 0.9888 | -9.07 | 2.75 | 171.94 | 0.00150 | 86.12 | 0.9941 | -2.65 |
| 200 | 0.9853 | -18.19 | 2.73 | 163.86 | 0.00292 | 79.56 | 0.9929 | -5.31 |
| 300 | 0.9762 | -27.09 | 2.69 | 155.90 | 0.00420 | 74.12 | 0.9916 | -7.92 |
| 400 | 0.9656 | -35.80 | 2.65 | 148.17 | 0.00540 | 69.71 | 0.9900 | -10.49 |
| 500 | 0.9502 | -44.45 | 2.59 | 140.50 | 0.00634 | 65.32 | 0.9882 | -13.05 |
| 600 | 0.9331 | -52.89 | 2.52 | 132.96 | 0.00709 | 61.01 | 0.9855 | -15.66 |
| 700 | 0.9155 | -61.08 | 2.45 | 125.69 | 0.00751 | 57.66 | 0.9830 | -18.24 |
| 800 | 0.8966 | -69.01 | 2.38 | 118.59 | 0.00782 | 54.58 | 0.9810 | -20.75 |
| 900 | 0.8755 | -76.72 | 2.30 | 111.71 | 0.00792 | 52.37 | 0.9798 | -23.19 |
| 1000 | 0.8550 | -84.10 | 2.22 | 105.07 | 0.00783 | 50.60 | 0.9785 | -25.68 |


8.3 Noise data for amplifiers A and B

Table 10. Noise data for amplifiers A and B

$V_{DS(A)} = 5$ V; $V_{G2-S} = 4$ V; $I_{D(A)} = 19$ mA, $T_{amb} = 25$ °C; typical values.

| f (MHz) | NF_{min} (dB) | Γ_{opt} | | r_n (ratio) |
|---------|-----------------|----------------|----------|---------------|
| | | (ratio) | (degree) | |
| 400 | 1.0 | 0.788 | 28.9 | 0.903 |
| 800 | 1.5 | 0.673 | 58.8 | 0.725 |

9. Test information




001aad926

Fig 17. Cross modulation test setup for one MOSFET

10. Package outline

Plastic surface-mounted package; 6 leads

SOT363



DIMENSIONS (mm are the original dimensions)

| UNIT | A | A_1 max | b_p | c | D | E | e | e_1 | H_E | L_p | Q | v | w | y |
|------|------------|--------------|--------------|--------------|------------|--------------|-----|-------|------------|--------------|--------------|-----|-----|-----|
| mm | 1.1 0.8 | 0.1 | 0.30 0.20 | 0.25 0.10 | 2.2 1.8 | 1.35 1.15 | 1.3 | 0.65 | 2.2 2.0 | 0.45 0.15 | 0.25 0.15 | 0.2 | 0.2 | 0.1 |

| OUTLINE VERSION | REFERENCES | | | | EUROPEAN PROJECTION | ISSUE DATE |
|--------------------|------------|-------|-------|--|------------------------|----------------------|
| | IEC | JEDEC | JEITA | | | |
| SOT363 | | | SC-88 | | | 04-11-08 06-03-16 |

Fig 18. Package outline SOT363

11. Abbreviations

Table 11. Abbreviations

| Acronym | Description |
|---------|---|
| AGC | Automatic Gain Control |
| MOSFET | Metal-Oxide Semiconductor Field-Effect Transistor |
| UHF | Ultra High Frequency |
| VHF | Very High Frequency |

12. Revision history

Table 12. Revision history

| Document ID | Release date | Data sheet status | Change notice | Supersedes |
|-------------|--------------|--------------------|---------------|------------|
| BF1216_1 | 20100429 | Product data sheet | - | - |

13. Legal information

13.1 Data sheet status

| Document status ^{[1][2]} | Product status ^[3] | Definition |
|-----------------------------------|-------------------------------|---|
| Objective [short] data sheet | Development | This document contains data from the objective specification for product development. |
| Preliminary [short] data sheet | Qualification | This document contains data from the preliminary specification. |
| Product [short] data sheet | Production | This document contains the product specification. |

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <http://www.nxp.com>.

13.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on a weakness or default in the customer application/use or the application/use of customer's third party customer(s) (hereinafter both referred to as "Application"). It is customer's sole responsibility to check whether the NXP Semiconductors product is suitable and fit for the Application planned. Customer has to do all necessary testing for the Application in order to avoid a default of the Application and the product. NXP Semiconductors does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nxp.com/profile/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Non-automotive qualified products — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

13.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any

liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

13.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

14. Contact information

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: salesaddresses@nxp.com

15. Contents

| | | |
|-----------|--|-----------|
| 1 | Product profile | 1 |
| 1.1 | General description | 1 |
| 1.2 | Features and benefits | 1 |
| 1.3 | Applications | 1 |
| 1.4 | Quick reference data | 2 |
| 2 | Pinning information | 2 |
| 3 | Ordering information | 2 |
| 4 | Marking | 3 |
| 5 | Limiting values | 3 |
| 6 | Thermal characteristics | 4 |
| 7 | Static characteristics | 4 |
| 8 | Dynamic characteristics | 5 |
| 8.1 | Graphs for amplifiers A and B | 6 |
| 8.2 | Scattering parameters for amplifiers A and B | 11 |
| 8.3 | Noise data for amplifiers A and B | 11 |
| 9 | Test information | 12 |
| 10 | Package outline | 13 |
| 11 | Abbreviations | 14 |
| 12 | Revision history | 14 |
| 13 | Legal information | 15 |
| 13.1 | Data sheet status | 15 |
| 13.2 | Definitions | 15 |
| 13.3 | Disclaimers | 15 |
| 13.4 | Trademarks | 16 |
| 14 | Contact information | 16 |
| 15 | Contents | 17 |

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP B.V. 2010.

All rights reserved.

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 29 April 2010

Document identifier: BF1216_1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NXP:](#)

[BF1216,115](#)