


General Purpose Plastic Rectifier



PRIMARY CHARACTERISTICS									
I _{F(AV)} 1.0 A									
V _{RRM}	50 V to 1000 V								
I _{FSM} (8.3 ms sine-wave)	30 A								
I _{FSM} (square wave t _p = 1 ms)	45 A								
V _F	1.1 V								
I _R	5.0 μA								
T _J max.	150 °C								

FEATURES





• High forward surge capability

• Solder dip 275 °C max. 10 s, per JESD 22-B106

• Compliant to RoHS Directive 2002/95/EC and in accordance to WEEE 2002/96/EC





ROHS

TYPICAL APPLICATIONS

For use in general purpose rectification of power supplies, inverters, converters and freewheeling diodes application.

Note

• These devices are not AEC-Q101 qualified.

MECHANICAL DATA

Case: DO-204AL, molded epoxy body

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS compliant, commercial grade

Terminals: Matte tin plated leads, solderable per

J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test **Polarity:** Color band denotes cathode end

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)										
PARAMETER		SYMBOL	1N4001	1N4002	1N4003	1N4004	1N4005	1N4006	1N4007	UNIT
Maximum repetitive peak reverse voltage		V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage		V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage		V_{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified 0.375" (9.5 mm) lead length at $T_A = 7$	I _{F(AV)}	1.0							А	
Peak forward surge current 8.3 ms s sine-wave superimposed on rated lo	I _{FSM}	30						А		
Non-repetitive peak forward	t _p = 1 ms		45							
surge current square waveform	t _p = 2 ms	I _{FSM}	35							
$T_A = 25$ °C (fig. 3) $t_p = 5 \text{ ms}$			30							
Maximum full load reverse current, full cycle average 0.375" (9.5 mm) lead length $T_L=75\ ^{\circ}C$		I _{R(AV)}	30							μΑ
Rating for fusing (t < 8.3 ms)		I ² t ⁽¹⁾	3.7							A ² s
Operating junction and storage temperature range		T _J , T _{STG}	- 50 to + 150						°C	

Note

(1) For device using on bridge rectifier appliaction



ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)											
PARAMETER	TEST	CONDITIONS	SYMBOL	1N4001	1N4002	1N4003	1N4004	1N4005	1N4006	1N4007	UNIT
Maximum instantaneous forward voltage	1.0 /	A	V _F	1.1					٧		
Maximum DC reverse current		T _A = 25 °C	I_	5.0					μA		
at rated DC blocking voltage		T _A = 125 °C	IR			50				μΑ	
Typical junction capacitance	4.0 \	/, 1 MHz	z C _J		15						pF

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)									
PARAMETER	SYMBOL 1N4001 1N4002 1N4003 1N4004 1N4005 1N4006 1N4007 UN						UNIT		
Typical thormal registance	R _{0JA} (1)	50							°C/W
Typical thermal resistance	R _{θJL} ⁽¹⁾	25							C/VV

Note

⁽¹⁾ Thermal resistance from junction to ambient at 0.375" (9.5 mm) lead length, PCB mounted

ORDERING INFORMATION (Example)									
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE					
1N4004-E3/54	0.33	54	5500	13" diameter paper tape and reel					
1N4004-E3/73	0.33	73	3000	Ammo pack packaging					

RATINGS AND CHARACTERISTICS CURVES

(T_A = 25 °C unless otherwise noted)




Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-repetitive Peak Forward Surge Current






Fig. 3 - Non-Repetitive Peak Forward Surge Current




Fig. 4 - Typical Instantaneous Forward Characteristics




Fig. 5 - Typical Reverse Characteristics




Fig. 6 - Typical Junction Capacitance





Fig. 7 - Typical Transient Thermal Impedance



PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Note

• Lead diameter is $\frac{0.026 (0.66)}{0.023 (0.58)}$ for suffix "E" part numbers



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.