



July 2015

Multilayer Triplexer

For 1560-1606MHz / 2400-2500MHz / 4900-5950MHz

TPX205950MT-7004A1

2.0x1.25mm [EIA 0805]*

* Dimensions Code JIS[EIA]


Multilayer Triplexer

Conformity to RoHS Directive


For 1560-1606MHz / 2400-2500MHz / 4900-5950MHz

TPX205950MT-7004A1**■ SHAPES AND DIMENSIONS**

[Top view]




[Bottom view]



Terminal functions

1	GND
2	Common port
3	GND
4	High (5.0G) band port
5	GND
6	Middle (2.4G) band port
7	GND
8	Low (1.5G) band port

Dimensions in mm

■ EVALUATION BOARD

Dimensions in mm

Line width should be designed to match 50Ω characteristic impedance,
depending on PCB material and thickness.

○ RoHS Directive Compliant Product: See the following for more details related to RoHS Directive compliant products. <http://product.tdk.com/en/environment/rohs/>

- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.

TPX205950MT-7004A1

■ ELECTRICAL CHARACTERISTICS

□ LOW(1.5G)-BAND

Item	Frequency Range (MHz)	Min.	Typ.	Max.
Insertion Loss (dB)	1560 to 1606	—	0.43	0.65
	1560 to 1606	—	—	0.80 (-40 to +85°C)
Return Loss (dB)	1560 to 1606	9.54	22	—
Attenuation (dB)	2400 to 2500	13	22	—
	4900 to 5950	15	20	—
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

□ MIDDLE(2.4G)-BAND

Item	Frequency Range (MHz)	Min.	Typ.	Max.
Insertion Loss (dB)	2400 to 2500	—	0.47	0.80
	2400 to 2500	—	—	1.00 (-40 to +85°C)
Return Loss (dB)	2400 to 2500	9.54	17	—
Attenuation (dB)	1560 to 1606	13	17	—
	4900 to 5950	15	21	—
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

□ HIGH(5.0G)-BAND

Item	Frequency Range (MHz)	Min.	Typ.	Max.
Insertion Loss (dB)	4900 to 5950	—	0.59	0.80
	4900 to 5950	—	—	1.00 (-40 to +85°C)
Return Loss (dB)	4900 to 5950	9.54	19	—
	1560 to 1606	20	26	—
Attenuation (dB)	2400 to 2500	25	32	—
	9800 to 11900	20	32	—
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

□ COMMON

Item	Frequency Range (MHz)	Min.	Typ.	Max.
Power Handling (W)		—	—	1

■ TEMPERATURE RANGE

Operating temperature (°C)	Storage temperature (°C)
-40 to +85	-40 to +85


- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.

TPX205950MT-7004A1

■ FREQUENCY CHARACTERISTICS


□ LOW-BAND

Insertion Loss




□ MIDDLE-BAND


Insertion Loss




Return Loss




Return Loss



Attenuation



Attenuation




- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.

TPX205950MT-7004A1


■ FREQUENCY CHARACTERISTICS

□ HIGH-BAND


Insertion Loss



Return Loss



Attenuation




- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.

TPX205950MT-7004A1


■ FREQUENCY CHARACTERISTICS

□ COMMON


Return Loss




Isolation (Low-Mid)



Isolation (Low-High)




Isolation (Mid-High)



- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.

■ RECOMMENDED REFLOW PROFILE



Preheating			Soldering		Peak	
			Critical zone (T3 to T4)			
Temp.	Time		Temp.	Time	Temp.	Time
T_1 150°C	T_2 200°C	t_1 60 to 120sec	T_3 217°C	t_2 60 to 120sec	T_4 240 to 260°C	t_3^* 30sec max.

* t_3 : Time within 5°C of actual peak temperature

The maximum number of reflow is 3.

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

REMINDERS

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

(1) Aerospace/Aviation equipment	(8) Public information-processing equipment
(2) Transportation equipment (cars, electric trains, ships, etc.)	(9) Military equipment
(3) Medical equipment	(10) Electric heating apparatus, burning equipment
(4) Power-generation control equipment	(11) Disaster prevention/crime prevention equipment
(5) Atomic energy-related equipment	(12) Safety equipment
(6) Seabed equipment	(13) Other applications that are not considered general-purpose applications
(7) Transportation control equipment	

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/equipment or providing backup circuits, etc., to ensure higher safety.

- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.