

# 2N6667, 2N6668

## Darlington Silicon Power Transistors

Designed for general-purpose amplifier and low speed switching applications.

- High DC Current Gain –  
 $h_{FE} = 3500$  (Typ) @  $I_C = 4.0$  Adc
- Collector-Emitter Sustaining Voltage – @ 200 mAdc  
 $V_{CE(sus)} = 60$  Vdc (Min) – 2N6667  
 $= 80$  Vdc (Min) – 2N6668
- Low Collector-Emitter Saturation Voltage –  
 $V_{CE(sat)} = 2.0$  Vdc (Max) @  $I_C = 5.0$  Adc
- Monolithic Construction with Built-In Base-Emitter Shunt Resistors
- TO-220AB Compact Package
- Complementary to 2N6387, 2N6388
- These Devices are Pb-Free and are RoHS Compliant\*





Figure 1. Darlington Schematic



**ON Semiconductor®**


[www.onsemi.com](http://www.onsemi.com)

**PNP SILICON  
DARLINGTON  
POWER TRANSISTORS  
10 A, 60–80 V, 65 W**



TO-220  
CASE 221A  
STYLE 1

### MARKING DIAGRAM



x = 7 or 8  
A = Assembly Location  
Y = Year  
WW = Work Week  
G = Pb-Free Package

### ORDERING INFORMATION

| Device  | Package             | Shipping      |
|---------|---------------------|---------------|
| 2N6667G | TO-220<br>(Pb-Free) | 50 Units/Rail |
| 2N6668G | TO-220<br>(Pb-Free) | 50 Units/Rail |

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

# 2N6667, 2N6668

## MAXIMUM RATINGS (Note 1)

| Rating                                                                                 | Symbol         | 2N6667       | 2N6668 | Unit                     |
|----------------------------------------------------------------------------------------|----------------|--------------|--------|--------------------------|
| Collector-Emitter Voltage                                                              | $V_{CEO}$      | 60           | 80     | Vdc                      |
| Collector-Base Voltage                                                                 | $V_{CB}$       | 60           | 80     | Vdc                      |
| Emitter-Base Voltage                                                                   | $V_{EB}$       | 5.0          |        | Vdc                      |
| Collector Current – Continuous<br>– Peak                                               | $I_C$          | 10<br>15     |        | Adc                      |
| Base Current                                                                           | $I_B$          | 250          |        | mAdc                     |
| Total Device Dissipation @ $T_C = 25^\circ\text{C}$<br>Derate above $25^\circ\text{C}$ | $P_D$          | 65<br>0.52   |        | W<br>W/ $^\circ\text{C}$ |
| Total Device Dissipation @ $T_A = 25^\circ\text{C}$<br>Derate above $25^\circ\text{C}$ | $P_D$          | 2.0<br>0.016 |        | W<br>W/ $^\circ\text{C}$ |
| Operating and Storage Junction Temperature Range                                       | $T_J, T_{stg}$ | –65 to +150  |        | $^\circ\text{C}$         |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

## THERMAL CHARACTERISTICS

| Characteristic                          | Symbol          | Max  | Unit               |
|-----------------------------------------|-----------------|------|--------------------|
| Thermal Resistance, Junction to Case    | $R_{\theta JC}$ | 1.92 | $^\circ\text{C/W}$ |
| Thermal Resistance, Junction to Ambient | $R_{\theta JA}$ | 62.5 | $^\circ\text{C/W}$ |

## ELECTRICAL CHARACTERISTICS (Note 1) ( $T_C = 25^\circ\text{C}$ unless otherwise noted)

| Characteristic | Symbol | Min | Max | Unit |
|----------------|--------|-----|-----|------|
|----------------|--------|-----|-----|------|

### OFF CHARACTERISTICS

|                                                                                                                                                                                                                                                                                                                                                      |                                      |                |                  |                          |                         |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------|----------------|------------------|--------------------------|-------------------------|
| Collector-Emitter Sustaining Voltage (Note 2)<br>( $I_C = 200\text{ mAdc}$ , $I_B = 0$ )                                                                                                                                                                                                                                                             | 2N6667<br>2N6668                     | $V_{CEO(sus)}$ | 60<br>80         | –<br>–                   | Vdc                     |
| Collector Cutoff Current ( $V_{CE} = 60\text{ Vdc}$ , $I_B = 0$ )<br>( $V_{CE} = 80\text{ Vdc}$ , $I_B = 0$ )                                                                                                                                                                                                                                        | 2N6667<br>2N6668                     | $I_{CEO}$      | –<br>–           | 1.0<br>1.0               | mAdc                    |
| Collector Cutoff Current<br>( $V_{CE} = 60\text{ Vdc}$ , $V_{EB(off)} = 1.5\text{ Vdc}$ )<br>( $V_{CE} = 80\text{ Vdc}$ , $V_{EB(off)} = 1.5\text{ Vdc}$ )<br>( $V_{CE} = 60\text{ Vdc}$ , $V_{EB(off)} = 1.5\text{ Vdc}$ , $T_C = 125^\circ\text{C}$ )<br>( $V_{CE} = 80\text{ Vdc}$ , $V_{EB(off)} = 1.5\text{ Vdc}$ , $T_C = 125^\circ\text{C}$ ) | 2N6667<br>2N6668<br>2N6667<br>2N6668 | $I_{CEX}$      | –<br>–<br>–<br>– | 300<br>300<br>3.0<br>3.0 | $\mu\text{Adc}$<br>mAdc |
| Emitter Cutoff Current ( $V_{BE} = 5.0\text{ Vdc}$ , $I_C = 0$ )                                                                                                                                                                                                                                                                                     |                                      | $I_{EBO}$      | –                | 5.0                      | mAdc                    |

### ON CHARACTERISTICS (Note 1)

|                                                                                                                                                 |               |             |            |     |
|-------------------------------------------------------------------------------------------------------------------------------------------------|---------------|-------------|------------|-----|
| DC Current Gain ( $I_C = 5.0\text{ Adc}$ , $V_{CE} = 3.0\text{ Vdc}$ )<br>( $I_C = 10\text{ Adc}$ , $V_{CE} = 3.0\text{ Vdc}$ )                 | $h_{FE}$      | 1000<br>100 | 20000<br>– | –   |
| Collector-Emitter Saturation Voltage ( $I_C = 5.0\text{ Adc}$ , $I_B = 0.01\text{ Adc}$ )<br>( $I_C = 10\text{ Adc}$ , $I_B = 0.1\text{ Adc}$ ) | $V_{CE(sat)}$ | –<br>–      | 2.0<br>3.0 | Vdc |
| Base-Emitter Saturation Voltage ( $I_C = 5.0\text{ Adc}$ , $I_B = 0.01\text{ Adc}$ )<br>( $I_C = 10\text{ Adc}$ , $I_B = 0.1\text{ Adc}$ )      | $V_{BE(sat)}$ | –<br>–      | 2.8<br>4.5 | Vdc |

### DYNAMIC CHARACTERISTICS

|                                                                                                                       |            |      |     |    |
|-----------------------------------------------------------------------------------------------------------------------|------------|------|-----|----|
| Current Gain – Bandwidth Product ( $I_C = 1.0\text{ Adc}$ , $V_{CE} = 5.0\text{ Vdc}$ , $f_{test} = 1.0\text{ MHz}$ ) | $ h_{fe} $ | 20   | –   | –  |
| Output Capacitance ( $V_{CB} = 10\text{ Vdc}$ , $I_E = 0$ , $f = 1.0\text{ MHz}$ )                                    | $C_{ob}$   | –    | 200 | pF |
| Small-Signal Current Gain ( $I_C = 1.0\text{ Adc}$ , $V_{CE} = 5.0\text{ Vdc}$ , $f = 1.0\text{ kHz}$ )               | $h_{fe}$   | 1000 | –   | –  |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

1. Indicates JEDEC Registered Data.
2. Pulse Test: Pulse Width  $\leq 300\text{ }\mu\text{s}$ , Duty Cycle  $\leq 2\%$ .

## 2N6667, 2N6668

$R_B$  &  $R_C$  VARIED TO OBTAIN DESIRED CURRENT LEVELS

$D_1$ , MUST BE FAST RECOVERY TYPES e.g.,

1N5825 USED ABOVE  $I_B \approx 100$  mA

MSD6100 USED BELOW  $I_B \approx 100$  mA

FOR  $t_d$  AND  $t_r$ ,  $D_1$  IS DISCONNECTED AND  $V_2 = 0$

$t_r, t_f \leq 10$  ns

DUTY CYCLE = 1.0%




Figure 2. Switching Times Test Circuit




Figure 3. Power Derating




Figure 4. Typical Switching Times




Figure 5. Thermal Response




Figure 6. Maximum Safe Operating Area

There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown. Safe operating area curves indicate  $I_C - V_{CE}$  limits of the transistor that must be observed for reliable operation; i.e., the transistor must not be subjected to greater dissipation than the curves indicate.

The data of Figure 6 is based on  $T_{J(pk)} = 150^\circ\text{C}$ ;  $T_C$  is variable depending on conditions. Second breakdown pulse limits are valid for duty cycles to 10% provided  $T_{J(pk)} < 150^\circ\text{C}$ .  $T_{J(pk)}$  may be calculated from the data in Figure 5. At high case temperatures, thermal limitations will reduce the power that can be handled to values less than the limitations imposed by second breakdown.




Figure 7. Typical Small-Signal Current Gain




Figure 8. Typical Capacitance




Figure 9. Typical DC Current Gain




Figure 10. Typical Collector Saturation Region

# 2N6667, 2N6668




Figure 11. Typical "On" Voltages




Figure 12. Typical Temperature Coefficients




Figure 13. Typical Collector Cut-Off Region

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)