



120mm sq.**San Ace 120**25mm thick (G type), 38mm thick (GV type)
38mm thick (G type), 38mm thick (SG type)**General Specifications** With a pulse sensor

- Material.....Frame: Aluminum, Impeller:Plastics (Flammability: UL94V-1)
- Life ExpectancyVaries for each model (L10:Survival rate:90% at 60°C ,
rated voltage, and continuously run in a free air state)
- Lead Wire⊕red ⊖black or blue (Sensor) yellow
- Storage Temperature ...-30°C to +70°C (Non-condensing)

120×120×38mm [Mass : 400g]**SG type** **Specifications**


Model No.	Rated Voltage [V]	Operating Voltage Range [V]	Rated Current [A]	Rated Input [W]	Rated Speed [min ⁻¹]	Air Flow		Static Pressure		SPL [dB(A)]	Operating Temperature [°C]	Life Expectancy [h]
						[m ³ /min]	[CFM]	[Pa]	[inchH ₂ O]			
9SG1224H101	24	20.4 to 27.6	0.46	11.04	3,400	4.02	141.9	126	0.5	48	-10 to +70	40,000

Dimensions (Unit : mm)**Reference dimension of mounting holes and vent opening (Unit : mm)**


Options (Unit : mm)

Finger guards


Model : 109-019C Surface treatment : Nickel-chrome plating (silver) Color : 109-019H : Cation electropainting (black)



Model : 109-019E Surface treatment : Nickel-chrome plating (silver) Color : 109-019K : Cation electropainting (black)



Air Flow - Static Pressure Characteristics



9SG1224H101