



MATERIAL NUMBER	ENGINEERING P/N	WIRE SIZE	INSULATION COLOR	I.D. MIN.	MWID*	"D" MAX.	"L" MAX.
192060012	D-655X	8	RED	.165 / 4.19	.33 / 8.3 (A)	.398 / 10.11	.07 / 27.2
192060013	E-66 IX	6	BLUE	.230 / 5.84	.44 / 11.1	.467 / 11.86	.30 / 33.0
192060015	F-655X	4	YELLOW	.277 / 7.03	.60 / 15.2	.537 / 13.64	.39 / 35.3

(A)



NOTES:

1. MATERIALS:
 - SPLICER: MATTE-TIN PLATED COPPER
 - INSULATION: PVC
2. MWID = MAXIMUM WIRE INSULATION DIAMETER
3. PARTS ARE ROHS COMPLIANT.

REDRAWN FROM DOC CD-21100

REDRAWN, D MWID EC NO: WNA2011-0558 DRWNR: THRODAHL 2011/05/12 CHKD: JMACNEIL 2011/05/12 APPR: JMACNEIL 2011/05/12		QUALITY SYMBOLS ▼=0 △=0	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE IN/MM (A)		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
REV	REV			mm	INCH			
		4 PLACES	± ---	± ---	CHECKED BY RWD	DATE 1996/04/15		
		3 PLACES	± ---	± .005	APPROVED BY JMACNEIL	DATE 2011/05/12		
		2 PLACES	± 0.13	± .01	MATERIAL NO.			
		1 PLACE	± 0.25	± ---	SEE CHART	DOCUMENT NO.	SD-19206-001	
		ANGULAR ± ---°				SIZE	A THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex](#):

[19206-0012](#)