

CMR5U-02 CMR5U-06
CMR5U-04 CMR5U-08

**SURFACE MOUNT SILICON
ULTRA FAST
RECOVERY RECTIFIERS
5.0 AMP, 200 THRU 800 VOLT**



SMC CASE



www.centralemi.com

DESCRIPTION:

The CENTRAL SEMICONDUCTOR CMR5U-02 series 5.0 Amp surface mount silicon rectifiers are highly reliable components designed for use in all types of commercial, industrial, entertainment, computer, and automotive applications. To order devices on 16mm Tape and Reel (3000/13" Reel), add TR13 suffix to part number.

MARKING CODE: SEE MARKING CODE TABLE ON FOLLOWING PAGE

FEATURES:

- High current density: 65% Increase compared to CMR3U Series
- High peak forward surge current (I_{FSM})
- Low forward voltage drop (V_F)
- Glass passivated chip
- "C" bend construction provides strain relief when mounted on PC board

MAXIMUM RATINGS: ($T_A=25^\circ\text{C}$ unless otherwise noted)

	SYMBOL	CMR5U-02	CMR5U-04	CMR5U-06	CMR5U-08	UNITS
Peak Repetitive Reverse Voltage	V_{RRM}	200	400	600	800	V
DC Blocking Voltage	V_R	200	400	600	800	V
RMS Reverse Voltage	$V_R(RMS)$	140	280	420	560	V
Average Forward Current ($T_A=55^\circ\text{C}$)	I_O			5.0		A
Peak Forward Surge Current, $t_p=8.3\text{ms}$	I_{FSM}			175		A
Operating and Storage Junction Temperature	T_J, T_{stg}			-65 to +150		$^\circ\text{C}$
Thermal Resistance	Θ_{JL}			10		$^\circ\text{C/W}$

ELECTRICAL CHARACTERISTICS: ($T_A=25^\circ\text{C}$) unless otherwise noted)

SYMBOL	TEST CONDITIONS	MAX	UNITS
I_R	$V_R=\text{Rated } V_{RRM}$	10	μA
I_R	$V_R=\text{Rated } V_{RRM}, T_A=100^\circ\text{C}$	100	μA
V_F	$I_F=5.0\text{A}, (\text{CMR5U-02})$	1.0	V
V_F	$I_F=5.0\text{A}, (\text{CMR5U-04})$	1.3	V
V_F	$I_F=5.0\text{A}, (\text{CMR5U-06, -08})$	1.7	V
t_{rr}	$I_F=0.5\text{A}, I_R=1.0\text{A}, I_{rr}=0.25\text{A} (\text{CMR5U-02, -04})$	50	ns
t_{rr}	$I_F=0.5\text{A}, I_R=1.0\text{A}, I_{rr}=0.25\text{A} (\text{CMR5U-06, -08})$	100	ns


R3 (11-September 2013)

CMR5U-02 CMR5U-06
CMR5U-04 CMR5U-08

**SURFACE MOUNT SILICON
ULTRA FAST
RECOVERY RECTIFIERS
5.0 AMP, 200 THRU 800 VOLT**



SMC CASE - MECHANICAL OUTLINE



DEVICE	MARKING CODE
CMR5U-02	CU502
CMR5U-04	CU504
CMR5U-06	CU506
CMR5U-08	CU508

DIMENSIONS				
SYMBOL	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.030	0.060	0.76	1.52
B	0.002	0.008	0.05	0.20
C	0.305	0.320	7.75	8.13
D	0.006	0.012	0.15	0.31
E	0.079	0.103	2.00	2.62
F	0.260	0.280	6.60	7.11
G	0.108	0.128	2.75	3.25
H	0.220	0.245	5.59	6.22

SMC (REV: R2)

R3 (11-September 2013)