








REV.	DATE	ECR NO.	DESCRIPTION
NC	09/23/10	XXXXXX	INITIAL RELEASE



RECOMMENDED
MOUNTING HOLE



RECOMMENDED
CABLE STRIPPING DIM'S



1. CRIMPED FERRULE HEX CRIMP SIZE .213"
2. CRIMPED CONTACT PIN HEX CRIMP SIZE .068"
3. MAX. PANEL THICKNESS=3.5mm

9	FERRULE	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex				
8	CONTACT PIN	BRASS	GOLD	1		DRAWN	M.ZHANG	09/23/10						
7	HEX NUT	BRASS	NICKEL	1		CHECKED								
6	LOCK WASHER	BRASS	NICKEL	1		ISSUED			PART DESCRIPTION BNC REVERSE BULKHEAD CRIMP JACK (FOR RG-55/U,142A/U,223/U,400/U CABLE)					
5	GASKET	RUBBER	RED	1		SHEET	1 OF 1							
4	BARREL	BRASS	NICKEL	1	DO NOT SCALE DRAWING			PART NO. 112505RP						
3	INSULATOR	PTFE	NATURAL	1		CAD FILE								
2	BODY	BRASS	NICKEL	1		C:/CONNEX/112505RP.DWG		DWG. NO. 112505RP.DWG			REV. B	SIZE A	SCALE NA	
1	HOUSING	BRASS	NICKEL	1										
DESCRIPTION		MATERIAL	FINISH	QTY										