


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


D	PANDUIT PART NUMBER	PACKAGE QUANTITY	MINIMUM BUNDLE DIAMETER	MAXIMUM BUNDLE DIAMETER	LENGTH = "L" ±.2 [5]
	MLT2.7WH-LP316	50	2.0" [51]	2.7" [69]	10.2" [259]
	MLT4WH-LP316	50	2.0" [51]	4.0" [102]	14.3" [362]
	MLT6WH-LP316	50	2.0" [51]	6.0" [152]	20.5" [521]
	MLT8WH-LP316	50	2.0" [51]	8.0" [203]	26.8" [679]
	MLT10WH-LP316	50	2.0" [51]	10.0" [203]	33.0" [838]



SECTION "A-A"
4X SCALE

FULLY ROUNDED
EDGES ALONG
STRAP BODY

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
05A	3/13	JAMB	MIM	RGRO	ORIG CAD FILE SPEC WAS S41123-04. UPDATED DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01037
04	3/07	JAMB	SKB	---	REMOVED PANDUIT PART NO. MLT2.7WH-TL316, MLT4WH-TL316 & MLT6WH-TL316 PACKAGE QTY 250	SS00338
03	11/06	JAMB	DPN	---	ADDED PANDUIT PART NO. MLT2.7WH-TL316, MLT4WH-TL316 & MLT6WH-TL316 PACKAGE QTY 250	SS00281
02	9/04	JAMB	DPN	JJB	REMOVED "AISI NO. 1 FULL RADIUSED" & REPLACED W/ "FULLY ROUNDED". ADDED "REF" TO DIM D mm was [50]	12052
01	10/03	BRH	DPN	JJB	ADDED ST3MT TO APPLICATION TOOL NOTE	11162

TITLE				
WAVE-TY HEAVY SERIES 316 STAINLESS STEEL				
CUSTOMER DRAWING				
ITEM REVISION NAME			PANDUIT	
N41123BS/05				
DATASET FILE NAME			MATERIAL:	
N41123BS/05				
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			316 STAINLESS STEEL	
.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °				
			DRAWING NUMBER: N41123BS_DC	
THIRD ANGLE PROJECTION				
DRAWN BY	DATE	CHK	SCALE	SIZE
JAMB	10/03	DPN	2:1	A
			SHT 1 OF 1	