



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	MAXIMUM BUNDLE DIAMETER	PACKAGE QUANTITY	LENGTH = "L" ±.3 [7]	
MLT2.7WLH-LP	2.7" [69]	50	10.2" [259]	(A)
MLT4WLH-LP	4" [102]	50	14.3" [362]	
MLT6WLH-LP	6" [152]	50	20.5" [521]	
MLT8WLH-LP	8" [203]	50	26.8" [679]	(B)




NOTES:

1. APPLICATION TOOLS - PPTMT, GS4MT, ST2MT, ST3MT, AND HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 250 LBS. (1112 NEWTONS) WHEN TESTED ON A 3" MANDREL.
PART NO. MLT2.7WLH-LP TESTED ON A 1 1/2" MANDREL.
3. [] DENOTES DIMENSION IN MILLIMETERS.
4. TOLERANCES: .XXX = ±.010 [.25]
.XX = ±.02 [.5]
.X = ±.03 [.8]
ANGLES = ±2°
5. MATERIAL: 304 STAINLESS STEEL



SECTION A - A

TITLE					
WAVE-TY LIGHT-HEAVY					
CUSTOMER DRAWING					
ITEM REVISION NAME		N41137BS/04			
DATASET FILE NAME		N41137BS/04			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xx ± .01 [.25] .xxx ± .005 [.127] ANGLES ± 5 °  THIRD ANGLE PROJECTION				MATERIAL:	
				304 STAINLESS STEEL	
				DRAWING NUMBER:	
				N41137BS_DC	
DRAWN BY	DATE	CHK	SCALE	SIZE	
JAMB	03/03	DPN	2:1	SHT 1 OF 1	
				A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	03/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO. ORIG CAD FILE SPEC WAS S41137_03	SSECN01042
03	08/04	JAMB	DPN	JJB	(D) REMOVED "AISI NO. 1 FULL RADIUSED" AND REPLACED WITH "FULLY ROUNDED" (E) ADDED "REF" TO DIMENSIONS	11907
02	10/03	BRH	DPN	JJB	(C) ADDED ST3MT TO APPLICATION TOOL NOTE	11162
01	06/03	JAMB	DPN	JJB	(A) TOLERANCE WAS ±.2 [5] (B) LGTH [mm] WAS [681]	10568
00	03/03	JAMB	DPN	JJB	DRAWING RELEASED	10563