

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191180090

Status:

Active

Description:


Krimptite™ Flanged Spade Tongue Terminal for 10-12 AWG Wire, Stud Size 10, Length 19.56mm (.7.70"), Mylar Tape Carrier

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Ring and Spade Terminals
Series	19118
Mil-Spec	N/A
Product Name	Krimptite™
Type	Spade
Physical	
Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Packaging Type	Adhesive Tape on Reel
Stud Size	10 (M5)
Wire Size AWG	10, 12
Wire Size mm²	4.00 - 6.00
Electrical	
CSA	LR18689
UL	E32244
Material Info	
Old Part Number	C-117-10T
Reference - Drawing Numbers	
Sales Drawing	SD-19118-002



Series
image - Reference only

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19118Series

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
ATP Perishable Tool Kit, Used in ATP Presses that Process Product on Tape	0190270088
Mini-Mac™ Applicator	0638851000

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION