




Ø.180x.040DP(3) 1.062 [26.97] Ø.090 [Ø2.29] Throu. (3)

Date	SYM	REVISION RECORD	AUTH	DR.	CK.
12/06/13	C	Dim. 2.14 was 2.15. Dim. .67 was .589. Added Dim. .26	T.B.	B.S.	
6/13/14	D	Updated to ROHS 2 Compliant	T.B.	B.S.	





PCB LAYOUT



NOTE:
ROHS 2 COMPLIANT

MOUNTING INSTRUCTION:
USE 2-56 MACHINE SCREWS OR EYELETS 0.089" OD
BY 0.15" FLANGE STIMPSON GS-3 SERIES OR EQUIVALENT.
ALSO ADHESIVES AND DOUBLE SIDED TAPES WORK WELL.



Tolerance (Except as noted)	<div>Memory Protection Devices, Inc</div> <div>200 Broad Hollow Road, Farmingdale, New York 11735</div>		
decimal		Scale	Drawn By T.S.
±.5 (.020)		2=1	Approved By T.B.
Fractional	Title BH9VPC ASSEMBLY		
± .8 (.030)			
Angular	Date	Drawing Number	
± 3°	12/06/13	BH9VPC	

TERMINALS	PC TERMINALS	TIN PLATED STEEL
WASHER	INSULATOR	RUBBER
HOLDER	HOLDER UL94V-0, FILE No. E56070 (S)	HIGH IMPACT ABS BLACK, UL940-0
CONTACTS	BRASS SNAPS	NICKEL PLATED BRASS
PART	DESCRIPTION	MATERIAL