

**HSS-HF 1/4 4.2-5.8/50Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration



The heat-shrinkable TwinMark sleeve is printable on 2 sides and can be used for marking and insulating conductors and cables between 1.2 and 24 mm in diameter. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**Advantages:**

- Application in extremely confined spaces
- Printing on 2 sides for better legibility
- Printed sleeves on a continuous backing
- Can be shrunk with conventional hot-air guns

TwinMark HSS-HF, halogen-free variant

Delivered form: reel

**General ordering data**

|                    |                                                                                  |
|--------------------|----------------------------------------------------------------------------------|
| Type               | HSS-HF 1/4 4.2-5.8/50Y                                                           |
| Order No.          | <a href="#">1961920000</a>                                                       |
| Version            | Conductor and cable markers, 4.2 - 5.8 mm, 50.8 x 11.3 mm, yellow                |
| GTIN (EAN)         | 4032248642618                                                                    |
| Qty.               | 2,500 pc(s).                                                                     |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a> <a href="#">1140490000</a> |

**HSS-HF 1/4 4.2-5.8/50Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 11.3 mm | Width (inches)  | 0.445 inch |
| Height     | 50.8 mm | Height (inches) | 2 inch     |
| Depth      | 0.77 mm | Depth (inches)  | 0.03 inch  |
| Net weight | 1.02 g  |                 |            |

**General data**

|                             |              |                                              |                |
|-----------------------------|--------------|----------------------------------------------|----------------|
| Colour                      | yellow       | Halogen                                      | No             |
| Material                    | Polyolefine  | Material colour according to resistance code | 4              |
| Operating temperature range | -55...105 °C | Recommended industries                       | Transportation |
| Type of printing            | neutral      | Width                                        | 11.3 mm        |

**Conductor and cable markers**

|                               |                   |                                   |                    |
|-------------------------------|-------------------|-----------------------------------|--------------------|
| Conductor O.D.                | 4.2 - 5.8 mm      | Conductor O.D., max.              | 5.8 mm             |
| Conductor O.D., min.          | 4.2 mm            | Conductor cross-section, max.     | 10 mm <sup>2</sup> |
| Conductor cross-section, min. | 4 mm <sup>2</sup> | Halogen                           | No                 |
| Rate of shrinkage             | 2:1               | Recommended shrinking temperature | 90 °C              |

**Classifications**

|             |             |            |             |
|-------------|-------------|------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0   | EC001530    |
| eClass 9.0  | 27-40-04-01 | eClass 9.1 | 27-40-04-01 |
| eClass 10.0 | 27-40-04-01 | UNSPSC     | 30-21-18-01 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                                             |                                                                                                                                               |
|---------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">NFX 70-100-1 2006 + NF X 70-100-2 2006</a><br><a href="#">BS EN 45545-2 2013+A1 2015</a><br><a href="#">BS EN ISO 4589-2 1999</a> |
| Engineering Data                            | <a href="#">EPLAN, WSCAD, Zuken E3,S</a>                                                                                                      |
| Engineering Data                            | <a href="#">STEP</a>                                                                                                                          |
| Software                                    | <a href="#">M-Print PRO configuration file</a>                                                                                                |

## HSS-HF 1/4 4.2-5.8/50Y

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

