

TT-UK5/110AC

Order No.: 2794770

The illustration shows version TT-UK5- 24 DC

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2794770>

Modular terminal block with surge voltage fine protection between clamping connector and DIN rail, nominal voltage: 110 V AC, for mounting on NS 32 or NS 35/7.5, terminal width: 6.2 mm, terminal height: 47 mm

Commercial data

GTIN (EAN)	 4 017918 072940
sales group	J303
Pack	50 pcs.
Customs tariff	85363030

Product notes

WEEE/RoHS-compliant since:
06/28/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Housing material	PA
Inflammability class acc. to UL 94	V2
Degree of protection	IP20

Protective circuit

Nominal voltage U_N	110 V AC
Maximum continuous voltage U_c (wire-ground)	121 V AC
Nominal current I_N	32 A (50°C)
Ground conductor current I_{PE}	$\leq 5 \mu A$
Nominal discharge surge current I_n (8/20) μs (Core-Earth)	51 A
Nominal pulse current I_{an} (10/1000) μs (Core-Earth)	5.5 A
Capacity (Core-Earth)	≤ 0.34 nF

Connection data

Type of connection	Screw terminal blocks
Screw thread	M3
Tightening torque	0.5 Nm
Stripping length	8 mm
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

Certificates / Approvals



Certification

CSA, CUL, GOST, UL

Accessories

Item	Designation	Description
Assembly		
2794990	D-TERMITRAB-UK 5	Cover for setting the end of a TT-UK 5 row of terminal blocks, color: black

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;