

3900 Splashproof Metal Lever Switches 16A 250Vac



16(4)A 250Vac T85 (3900 & 3950)
 10(4)A 250Vac T85 (All other circuits)
 UL CSA 20A 125/277Vac (ON-OFF Circuits)
 UL CSA 16A 125/277Vac (Other Circuits)
 UL CSA 7A 72Vdc, 14A 36Vdc
 UL 250Vac 1hp, 125Vac 1/2hp
 UL 85°C, file E45221, CSA file LR10990

Inrush rating - Contact factory for details

Approvals and ratings vary with function
 3mm contact gap except where marked μ
 Integral O-ring neck seal
 Technical data on pages 4 & 5

C 3900 B A - - -
 TERMINAL FUNCTION ACTUATOR BODY OPTIONS

TERMINAL	FUNCTION	ACTUATOR
C 6.3 x 0.8	Single pole Double pole 	B
	3900 3950 	
	3901 3951 	
	3902 3952 	
	3910 3960 	
	3911 3961 	
	3920 3970 	
	3921 3971 	
	3922 3972 	
S Screw & clamp available for On - Off switches only		
T Solder		
		Finish is nickel plate



C3900BA ---



C3920BA ---



Guard R17-10

Anti-rotation tab can be specified
for guard fitted in On or Off position



C3950BB ---




C3972BB ---

BODY



A

Without terminal barrier
Single pole



B

With terminal barrier
Double pole only



Panel hole (all types)

OPTIONS

Neck Seal M539

Actuator is visible



Cover M1080



Covers have internal nylon nuts

Fixing nuts

Nickel plated brass are supplied



Hex Back nut





Knurled Front nut

Panel thickness 4.0 with backnut

DIMENSIONS (mm) * Indicates ON position (for On - Off switches)

Single Pole

(C terminals shown)



Optional
P232 plate
SP or DP

Double Pole

(C terminals shown)

