

**TAV**

## SSF215 Series

### Long reach external mount via 1/2" NPT



- Long reach for thick walled tanks and boss mounting
- Available with flying lead or M12 plug connection
- Float material SS 316, stem material SS 304
- External mount via 1/2" NPT thread, so does not require access to the inside of the tank for fitting.
- N/O or N/C switching action

#### Technical Specification

Mounting style	External	Cable length - standard	100cm
Mounting thread	1/2" NPT	Cable size	17/0.10 - AWG22
Float & Stem material	316/304 grade SS	Cable conductor material	Tinned copper
Maximum Temperature	120°C	Cable sheath material	Teflon
Maximum pressure	10 bar	Cable temperature rating	200°C
Float SG	0.7	Sealing gasket	Not supplied
Minimum fluid SG	0.8	Tightening torque for fixing	2.0kg/cm

#### Electrical Specification



Contact Form	N/O (N/C)
Switching Power Max	VA
Switching Voltage AC Max	V
Switching Voltage DC Max	V
Switching Current Max	A

All ratings are for resistive load only.

Standard Parts	Stem Material	Float Material	Max Power	Leadouts
SSF215X100	SS304	SS316	50VA	100cm Teflon AWG 22
SSF215XPM12	SS304	SS316	50VA	M12 Plug connection

Custom versions can be made for particular applications. Please contact Cynergy3 with your requirements.

#### Mechanical Dimensions



The SSF215 series of floats switches are externally mounted horizontal switches. This series has an extended reach to provide a solution for extra thick tank walls or for mounting in welded on 1/2" NPT bosses.

The 1/2" NPT thread enables the switches to be fitted through the wall of a tank from the outside, so does not require access to the inside of the tank.

The floatswitch can be fitted to achieve either N/O (make on rise) or N/C (make on fall) switching action by simply rotating the switch through 180°.

Cynergy3 Components Ltd.  
7 Cobham Road  
Ferndown Industrial Estate  
Wimborne, Dorset BH21 7PE  
Telephone +44 (0) 1202 897969

Email:sales@cynergy3.com

**ISO9001 CERTIFIED**

[www.cynergy3.com](http://www.cynergy3.com)