



### FEATURES:

- Fits Fluke, HP, Tektronix Wavetek and Amprobe meters configured with non-sheathed standard and 4 mm banana jacks.
- Test probe & banana plug bodies are molded directly to a flexible 48" (122 cm) high strand count/high temperature silicone leads for added pull strength, overall probe length 4.85" (12.3 cm).
- Nickel plated brass tip offers high conductivity for precision measurements.
- Medium alligators are insulated for added safety and can quickly snap onto the .080" (2.03 mm) O.D. probe tip.
- Medium alligators have an overall length of 2.25" (5.7 cm) and grip up to 0.30" (7.62 mm) O.D. terminals.
- Slide-on extended tips have an overall length of 4" (10.16 cm) & attaches to the probe tip to allow access to hard to reach test points. The Extended Tip is insulated to the point to prevent accidental shorting.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).  
All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA

### MATERIALS:

#### Model 5309A: Test Probe Set:

Probe body Polypropylene. Fire Retardant - Santoprene overmold., Tip: Brass

Wire: 18 AWG, 65 x 36 Tinned Copper Strand, Silicone Insulation, O.D. 0.144" (3.7 mm). Length: 48" (122 cm)

Banana Plug: Insulation: Polypropylene – Plug Body: Brass Nickel Plated, Spring: Beryllium Copper, Nickel Plated

**RATINGS:** Operating Voltage: 1000 VRMS, Current: 10 Amperes

#### Model 6262: Slide-on Extended Tip:

Insulation – Polypropylene UL94 V-2, Color: one black and one red

Probe Tip: Stainless Steel with Kynar Insulation Sleeve to Tip End

**RATINGS:** 300 VRMS, 3 Amperes

#### Model 6264: Alligator Adapter:

Insulation: Polypropylene, Color: One Black, One Red

Body: Steel, Nickel Plated, Spring: Music Wire

**RATINGS:** 300 VRMS, Current: 5 Amperes

### Ordering Information: Model 5325A

Kit shipped in a plastic blister package. Replacement P/N's: Model 5309A: Test Probes, set of one black and one red, Model 6262: Slide-on Extended Tip, set of one black and one red, Model 6264: Alligator Adapter, set of one black and one red.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

5325A