





PRODUCT NUMBER
SEE TABLE




WITH END WINDOW
NOTE 10
-5XXX & POCKETS
FOR END LATCHES

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101	projection INCH/MM	product family QUICKIE	
ltr	ecn	no	dr	date	tolerances unless otherwise specified			title	
J	V01358	MEM	6/01/00		angles	.XX±.01/.3	scale 1:1	P.F. HDR. ASS'Y. SLIMLINE 4 WALL	
K	V01830	MEM	7/19/00		linear	.XXX±.005/.13			
L	V11733	DAI	6/20/01	0'±2'		.XXXX±.0020/.051		sheet 1 of 6 size	
M	V20434	RGD	3/05/02	dr	S. ROYER	9/09/97	FCI	dwg no	
N	V21540	GIP	9/25/02	enr	L. FYE	9/09/97		73638	
P	M05-0089	ERE	5/20/05	chr	L. FYE	9/09/97		type	
R	M07-0116	AGS	2/24/07	appd	L. FYE	9/09/97		Product Customer Drawing	
sheet	revision	R	R	R	R	R	R		
index	sheet	1	2	3	4	5	6		


PRODUCT NUMBER
SEE TABLE

NOTES:


- ①. MOLDING MATERIAL: 30% GLASS FILLED POLYESTER
FLAME RETARDANT PER UL94V-0. COLOR-BLUE.
- ②. TERMINAL MATERIAL: PHOSPHOR BRONZE.
- ③. REFER TO TA 556 FOR APPLICATION, TOOLING
AND INSTRUCTIONS.
4. UNLESS OTHERWISE SPECIFIED, 1"
PERMISSIBLE ON ALL SURFACES.
5. LOGO LOCATION OPTIONAL.
- ⑥. TWO NON-CRITICAL SIDES OF PIN TIP NOT
PLATED TYP BOTH ENDS.
7. 3 LBS / .36 KG PIN RETENTION IN BOTH
DIRECTIONS. MAX DRAFT
8. RECOMMENDED PLATED-THRU-HOLE DIMENSIONS ARE:
DRILLED HOLE: .0453/1.151±.0010/.025 DIA
COPPER PLATING THICKNESS: .001/.025 TO .003/.076
SOLDER PLATING THICKNESS: .0003/.076 TO .0007/.0178
OVERALL HOLE SIZE: .040/1.016±.003/.076 DIA
- ⑨. ON HEADERS 2 X 20 AND LARGER THE .260/6.6 DIM
HAS A MINIMUM SIZE OF .240/6.1.
- ⑩. DASH -5XX SERIES HAS END WINDOWS & POCKETS
FOR END LATCHES. P/N 68767-002
11. DASH -0XX SERIES; NO END WINDOWS
- ⑫. DASH -2XX SERIES; DUPLEX (GOLD-TIN/LEAD 60/40)
PLATING WITH NO END WINDOWS
LEAD FREE OPTION: DASH -2XX SERIES; DUPLEX (GOLD-TIN)
PLATING WITH NO END WINDOWS
- ⑬. ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- ⑭. IF "LF" P/N THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- ⑮. THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING
SOLDER PROCESS.
- ⑮. PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.




2 X 5
STYLE A



2 X 7
STYLE C



2 X 5
STYLE B



2 X 8 & LARGER
STYLE D

mat'l. code					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE					
ltr	ecn	no	dr	date	tolerances unless otherwise specified							title				
R					angles	linear		.XX±.01/.3 .XXX±.005/.13 .XXXX±.0020/.051		INCH/MM		P.F. HDR. ASS'Y. SLIMLINE 4 WALL				
					0°±2'				scale 1:1		dwg no			sheet 2 of 6	size	
					dr	S. ROYER		9/09/97				73638			A3	
					enr	L. FYE		9/09/97				type			Product	Customer
					chr	L. FYE		9/09/97				Drawing				
					appd	L. FYE		9/09/97								
sheet index		revision sheet														



FCIconnect.com

Copyright FCI

PRODUCT NO NOTE 13	NO OF POS	DIM R	DIM S	DIM T	DIM E	TERMINAL PLATING NOTE 16	STYLE
73638 -X01	2 X 5	.78/19.81	.72/18.28	.400/10.16	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	A
-X02					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-X03					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-X04					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-X05					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-X06	2 X 5	.78/19.81	.72/18.28	.400/10.16	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	A
-X07	2 X 7	.98/24.89	.92/23.37	.600/15.24	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	C
-X08					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-X09					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-X10					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-X11					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-X12	2 X 7	.98/24.89	.92/23.37	.600/15.24	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	C
-X13	2 X 8	1.08/27.43	1.02/25.91	.700/17.78	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
-X14					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-X15					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-X16					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-X17					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-X18	2 X 8	1.08/27.43	1.02/25.91	.700/17.78	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D
-X19	2 X 10	1.28/35.51	1.22/30.99	.900/22.86	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
-X20					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-X21					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-X22					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-X23					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
73638-X24	2 X 10	1.28/35.51	1.22/30.99	.900/22.86	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D

mat'l. code				surface ISO 1302 ☒ ISO 406 ISO 1101		projection 	product family QUICKIE		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title		
R					angles .XX±.01/.3	INCH/MM	P.F. HDR. ASS'Y. SLIMLINE 4 WALL		
					linear .XXX±.005/.13				
					0°±2'		scale 1:1		
					dr S. ROYER 9/09/97		dwg no sheet 3 of 6 size 73638 A3		
					enr L. FYE 9/09/97				
					chr L. FYE 9/09/97				
					appd L. FYE 9/09/97				
sheet index	revision sheet						type Product Customer Drawing		

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO. NOTE 13	NO OF POS	DIM R	DIM S	DIM T	DIM E	TERMINAL PLATING NOTE 16	STYLE
73638-X25	2 X 12	1.48/37.59	1.42/36.07	1.100/27.94	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
↑ -X26	↑	↑	↑	↑	.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	↑
-X27					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-X28					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
↓ -X29	↓	↓	↓	↓	.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	↓
-X30	2 X 12	1.48/37.59	1.42/36.07	1.100/27.94	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D
-X31	2 X 13	1.58/40.13	1.52/38.61	1.200/30.48	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
↑ -X32	↑	↑	↑	↑	.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	↑
-X33					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-X34					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
↓ -X35	↓	↓	↓	↓	.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	↓
-X36	2 X 13	1.58/40.13	1.52/38.61	1.200/30.48	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D
-X37	2 X 15	1.78/45.21	1.72/43.69	1.400/35.56	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
↑ -X38	↑	↑	↑	↑	.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	↑
-X39					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-X40					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
↓ -X41	↓	↓	↓	↓	.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	↓
-X42	2 X 15	1.78/45.21	1.72/43.69	1.400/35.56	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D
-X43	2 X 17	1.98/50.29	1.92/48.77	1.600/40.64	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
↑ -X44	↑	↑	↑	↑	.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	↑
-X45					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-X46					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
↓ -X47	↓	↓	↓	↓	.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	↓
-X48	2 X 17	1.98/50.29	1.92/48.77	1.600/40.64	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	
↓ -X49	2 X 20	2.28/57.91	2.22/56.39	1.900/48.26	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	↓
73638-X50	2 X 20	2.28/57.91	2.22/56.39	1.900/48.26	.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	D

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE	
ltr	ecn	no	dr	date	tolerances unless otherwise specified				
R					angles	.XX±.01/.3		title P.F. HDR. ASS'Y.	
					linear	.XXX±.005/.13		SLIMLINE 4 WALL	
					0°±2'	.XXXX±.0020/.051		scale 1:1	
					dr	S. ROYER	9/09/97	dwg no	
					enr	L. FYE	9/09/97	sheet 4 of 6	
					chr	L. FYE	9/09/97	size A3	
					appd	L. FYE	9/09/97	type Product Customer Drawing	
sheet index	revision sheet								

form: A3

PRODUCT NO NOTE 13	NO OF POS	DIM R	DIM S	DIM T	DIM E	TERMINAL PLATING	STYLE	
73638-210	2 X 5	.78/19.81	.72/18.29	.400/10.16	.255/6.48	30u"/.76u GOLD DUPLEX	A	NOTE 12
↑ -219	2 X 10	1.28/32.51	1.22/30.99	.900/22.86	.160/4.06	30u"/.76u GOLD DUPLEX	D	NOTE 12
-220	2 X 10	1.28/32.51	1.22/30.99	.900/22.86	.255/6.48	30u"/.76u GOLD DUPLEX	D	NOTE 12
-225	2 X 12	1.48/39.59	1.42/36.07	1.100/27.94	.160/4.06	30u"/.76u GOLD DUPLEX	D	NOTE 12
↓ -237	2 X 15	1.78/45.21	1.72/43.69	1.400/35.56	.160/4.06	30u"/.76u GOLD DUPLEX	D	NOTE 12
73638-261	2 X 25	2.78/70.61	2.72/69.09	2.400/60.91	.160/4.06	30u"/.76u GOLD DUPLEX	D	NOTE 12



FCIconnect.com

Copyright FCI

form: A3

mat'l. code					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE				
ltr	ecn	no	dr	date	tolerances unless otherwise specified							title			
R					angles	linear	.XX±.01/.3 .XXX±.005/.13 0°±2° .XXXX±.0020/.051		INCH/MM		P.F. HDR. ASS'Y. SLIMLINE 4 WALL				
									scale 1:1		dwg no				
					dr	S. ROYER	9/09/97				sheet 6 of 6			size	
					engr	L. FYE	9/09/97				73638			A3	
					chr	L. FYE	9/09/97								
					appd	L. FYE	9/09/97				type Product Customer Drawing				
sheet index		revision sheet													