

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC
HBDIST
-


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REMOVED CSA&OPTIMIZATION SSA RATING&USED WELDED CONTACT ECO-13-000705	21Aug2013	YS.H	F.B



①

PART A



C:MADE IN CHINA


SEE NOTE 5.

PART B

0.45


0.3

0.3




1

1



CONNECTION FIGURE

FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING
(BOTTOM VIEW)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	H.Sasaki
CHK	Y.Oikawa
APVD	A.Nagai
PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	-
CUSTOMER DRAWING	-

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
4 PLC ANGLES	± -
MATERIAL	FINISH
-	-



TE Connectivity

OJ-SH-LM SPEC,000 CUSTOMER DRAWING

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C= 1461404	-
SCALE	5:1	SHEET	1 of 2
REV	D		

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC
HBDIST
—


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

⑫	ACTIVE	1461404-4	OJ-SH-124LM, 000	107-79010	24V	OJ-SH-124LM	f
	ACTIVE	1461404-6	OJ-SH-112LM, 000	107-79010	12V	OJ-SH-112LM	e
	OBSOLETE	1461404-3	OJ-SH-109LM, 000	107-79010	9V	OJ-SH-109LM	d
	OBSOLETE	1461404-2	OJ-SH-106LM, 000	107-79010	6V	OJ-SH-106LM	c
	ACTIVE	1461404-1	OJ-SH-105LM, 000	107-79010	5V	OJ-SH-105LM	b
	OBSOLETE	1461404-5	OJ-SH-103LM, 000	107-79010	3V	OJ-SH-103LM	a
	PART STATUS	TE CONNECTIVITY PART NUMBER	TE CONNECTIVITY TYPE NAME	PACKAGE SPEC,	PART B	PART A	TYPE

RELAY TYPE

①④ NOTE:
1.LOT NO. SYSTEM AS FOLLOWING:



⑫ 2.TERMINAL DIMENSION IS BEFORE SOLDER DIP;

⑫ 3.FOR THE TIN-PLATING OF THE PINS:
+0.1mm FOR WIDTH,THICKENSS AND DIAMETER.
+0.5mm FOR LENGTH.

⑫ 4.USED WELDED CONTACT&LASER MARKING.

⑫ 5.ADD LOT NO. SYSTEM AS FOLLOWING;

① ① A
I II III

I, DIGITS FOR DAY OF THE WEEK

1...MONDAY IN THIS WEEK;
2...TUESDAY IN THIS WEEK;

7...SUNDAY IN THIS WEEK

II, DIGITS FOR SHIFT OF THE DAY

1...DAY SHIFT IN THIS DAY;
2...NIGHT SHIFT IN THIS DAY;

III, ONE CHARACTER DISTINGUISH THE
LINE IDENTITY, SUCH AS: A,B.....Z

		UV RESIN	SEAL (VENT HOLE)	16
		EPOXY RESIN	SEAL (BASE & BOBBIN)	15
		3UEW	MAGNETIC WIRE	14
94V-0		P.B.T	CASE	13
94V-0		P.B.T	BASE	12
94V-0		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
94V-0		P.P.S	CARD	9
		Ag	MOVABLE CONTACT	8
		Ag	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	Cu ALLOY	NO.TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	H.Sasaki				
DIMENSIONS: mm		CHK	Y.Oikawa				
		APVD	A.Nagai				
		PRODUCT SPEC					
		APPLICATION SPEC					
		WEIGHT					
MATERIAL		FINISH		CUSTOMER DRAWING			
		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
		A3		00779	C=	1461404	—
		SCALE		5:1	SHEET	2 of 2	REV D