

8838	3100	8853	6800
8838-0-15-XX-34-XX-10-0 Solder mount in .086 min. mounting hole	3100-0-15-XX-34-XX-10-0 Solder mount in .074 min. mounting hole	8853-0-15-XX-34-XX-10-0 Press-fit in .071 mounting hole	6800-0-15-XX-34-XX-04-0 Solder mount in .080 min. mounting hole

8206	0739		
8206-0-15-XX-34-XX-40-0 Surface mount	0739-0-15-XX-34-XX-10-0 Hex press-fit in .078±.002 plated thru hole		

--	--	--	--

SPECIFICATIONS SHELL MATERIAL: Brass Alloy 360, 1/2 Hard CONTACT MATERIAL: Beryllium Copper Alloy 172, HT DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ±.002°	ORDER CODE: XXXX - 0 - 15 - XX - 34 - XX - 10 - 0 BASIC PART # → SPECIFY SHELL FINISH: 01 200μ" TIN/LEAD OVER NICKEL 80 200μ" TIN OVER NICKEL ◇ 15 10μ" GOLD OVER NICKEL ◇ SPECIFY CONTACT FINISH: 01 200μ" TIN/LEAD OVER NICKEL 80 200μ" TIN OVER NICKEL ◇ 27 30μ" GOLD OVER NICKEL ◇ CONTACT #34 CONTACT (DATA ON PAGE 222) RoHS 2002/95/EC
--	---