





DIMENSIONS



TERMINATION



PCB LAYOUT



ORDERING INFORMATION

SERIES	8609	3	96	7	1	13	7	4	5	ELF							
ROWS FITTED WITH CONTACTS	ROW a	b	c	d	e	f	g	h	i	j							
ROW a - c	d	e	f	g	h	i	j	k	l	m							
NO. OF CONTACTS	TYPE OF INSULATOR	3 ROW MALE INSULATOR	METHOD OF MOUNTING	STANDARD MOUNTING - STYLE C	TERMINATION	ANGLED SPILL	OPTIONS	NO. OPTION WITH HARPOONS	PERFORMANCE CLASS	DIN 4,1612 CLASS 3	DIN 4,1612 CLASS 2	DIN 4,1612 CLASS 1	AS PER MIL C 55302 / JSS 50808	PITCH PER ROW	2,54 mm	LEAD FREE VERSION	ELF

GENERAL CHARACTERISTICS & ROHS INFO
REFER DRAWING C-8609-0000A

mat'l. code				surface		tolerance		projection		product family	
SEE DRAWING C-8609-0000A				ISO 1302		ISO 406 ISO 1101				8609	
tr				ecn		no		dr		date	
A				104-0063		MINI		2004-09-16		angles	
B				105-0042		MINI		2005-05-19		linear	
C				106-0061		MINI		2006-05-31		0°±2°	
D				107-0100		KR		2007-08-20		mini k v	
E				108-0146		KR		2008-10-21		engr	
								chr		KESAVAN R	
								apdd		KESAVAN R	
sheet index				revision		E					
1				sheet		1					
dwg no				sheet 1 of 1		size		type		Product Customer Drawing	
C-8609-2001				A3							