



- Ferrite drum core construction.
- Magnetically shielded.
- L x W x H: 8.5 x 8.5 x 4.0 mm Max.
- Product weight: 0.9 g (Ref.)
- Moisture Sensitivity Level: 1
- RoHS compliance.
- Qualification to AEC-Q200.

Environmental Data



- Carrier tape and reel packaging
- 13.0" diameter reel
- 1000pcs per reel

Applications



- Automotive and other high temperature, high reliability application.

SMD Power Inductor CDRH8D38/A



Electrical Characteristics

Part No.	Stamp	Inductance (μ H) 100kHz	D.C.R. (m Ω) [Max.] (Typ.) (at 20°C) ※1	Rated current (A) (at 125°C)※2
CDRH8D38/ANP-100MC	100	10 μ H $\pm$ 20%	42.5(34)	1.72
CDRH8D38/ANP-120MC	120	12 μ H $\pm$ 20%	55.0(44)	1.57
CDRH8D38/ANP-150MC	150	15 μ H $\pm$ 20%	70.0(56)	1.41
CDRH8D38/ANP-180MC	180	18 μ H $\pm$ 20%	83.8(67)	1.33
CDRH8D38/ANP-220MC	220	22 μ H $\pm$ 20%	100.0(80)	1.24
CDRH8D38/ANP-270MC	270	27 μ H $\pm$ 20%	125.0(100)	1.11
CDRH8D38/ANP-330MC	330	33 μ H $\pm$ 20%	141.3(113)	0.98
CDRH8D38/ANP-390MC	390	39 μ H $\pm$ 20%	171.3(137)	0.89
CDRH8D38/ANP-470MC	470	47 μ H $\pm$ 20%	225.0(180)	0.78
CDRH8D38/ANP-560MC	560	56 μ H $\pm$ 20%	290.0(232)	0.68
CDRH8D38/ANP-680MC	680	68 μ H $\pm$ 20%	318.8(255)	0.65
CDRH8D38/ANP-820MC	820	82 μ H $\pm$ 20%	363.8(291)	0.60
CDRH8D38/ANP-101MC	101	100 μ H $\pm$ 20%	478.8(383)	0.53
CDRH8D38/ANP-121MC	121	120 μ H $\pm$ 20%	530.0(424)	0.50

※1 D.C.R.() are typical value. .













※2. Rated current: The DC current at which the inductance decreases to 65% of its nominal value or when $\Delta t=30^{\circ}\text{C}$, whichever is lower .

SMD Power Inductor CDRH8D38/A



Saturation Current & Temperature Rise Graph

— L (20°C) — L (125°C) — ΔT





SMD Power Inductor CDRH8D38/A





Saturation Current & Temperature Rise Graph

— L (20°C) — L (125°C) — ΔT



Solder Reflow Condition



Please refer to the sales offices on our website - <http://www.sumida.com>

Hong Kong

Tel. +852-2880-6781
FAX. +852-2565-9600
sales@hk.sumida.com

Saitama(Japan)

Tel. +81-48-691-7300
FAX. +81-48-691-7340
sales@jp.sumida.com

Chicago

Tel. +1-847-545-6700
FAX. +1-847-545-6720
sales@us.sumida.com

Shanghai

Tel. +86-21-5836-3299
FAX. +86-21-5836-3266
shanghai.sales@cn.sumida.com

Seoul

Tel. +82-2-6237-0777
FAX. +82-2-6237-0778
sales@kr.sumida.com

Obernzell

Tel. +49-8591-937-0
FAX. +49-8591-937-103
contact@eu.sumida.com

Shenzhen

Tel. +86-755-8291-0228
FAX. +86-755-8291-0338
shenzhen.sales@cn.sumida.com

Singapore

Tel. +65-6296-3388
FAX. +65-6841-4426
sales@sg.sumida.com

Neumarkt

Tel. +49-9181-4509-110
FAX. +49-9181-4509-310
info@comp@eu.sumida.com

Taipei

Tel. +886-2-8751-2737
FAX. +886-2-8751-2738
sales@tw.sumida.com

San Jose

Tel. +1-408-321-9660
FAX. +1-408-321-9308
sales@us.sumida.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sumida:

[CDRH8D38/ANP-120MC](#) [CDRH8D38/ANP-820MC](#) [CDRH8D38/ANP-390MC](#) [CDRH8D38/ANP-121MC](#)
[CDRH8D38/ANP-680MC](#) [CDRH8D38/ANP-180MC](#) [CDRH8D38/ANP-330MC](#) [CDRH8D38/ANP-560MC](#)
[CDRH8D38/ANP-101MC](#) [CDRH8D38/ANP-270MC](#)