


T-2³/₄ MINIATURE BAYONET BASE

QUARTZ HALOGEN LAMP

12V 25W

WAMCO PART NO.		ENVELOPE SIZE	BASE TYPE	RATING	FILAMENT SHAPE		
WL-8GH005597-12		T-2 ³ / ₄	BA9s/13	12V 25W	C-6		
TEST VOLTS	CURRENT (A)			LIGHT OUTPUT (MSCP)			LIFE HRS
	MIN	NOM	MAX	MIN	NOM	MAX	
12V	1.87	2.08	2.28	27.0	32.0	37.0	2,000

DIMENSIONAL CHARACTERISTICS



NOTES

1. Lamp clean with no foreign materials or glass chips inside
2. Envelope clear and free of scratches, discoloration, and any cement residue
3. Nickel-plated base
4. Primary contact silver-plated disk
5. Park mark WL-8GH005597-12
6. RoHS compliant

