




- 1 WIRE RANGE: 0.3 – 0.9MM² (22–18 AWG).
- 2 INSULATION RANGE: 1.50–2.40[.060–.094] DIA.
- 3 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4 BOTTOM CONTACT STOP IS OPTIONAL CONSTRUCTION.
- 5 0.000762 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN LOCALIZED TIN PLATE AREA OVER 0.00127 [.000050] MIN NICKEL.



5	0.20 [.008] BRASS	794440-3
NONE	0.20 [.008] BRASS	794440-2
PRE-TIN	0.20 [.008] BRASS	794440-1
FINISH	MATERIAL	PART NO



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 20FEB2004	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK C. JONES 20FEB04				
		APVD C. JONES 20FEB04	NAME PIN, UNIVERSAL MATE-N-LOK			
		PRODUCT SPEC				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC				
0 PLC ± -		—				
1 PLC ± -		—				
2 PLC ± 0.13 [.005]		—				
3 PLC ± -		—				
4 PLC ± -		—				
ANGLES ± 0°30'		—				
FINISH		WEIGHT				
SEE TABLE		—				
		CUSTOMER DRAWING				
		SCALE 10:1				
		SHEET 1 OF 1				
		REV H				