








RECOMMEND P.C.B. LAYOUT



CIRCUIT: SPST
CONTACT CONFIGURATION

NOTES:

1. ALL DIMENSIONS IN MM
2. TERM. NOS. FOR REF ONLY
3. RATING: DC 12V, 50mA
4. TRAVEL: 0.3 ± 0.15 mm
5. CONTACT RESISTANCE: 100m Ohms Max.

				E-SWITCH®					
REV.	DESCRIPTION	DATE	CHKD	TOLERANCES	TITLE				
					TL 1100 F F260 Q				
A	RELEASED FOR PRODUCTION			±0.4	SCALE	DATE	DR	DWG	REV
				±0.25					
				0.0	2:1	11/10/97	MM	P001105	A
				0.00					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED									