


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			D	REVISED PER E.O. P17811	24JUL2002	XS	RDR
			E	REVISED PER E.O. P21412	20JUL2012	AM	RDR
			F	REVISED PER ECO-14-019072	23FEB2015	JA	DM
			F1	REVISED PER ECO-16-013285	08SEP2016	DD	DM



5. RECEPTACLE IS SUPPLIED WITH DUST CAP (2415-001-2405).
7. PART MODIFICATION: THREADED ADAPTER
- 4 MATERIAL: RECEPTACLE HOUSING: PA66 GF10 (BLACK)
CONDUIT ADAPTER: PA66 GF10 (GREEN, GRAY, BLUE)
GROMMET: SILICONE (ORANGE-RED)
- 6 CONDUIT ADAPTER ACCEPTS EITHER TYPES:
A. CONDUIT ADAPTER CAP NUT (CN21) AND SEAL RING (SRN21)
B. BACKSHELL (M902-2243) COMPRESSION NUT (M902-2053) CABLE $\varnothing .430-.570$ [10.92-14.78]
C. BACKSHELL (M902-2244) COMPRESSION NUT (M902-2054) CABLE $\varnothing .570-710$ [14.78-18.03]
- 8 DATE CODE: IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY.
YEAR: FIRST AND SECOND DIGITS. (14 = 2014)
MONTH: THRID DIGIT, EXCLUDING I. A = JAN., B = FEB., C = MARCH.... (K = OCTOBER)
DAY: FOURTH AND FIFTH DIGITS (14 = 14th DAY)
HOUR: SIXTH AND SEVENTH DIGITS (11 = 11AM)
- 3 SEE 0425-021-0000 APPLICATION SPECIFICATION
A. RECOMMENDED WIRE INSULATION RANGE
B. CONTACT REMOVAL TOOLS
C. RECOMMENDED MOUNTING HOLE & PANEL THICKNESS
D. MOUNTING HARDWARE & MOUNTING TORQUE.
2. THIS RECEPTACLE MATES WITH HDP26-24-XXP/SX-XXXX PLUG
X = SEAL TYPE (N,T,E)
XX = INSERT ARRANGEMENT
XXXX = MODIFICATION

1 SEE CUSTOMER DRAWING, 0425-014-2400 FOR AVAILABLE INSERT ARRANGEMENTS AND PART NUMBERS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 04SEP1997 STEVE BEARD	TE Connectivity	
		CHK 19JUL2002 PAUL BURKE		
DIMENSIONS: INCHES[mm]		APVD 23JUL2002 STEVE BEARD	NAME RECEPTACLE, THREADED SIZE 24, -L015 MOD HDP SERIES	
		PRODUCT SPEC 0425-021-0000	SIZE A3	
		APPLICATION SPEC 3	CAGE CODE 4AFU8	
MATERIAL 4	FINISH N/A	WEIGHT	DRAWING NO G-HDP24-24-XXP/SX-L015	
		Customer Drawing	SCALE 2:1	SHEET 1 OF 1
			REV F1	RESTRICTED TO