

## Overview

KEMET's C0G dielectric features a 125°C maximum operating temperature and is considered "stable." The Electronics Components, Assemblies & Materials Association (EIA) characterizes C0G dielectric as a Class I material. Components of this classification are temperature compensating and are suited for resonant circuit applications or those where Q and

stability of capacitance characteristics are required. C0G exhibits no change in capacitance with respect to time and voltage and boasts a negligible change in capacitance with reference to ambient temperature. Capacitance change is limited to  $\pm 30$  ppm/°C from -55°C to +125°C.

## Benefits

- -55°C to +125°C operating temperature range
- Lead (Pb)-Free, RoHS, and REACH compliant
- EIA 0201, 0402, 0603, 0805, 1206, 1210, 1808, 1812, 1825, 2220, and 2225 case sizes
- DC voltage ratings of 10 V, 16 V, 25 V, 50 V, 100 V, 200 V and 250 V
- Capacitance offerings ranging from 0.5 pF up to 0.47  $\mu$ F
- Available capacitance tolerances of  $\pm 0.10$  pF,  $\pm 0.25$  pF,  $\pm 0.5$  pF,  $\pm 1\%$ ,  $\pm 2\%$ ,  $\pm 5\%$ ,  $\pm 10\%$ , and  $\pm 20\%$
- No piezoelectric noise
- Extremely low ESR and ESL
- High thermal stability
- High ripple current capability



## Ordering Information

| C       | 1206                                                                                 | C                                  | 104                                                                                                                                     | J                                                                                                                                                 | 3                                                                                   | G          | A                    | C                               | TU                                       |
|---------|--------------------------------------------------------------------------------------|------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|------------|----------------------|---------------------------------|------------------------------------------|
| Ceramic | Case Size (L" x W")                                                                  | Specification/ Series <sup>1</sup> | Capacitance Code (pF)                                                                                                                   | Capacitance Tolerance <sup>2</sup>                                                                                                                | Voltage                                                                             | Dielectric | Failure Rate/ Design | Termination Finish <sup>3</sup> | Packaging/Grade (C-Spec) <sup>4</sup>    |
|         | 0201<br>0402<br>0603<br>0805<br>1206<br>1210<br>1808<br>1812<br>1825<br>2220<br>2225 | C = Standard                       | 2 significant digits + number of zeros.<br>Use 9 for 1.0 – 9.9 pF<br>Use 8 for 0.5 – .99 pF<br>e.g., 2.2 pF = 229<br>e.g., 0.5 pF = 508 | B = $\pm 0.10$ pF<br>C = $\pm 0.25$ pF<br>D = $\pm 0.5$ pF<br>F = $\pm 1\%$<br>G = $\pm 2\%$<br>J = $\pm 5\%$<br>K = $\pm 10\%$<br>M = $\pm 20\%$ | 8 = 10 V<br>4 = 16 V<br>3 = 25 V<br>5 = 50 V<br>1 = 100 V<br>2 = 200 V<br>A = 250 V | G = C0G    | A = N/A              | C = 100% Matte Sn               | Blank = Bulk<br>TU = 7" Reel<br>Unmarked |

<sup>1</sup> Flexible termination option is available. Please see FT-CAP product bulletin C1062\_C0G\_FT-CAP\_SMD

<sup>2</sup> Additional capacitance tolerance offerings may be available. Contact KEMET for details.

<sup>3</sup> Additional termination finish options may be available. Contact KEMET for details.

<sup>4</sup> Additional reeling or packaging options may be available. Contact KEMET for details.

## Dimensions – Millimeters (Inches)



| EIA Size Code | Metric Size Code | L Length                  | W Width                   | T Thickness               | B Bandwidth               | S Separation Minimum | Mounting Technique           |
|---------------|------------------|---------------------------|---------------------------|---------------------------|---------------------------|----------------------|------------------------------|
| 0201          | 0603             | 0.60 (.024) ± 0.03 (.001) | 0.30 (.012) ± 0.03 (.001) | See Table 2 for Thickness | 0.15 (.006) ± 0.05 (.002) | N/A                  | Solder Reflow Only           |
| 0402          | 1005             | 1.00 (.040) ± 0.05 (.002) | 0.50 (.020) ± 0.05 (.002) |                           | 0.30 (.012) ± 0.10 (.004) | 0.30 (.012)          |                              |
| 0603          | 1608             | 1.60 (.063) ± 0.15 (.006) | 0.80 (.032) ± 0.15 (.006) |                           | 0.35 (.014) ± 0.15 (.006) | 0.70 (.028)          | Solder Wave or Solder Reflow |
| 0805          | 2012             | 2.00 (.079) ± 0.20 (.008) | 1.25 (.049) ± 0.20 (.008) |                           | 0.50 (.02) ± 0.25 (.010)  | 0.75 (.030)          |                              |
| 1206          | 3216             | 3.20 (.126) ± 0.20 (.008) | 1.60 (.063) ± 0.20 (.008) |                           | 0.50 (.02) ± 0.25 (.010)  | N/A                  | Solder Reflow Only           |
| 1210          | 3225             | 3.20 (.126) ± 0.20 (.008) | 2.50 (.098) ± 0.20 (.008) |                           | 0.50 (.02) ± 0.25 (.010)  |                      |                              |
| 1808          | 4520             | 4.70 (.185) ± 0.50 (.020) | 2.00 (.079) ± 0.20 (.008) |                           | 0.60 (.024) ± 0.35 (.014) |                      |                              |
| 1812          | 4532             | 4.50 (.177) ± 0.30 (.012) | 3.20 (.126) ± 0.30 (.012) |                           | 0.60 (.024) ± 0.35 (.014) |                      |                              |
| 1825          | 4564             | 4.50 (.177) ± 0.30 (.012) | 6.40 (.252) ± 0.40 (.016) |                           | 0.60 (.024) ± 0.35 (.014) |                      |                              |
| 2220          | 5650             | 5.70 (.224) ± 0.40 (.016) | 5.00 (.197) ± 0.40 (.016) |                           | 0.60 (.024) ± 0.35 (.014) |                      |                              |
| 2225          | 5664             | 5.60 (.220) ± 0.40 (.016) | 6.40 (.248) ± 0.40 (.016) |                           | 0.60 (.024) ± 0.35 (.014) |                      |                              |

## Benefits cont'd

- Preferred capacitance solution at line frequencies and into the MHz range
- No capacitance change with respect to applied rated DC voltage
- Negligible capacitance change with respect to temperature from -55°C to +125°C
- No capacitance decay with time
- Non-polar device, minimizing installation concerns
- 100% pure matte tin-plated termination finish allowing for excellent solderability
- SnPb plated termination finish option available upon request (5% minimum)

## Applications

Typical applications include critical timing, tuning, circuits requiring low loss, circuits with pulse, high current, decoupling, bypass, filtering, transient voltage suppression, blocking and energy storage.

## Qualification/Certification

Commercial Grade products are subject to internal qualification. Details regarding test methods and conditions are referenced in Table 4, Performance and Reliability.

## Environmental Compliance

Lead (Pb)-Free, RoHS, and REACH compliant without exemptions.



RoHS Compliant

## Electrical Parameters/Characteristics

| Item                                                               | Parameters/Characteristics                                                              |
|--------------------------------------------------------------------|-----------------------------------------------------------------------------------------|
| Operating Temperature Range                                        | -55°C to +125°C                                                                         |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC) | ±30 ppm/°C                                                                              |
| Aging Rate (Maximum % Capacitance Loss/Decade Hour)                | 0%                                                                                      |
| Dielectric Withstanding Voltage (DWV)                              | 250% of rated voltage<br>(5 ±1 seconds and charge/discharge not exceeding 50 mA)        |
| Dissipation Factor (DF) Maximum Limit @ 25°C                       | 0.1%                                                                                    |
| Insulation Resistance (IR) Limit @ 25°C                            | 1,000 megohm microfarads or 100 GΩ<br>(Rated voltage applied for 120 ±5 seconds @ 25°C) |

To obtain IR limit, divide  $M\Omega \cdot \mu F$  value by the capacitance and compare to GΩ limit. Select the lower of the two limits.

Capacitance and Dissipation Factor (DF) measured under the following conditions:

1 MHz ±100 kHz and 1.0 Vrms ±0.2 V if capacitance ≤ 1,000 pF

1 kHz ±50 Hz and 1.0 Vrms ±0.2 V if capacitance > 1,000 pF

Note: When measuring capacitance it is important to ensure the set voltage level is held constant. The HP4284 and Agilent E4980 have a feature known as Automatic Level Control (ALC). The ALC feature should be switched to "ON."

## Post Environmental Limits

| High Temperature Life, Biased Humidity, Moisture Resistance |                  |                   |                                |                   |                       |
|-------------------------------------------------------------|------------------|-------------------|--------------------------------|-------------------|-----------------------|
| Dielectric                                                  | Rated DC Voltage | Capacitance Value | Dissipation Factor (Maximum %) | Capacitance Shift | Insulation Resistance |
| C0G                                                         | All              | All               | 0.5                            | 0.3% or ±0.25 pF  | 10% of Initial Limit  |



**Table 1A – Capacitance Range/Selection Waterfall (0201 – 1206 Case Sizes) cont'd**

| Cap           | Cap Code   | Case Size/<br>Series     |  |   |   |   |   | C0201C                                                                                     |     |     | C0402C |    |    |    |     |     | C0603C |    |    |    |    |     | C0805 C |     |    |    |    |    | C1206C |     |     |    |    |    |    |     |     |     |    |    |    |    |  |  |  |
|---------------|------------|--------------------------|--|---|---|---|---|--------------------------------------------------------------------------------------------|-----|-----|--------|----|----|----|-----|-----|--------|----|----|----|----|-----|---------|-----|----|----|----|----|--------|-----|-----|----|----|----|----|-----|-----|-----|----|----|----|----|--|--|--|
|               |            | Voltage Code             |  |   |   |   |   | 8                                                                                          | 4   | 3   | 8      | 4  | 3  | 5  | 1   | 2   | A      | 8  | 4  | 3  | 5  | 1   | 2       | A   | 8  | 4  | 3  | 5  | 1      | 2   | A   | 8  | 4  | 3  | 5  | 1   | 2   | A   |    |    |    |    |  |  |  |
|               |            | Rated Voltage (VDC)      |  |   |   |   |   | 10                                                                                         | 16  | 25  | 10     | 16 | 25 | 50 | 100 | 200 | 250    | 10 | 16 | 25 | 50 | 100 | 200     | 250 | 10 | 16 | 25 | 50 | 100    | 200 | 250 | 10 | 16 | 25 | 50 | 100 | 200 | 250 |    |    |    |    |  |  |  |
|               |            | Capacitance<br>Tolerance |  |   |   |   |   | Product Availability and Chip Thickness Codes<br>See Table 2 for Chip Thickness Dimensions |     |     |        |    |    |    |     |     |        |    |    |    |    |     |         |     |    |    |    |    |        |     |     |    |    |    |    |     |     |     |    |    |    |    |  |  |  |
| 91 pF         | 910        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  |        | BB | BB | BB | BB |     | CF      | CF  | CF | CF | CF | CF |        | DC  | DC  | DC | DC | DC | DC |     | EB  | EB  | EB | EB | EB | EB |  |  |  |
| 100 pF        | 101        |                          |  | F | G | J | K | M                                                                                          | AB² | AB² | AB²    |    | BB | BB | BB  | BB  | BB     | BB | BB | BB | BD | BD  | CF      | CF  | CF | CF | CF | CF |        | DC  | DC  | DC | DC | DC | DC |     | EB  | EB  | EB | EB | EB | EB |  |  |  |
| 110 – 180 pF* | 111 – 181* |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  | BB     | BB | BB | BB | BD | BD  | CF      | CF  | CF | CF | CF | CF |        | DC  | DC  | DC | DC | DC | DC |     | EB  | EB  | EB | EB | EB | EB |  |  |  |
| 200 – 270 pF* | 201 – 271* |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  | BB     | BB | BB | BD | BD | CF  | CF      | CF  | CF | CF | CF | CF | DC     | DC  | DC  | DC | DC | DC |    | EB  | EB  | EB  | EB | EB | EB |    |  |  |  |
| 300 pF        | 301        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  | BB     | BB | BD | BD |    |     | CF      | CF  | CF | CF | CF | CF | CF     | DC  | DC  | DC | DC | DC | DC |     | EB  | EB  | EB | EB | EB | EB |  |  |  |
| 330 pF        | 331        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  | BB     | BD | BD |    |    | CF  | CF      | CF  | CF | CF | CF | CF | DC     | DC  | DC  | DC | DC | DC |    | EB  | EB  | EB  | EB | EB | EB |    |  |  |  |
| 360 pF        | 361        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  | BB     |    |    |    |    | CF  | CF      | CF  | CF | CF | CF | CF | DC     | DC  | DC  | DC | DC | DC |    | EB  | EB  | EB  | EB | EB | EB |    |  |  |  |
| 390 pF        | 391        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  | BB     |    |    |    |    | CF  | CF      | CF  | CF | CF | CF | CF | DC     | DC  | DC  | DC | DC | DC |    | EB  | EB  | EB  | EB | EB | EB |    |  |  |  |
| 430 pF        | 431        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  | BB     |    |    |    |    | CF  | CF      | CF  | CF | CF | CF | CF | DC     | DC  | DC  | DC | DC | DC |    | EB  | EB  | EB  | EB | EB | EB |    |  |  |  |
| 470 pF        | 471        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  | BB     |    |    |    |    | CF  | CF      | CF  | CF | CF | CF | CF | DC     | DC  | DC  | DC | DC | DD |    | EB  | EB  | EB  | EB | EB | EB |    |  |  |  |
| 510 pF        | 511        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  | BB     |    |    |    |    | CF  | CF      | CF  | CF | CF | CF | CF | DC     | DC  | DC  | DC | DC | DC |    | EB  | EB  | EB  | EB | EB | EB |    |  |  |  |
| 560 pF        | 561        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  | BB     |    |    |    |    | CF  | CF      | CF  | CF | CF | CF | CF | DC     | DC  | DC  | DC | DC | DC |    | EB  | EB  | EB  | EB | EB | EB |    |  |  |  |
| 620 pF        | 621        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  | BB     |    |    |    |    | CF  | CF      | CF  | CF | CF | CF | CF | DC     | DC  | DC  | DC | DC | DC |    | EB  | EB  | EB  | EB | EB | EB |    |  |  |  |
| 680 pF        | 681        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  | BB     |    |    |    |    | CF  | CF      | CF  | CF | CF | CF | CF | DC     | DC  | DC  | DC | DC | DC |    | EB  | EB  | EB  | EB | EB | EB |    |  |  |  |
| 750 pF        | 751        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  | BB     |    |    |    |    | CF  | CF      | CF  | CF | CF | CF | CF | DC     | DC  | DC  | DC | DC | DC |    | EB  | EB  | EB  | EB | EB | EB |    |  |  |  |
| 820 pF        | 821        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  | BB     |    |    |    |    | CF  | CF      | CF  | CF | CF | CF | CF | DC     | DC  | DC  | DC | DC | DC |    | EB  | EB  | EB  | EB | EB | EB |    |  |  |  |
| 910 pF        | 911        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  | BB     |    |    |    |    | CF  | CF      | CF  | CF | CF | CF | CF | DC     | DC  | DC  | DC | DD | DD |    | EB  | EB  | EB  | EB | EB | EB |    |  |  |  |
| 1,000 pF      | 102        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  | BB     |    |    |    |    | CF  | CF      | CF  | CF | CF | CF | CF | DC     | DC  | DC  | DC | DD | DD |    | EB  | EB  | EB  | EB | EB | EB |    |  |  |  |
| 1,100 pF      | 112        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  |        |    |    |    |    | CF  | CF      | CF  | CF | CF | CH | CH | DC     | DC  | DC  | DC | DC | DC |    | EB  | EB  | EB  | EB | EB | EB |    |  |  |  |
| 1,200 pF      | 122        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  |        |    |    |    |    | CF  | CF      | CF  | CF | CF | CH | CH | DC     | DC  | DC  | DC | DC | DC |    | EB  | EB  | EB  | EB | EB | EB |    |  |  |  |
| 1,300 pF      | 132        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  |        |    |    |    |    | CF  | CF      | CF  | CF | CF | CH | CH | DD     | DD  | DD  | DD | DD | DC | DC |     | EB  | EB  | EB | EB | EC | EC |  |  |  |
| 1,500 pF      | 152        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  | BB  |        |    |    |    |    | CF  | CF      | CF  | CF | CF | CH | CH | DD     | DD  | DD  | DD | DD | DC | DC |     | EB  | EB  | EB | EB | ED | ED |  |  |  |
| 1,600 pF      | 162        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  |     |        |    |    |    |    | CF  | CF      | CF  | CF | CF | CH | CH | DD     | DD  | DD  | DD | DD | DC | DC |     | EB  | EB  | EB | EB | ED | ED |  |  |  |
| 1,800 pF      | 182        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  |     |        |    |    |    |    | CF  | CF      | CF  | CF | CF | CH | CH | DD     | DD  | DD  | DD | DD | DC | DC |     | EB  | EB  | EB | EB | ED | ED |  |  |  |
| 2,000 pF      | 202        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  |     |        |    |    |    |    | CF  | CF      | CF  | CF | CF | CH | CH | DC     | DC  | DC  | DC | DC | DC | DC |     | EB  | EB  | EB | EB | ED | ED |  |  |  |
| 2,200 pF      | 222        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    | BB | BB | BB  |     |        |    |    |    |    | CF  | CF      | CF  | CF | CF | CH | CH | DC     | DC  | DC  | DC | DC | DC | DC |     | EB  | EB  | EB | EB | EE | EE |  |  |  |
| 2,400 pF      | 242        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  | CF | CF |    |    | DC     | DC  | DC  | DC | DC | DC | DC |     | EB  | EB  | EB | EB | EC | EC |  |  |  |
| 2,700 pF      | 272        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  | CF | CF |    |    | DC     | DC  | DC  | DC | DC | DC | DC |     | EB  | EB  | EB | EB | EC | EC |  |  |  |
| 3,000 pF      | 302        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  | CF | CF |    |    | DD     | DD  | DD  | DD | DC | DC | DC |     | EC  | EC  | EC | EC | EC | EB |  |  |  |
| 3,300 pF      | 332        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  | CF | CF |    |    | DD     | DD  | DD  | DD | DC | DC | DC |     | EC  | EC  | EC | EC | EE | EB |  |  |  |
| 3,600 pF      | 362        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  | CF | CF |    |    | DD     | DD  | DD  | DD | DC | DD | DD |     | EC  | EC  | EC | EE | EB | EB |  |  |  |
| 3,900 pF      | 392        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  | CF | CF |    |    | DE     | DE  | DE  | DE | DC | DD | DD |     | EC  | EC  | EC | EF | EB | EB |  |  |  |
| 4,300 pF      | 432        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  | CF | CF |    |    | DE     | DE  | DE  | DE | DC | DD | DD |     | EC  | EC  | EC | EC | EC | EB |  |  |  |
| 4,700 pF      | 472        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  | CF | CF |    |    | DE     | DE  | DE  | DE | DC | DD | DD |     | EC  | EC  | EC | EC | EC | EB |  |  |  |
| 5,100 pF      | 512        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  | CF |    |    |    | DE     | DE  | DE  | DE | DC | DD | DD |     | ED  | ED  | ED | ED | ED | EB |  |  |  |
| 5,600 pF      | 562        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  | CF |    |    |    | DC     | DC  | DC  | DC | DD | DD | DD |     | ED  | ED  | ED | ED | ED | EB |  |  |  |
| 6,200 pF      | 622        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  | CF |    |    |    | DC     | DC  | DC  | DC | DC | DG | DG |     | EB  | EB  | EB | EB | EB | EB |  |  |  |
| 6,800 pF      | 682        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  | CF |    |    |    | DC     | DC  | DC  | DC | DC | DG | DG |     | EB  | EB  | EB | EB | EB | EB |  |  |  |
| 7,500 pF      | 752        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  |    |    |    |    | DC     | DC  | DC  | DC | DC | DG | DG |     | EB  | EB  | EB | EB | EB | EB |  |  |  |
| 8,200 pF      | 822        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  |    |    |    |    | DC     | DC  | DC  | DC | DC | DG | DG |     | EC  | EC  | EC | EC | EB | EC |  |  |  |
| 9,100 pF      | 912        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  |    |    |    |    | DC     | DC  | DC  | DC | DC |    |    |     |     |     |    |    |    |    |  |  |  |
| 10,000 pF     | 103        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  |    |    |    |    | DC     | DC  | DC  | DC | DD |    |    |     |     |     |    |    |    |    |  |  |  |
| 12,000 pF     | 123        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  |    |    |    |    | DC     | DC  | DC  | DC | DE |    |    |     |     |     |    |    |    |    |  |  |  |
| 15,000 pF     | 153        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    | CF  | CF      | CF  |    |    |    |    | DC     | DC  | DC  | DD | DG |    |    |     |     |     |    |    |    |    |  |  |  |
| 18,000 pF     | 183        |                          |  | F | G | J | K | M                                                                                          |     |     |        |    |    |    |     |     |        |    |    |    |    |     |         |     |    |    |    | DC | DC     | DC  | DD  |    |    |    |    |     |     |     |    |    |    |    |  |  |  |

**Table 1A – Capacitance Range/Selection Waterfall (0201 – 1206 Case Sizes) cont'd**

| Cap       | Cap Code | Case Size/<br>Series  |  |   |   | C0201C                                                                                     |    |    | C0402C |        |    |    |     | C0603C |        |    |    |    |    | C0805 C |     |     |    |    |        | C1206C |     |     |     |    |    |    |    |     |     |     |    |
|-----------|----------|-----------------------|--|---|---|--------------------------------------------------------------------------------------------|----|----|--------|--------|----|----|-----|--------|--------|----|----|----|----|---------|-----|-----|----|----|--------|--------|-----|-----|-----|----|----|----|----|-----|-----|-----|----|
|           |          | Voltage Code          |  |   |   | 8                                                                                          | 4  | 3  | 8      | 4      | 3  | 5  | 1   | 2      | A      | 8  | 4  | 3  | 5  | 1       | 2   | A   | 8  | 4  | 3      | 5      | 1   | 2   | A   | 8  | 4  | 3  | 5  | 1   | 2   | A   |    |
|           |          | Rated Voltage (VDC)   |  |   |   | 10                                                                                         | 16 | 25 | 10     | 16     | 25 | 50 | 100 | 200    | 250    | 10 | 16 | 25 | 50 | 100     | 200 | 250 | 10 | 16 | 25     | 50     | 100 | 200 | 250 | 10 | 16 | 25 | 50 | 100 | 200 | 250 |    |
|           |          | Capacitance Tolerance |  |   |   | Product Availability and Chip Thickness Codes<br>See Table 2 for Chip Thickness Dimensions |    |    |        |        |    |    |     |        |        |    |    |    |    |         |     |     |    |    |        |        |     |     |     |    |    |    |    |     |     |     |    |
| 47,000 pF | 473      |                       |  | F | G | J                                                                                          | K  | M  |        |        |    |    |     |        |        |    |    |    |    |         |     |     | DG | DG | DG     |        |     |     |     |    |    |    | EC | EC  | EC  | EE  | EH |
| 56,000 pF | 563      |                       |  | F | G | J                                                                                          | K  | M  |        |        |    |    |     |        |        |    |    |    |    |         |     |     |    |    |        |        |     |     |     |    |    |    | ED | ED  | ED  | EF  |    |
| 68,000 pF | 683      |                       |  | F | G | J                                                                                          | K  | M  |        |        |    |    |     |        |        |    |    |    |    |         |     |     |    |    |        |        |     |     |     |    |    |    | EF | EF  | EF  | EH  |    |
| 82,000 pF | 823      |                       |  | F | G | J                                                                                          | K  | M  |        |        |    |    |     |        |        |    |    |    |    |         |     |     |    |    |        |        |     |     |     |    |    |    | EH | EH  | EH  | EH  |    |
| 0.10 µF   | 104      |                       |  | F | G | J                                                                                          | K  | M  |        |        |    |    |     |        |        |    |    |    |    |         |     |     |    |    |        |        |     |     |     |    |    |    | EH | EH  | EH  |     |    |
| Cap       | Cap Code | Rated Voltage (VDC)   |  |   |   | 10                                                                                         | 16 | 25 | 10     | 16     | 25 | 50 | 100 | 200    | 250    | 10 | 16 | 25 | 50 | 100     | 200 | 250 | 10 | 16 | 25     | 50     | 100 | 200 | 250 | 10 | 16 | 25 | 50 | 100 | 200 | 250 |    |
|           |          | Voltage Code          |  |   |   | 8                                                                                          | 4  | 3  | 8      | 4      | 3  | 5  | 1   | 2      | A      | 8  | 4  | 3  | 5  | 1       | 2   | A   | 8  | 4  | 3      | 5      | 1   | 2   | A   | 8  | 4  | 3  | 5  | 1   | 2   | A   |    |
|           |          | Case Size/Series      |  |   |   | C0201C                                                                                     |    |    |        | C0402C |    |    |     |        | C0603C |    |    |    |    | C0805C  |     |     |    |    | C1206C |        |     |     |     |    |    |    |    |     |     |     |    |

\*Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82 and 91).

xx<sup>1</sup> Available only in D, J, K, M tolerance

xx<sup>2</sup> Available only in J, K, M tolerance.

These products are protected under US Patents 7,172,985 & 7,670,981, other patents pending, and any foreign counterparts.

Table 1B – Capacitance Range/Selection Waterfall (1210 – 2225 Case Sizes)

| Capacitance   | Capacitance Code | Case Size/ Series     |   |   | C1210C                                                                                     |    |    |    |     |     |     |    | C1808C |     |     |    | C1812C |     |     |    | C1825C |     |     |    | C2220C |     |     |    | C2225C |     |  |
|---------------|------------------|-----------------------|---|---|--------------------------------------------------------------------------------------------|----|----|----|-----|-----|-----|----|--------|-----|-----|----|--------|-----|-----|----|--------|-----|-----|----|--------|-----|-----|----|--------|-----|--|
|               |                  | Voltage Code          |   |   | 8                                                                                          | 4  | 3  | 5  | 1   | 2   | A   | 5  | 1      | 2   | A   | 5  | 1      | 2   | A   | 5  | 1      | 2   | A   | 5  | 1      | 2   | A   | 5  | 1      | 2   |  |
|               |                  | Rated Voltage (VDC)   |   |   | 10                                                                                         | 16 | 25 | 50 | 100 | 200 | 250 | 50 | 100    | 200 | 250 | 50 | 100    | 200 | 250 | 50 | 100    | 200 | 250 | 50 | 100    | 200 | 250 | 50 | 100    | 200 |  |
|               |                  | Capacitance Tolerance |   |   | Product Availability and Chip Thickness Codes<br>See Table 2 for Chip Thickness Dimensions |    |    |    |     |     |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 1.0 – 9.1 pF* | 109 – 919*       | B                     | C | D | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FB  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 10 – 91 pF*   | 100 – 910*       |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FB  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 100 – 300 pF* | 101 – 301*       |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FB  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 330 – 430 pF* | 331 – 431*       |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FB  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 470 – 910 pF* | 471 – 911*       |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FB  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 1,000 pF      | 102              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FB  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 1,100 pF      | 112              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FB  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 1,200 pF      | 122              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FB  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 1,300 pF      | 132              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FC  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 1,500 pF      | 152              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FE  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 1,600 pF      | 162              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FE  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 1,800 pF      | 182              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FE  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 2,000 pF      | 202              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FC  | FE  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 2,200 pF      | 222              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FC  | FG  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 2,400 pF      | 242              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FC  | FC  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 2,700 pF      | 272              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FC  | FC  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 3,000 pF      | 302              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FC  | FF  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 3,300 pF      | 332              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FF  | FF  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 3,600 pF      | 362              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FF  | FF  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 3,900 pF      | 392              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FF  | FF  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 4,300 pF      | 432              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FF  | FF  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 4,700 pF      | 472              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FF  | FF  | FF | FF     | FG  | FG  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 5,100 pF      | 512              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FG  | FG  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 5,600 pF      | 562              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FG  | FG  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 6,200 pF      | 622              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FG  | FB  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 6,800 pF      | 682              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FG  | FB  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 7,500 pF      | 752              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FC  | FC  | FC | FC     | FC  | FB  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 8,200 pF      | 822              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FC  | FC  | FC | FC     | FC  | FB  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 9,100 pF      | 912              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FE  | FE  | FE | FE     | FE  | FB  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 10,000 pF     | 103              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FF  | FF  | FF | FF     | FF  | FB  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 12,000 pF     | 123              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FG  | FG  | FG | FG     | FB  | FB  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 15,000 pF     | 153              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FG  | FG  | FG | FG     | FB  | FC  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 18,000 pF     | 183              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FC  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 22,000 pF     | 223              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FF  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 27,000 pF     | 273              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FG  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 33,000 pF     | 333              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FH  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 39,000 pF     | 393              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FB  | FH  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 47,000 pF     | 473              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FE  | FJ  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 56,000 pF     | 563              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FF  |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 68,000 pF     | 683              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FB  | FB  | FB | FB     | FC  | FG  |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 82,000 pF     | 823              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FC  | FC  | FC | FF     | FH  |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 0.10 µF       | 104              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FE  | FE  | FE | FG     | FM  |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 0.12 µF       | 124              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FG  | FG  | FG | FG     | FH  |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 0.15 µF       | 154              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FH  | FH  | FH | FH     | FM  |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 0.18 µF       | 184              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FJ  | FJ  | FJ |        |     |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 0.22 µF       | 224              |                       |   |   | F                                                                                          | G  | J  | K  | M   | FK  | FK  | FK |        |     |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 0.27 µF       | 274              |                       |   |   | F                                                                                          | G  | J  | K  | M   |     |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 0.33 µF       | 334              |                       |   |   | F                                                                                          | G  | J  | K  | M   |     |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 0.39 µF       | 394              |                       |   |   | F                                                                                          | G  | J  | K  | M   |     |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| 0.47 µF       | 474              |                       |   |   | F                                                                                          | G  | J  | K  | M   |     |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |     |    |        |     |  |
| Capacitance   | Capacitance Code | Rated Voltage (VDC)   |   |   | 10                                                                                         | 16 | 25 | 50 | 100 | 200 | 250 | 50 | 100    | 200 | 250 | 50 | 100    | 200 | 250 | 50 | 100    | 200 | 250 | 50 | 100    | 200 | 250 | 50 | 100    | 200 |  |
|               |                  | Voltage Code          |   |   | 8                                                                                          | 4  | 3  | 5  | 1   | 2   | A   | 5  | 1      | 2   | A   | 5  | 1      | 2   | A   | 5  | 1      | 2   | A   | 5  | 1      | 2   | A   | 5  | 1      | 2   |  |
|               |                  | Case Size/ Series     |   |   | C1210C                                                                                     |    |    |    |     |     |     |    | C1808C |     |     |    | C1812C |     |     |    | C1825C |     |     |    | C2220C |     |     |    | C2225C |     |  |


\*Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82 and 91).

These products are protected under US Patents 7,172,985 &amp; 7,670,981, other patents pending, and any foreign counterparts.

**Table 2 – Chip Thickness/Packaging Quantities**

| Thickness Code | Case Size | Thickness ± Range (mm) | Paper Quantity |          | Plastic Quantity |          |
|----------------|-----------|------------------------|----------------|----------|------------------|----------|
|                |           |                        | 7" Reel        | 13" Reel | 7" Reel          | 13" Reel |
| AB             | 0201      | 0.30 ± 0.03            | 15,000         | 0        | 0                | 0        |
| BB             | 0402      | 0.50 ± 0.05            | 10,000         | 50,000   | 0                | 0        |
| BD             | 0402      | 0.55 ± 0.05            | 10,000         | 50,000   | 0                | 0        |
| CF             | 0603      | 0.80 ± 0.07            | 4,000          | 15,000   | 0                | 0        |
| CH             | 0603      | 0.85 ± 0.07            | 4,000          | 15,000   | 0                | 0        |
| DJ             | 0805      | 0.70 ± 0.20            | 4,000          | 10,000   | 0                | 0        |
| DC             | 0805      | 0.78 ± 0.10            | 4,000          | 10,000   | 0                | 0        |
| DD             | 0805      | 0.90 ± 0.10            | 4,000          | 10,000   | 0                | 0        |
| DE             | 0805      | 1.00 ± 0.10            | 0              | 0        | 2,500            | 10,000   |
| DF             | 0805      | 1.10 ± 0.10            | 0              | 0        | 2,500            | 10,000   |
| DG             | 0805      | 1.25 ± 0.15            | 0              | 0        | 2,500            | 10,000   |
| EB             | 1206      | 0.78 ± 0.10            | 4,000          | 10,000   | 4,000            | 10,000   |
| EC             | 1206      | 0.90 ± 0.10            | 0              | 0        | 4,000            | 10,000   |
| ED             | 1206      | 1.00 ± 0.10            | 0              | 0        | 2,500            | 10,000   |
| EE             | 1206      | 1.10 ± 0.10            | 0              | 0        | 2,500            | 10,000   |
| EF             | 1206      | 1.20 ± 0.15            | 0              | 0        | 2,500            | 10,000   |
| EH             | 1206      | 1.60 ± 0.20            | 0              | 0        | 2,000            | 8,000    |
| FB             | 1210      | 0.78 ± 0.10            | 0              | 0        | 4,000            | 10,000   |
| FC             | 1210      | 0.90 ± 0.10            | 0              | 0        | 4,000            | 10,000   |
| FE             | 1210      | 1.00 ± 0.10            | 0              | 0        | 2,500            | 10,000   |
| FF             | 1210      | 1.10 ± 0.10            | 0              | 0        | 2,500            | 10,000   |
| FG             | 1210      | 1.25 ± 0.15            | 0              | 0        | 2,500            | 10,000   |
| FH             | 1210      | 1.55 ± 0.15            | 0              | 0        | 2,000            | 8,000    |
| FM             | 1210      | 1.70 ± 0.20            | 0              | 0        | 2,000            | 8,000    |
| FJ             | 1210      | 1.85 ± 0.20            | 0              | 0        | 2,000            | 8,000    |
| FK             | 1210      | 2.10 ± 0.20            | 0              | 0        | 2,000            | 8,000    |
| NC             | 1706      | 1.00 ± 0.15            | 0              | 0        | 4,000            | 10,000   |
| LF             | 1808      | 1.00 ± 0.15            | 0              | 0        | 2,500            | 10,000   |
| GB             | 1812      | 1.00 ± 0.10            | 0              | 0        | 1,000            | 4,000    |
| GD             | 1812      | 1.25 ± 0.15            | 0              | 0        | 1,000            | 4,000    |
| GH             | 1812      | 1.40 ± 0.15            | 0              | 0        | 1,000            | 4,000    |
| GG             | 1812      | 1.55 ± 0.10            | 0              | 0        | 1,000            | 4,000    |
| GK             | 1812      | 1.60 ± 0.20            | 0              | 0        | 1,000            | 4,000    |
| GJ             | 1812      | 1.70 ± 0.15            | 0              | 0        | 1,000            | 4,000    |
| GN             | 1812      | 1.70 ± 0.20            | 0              | 0        | 1,000            | 4,000    |
| GM             | 1812      | 2.00 ± 0.20            | 0              | 0        | 500              | 2,000    |
| HB             | 1825      | 1.10 ± 0.15            | 0              | 0        | 1,000            | 4,000    |
| HE             | 1825      | 1.40 ± 0.15            | 0              | 0        | 1,000            | 4,000    |
| HG             | 1825      | 1.60 ± 0.20            | 0              | 0        | 1,000            | 4,000    |
| JB             | 2220      | 1.00 ± 0.15            | 0              | 0        | 1,000            | 4,000    |
| JD             | 2220      | 1.30 ± 0.15            | 0              | 0        | 1,000            | 4,000    |
| JE             | 2220      | 1.40 ± 0.15            | 0              | 0        | 1,000            | 4,000    |
| JF             | 2220      | 1.50 ± 0.15            | 0              | 0        | 1,000            | 4,000    |
| JG             | 2220      | 1.70 ± 0.15            | 0              | 0        | 1,000            | 4,000    |
| JL             | 2220      | 2.00 ± 0.20            | 0              | 0        | 500              | 2,000    |
| KE             | 2225      | 1.40 ± 0.15            | 0              | 0        | 1,000            | 4,000    |
| Thickness Code | Case Size | Thickness ± Range (mm) | 7" Reel        | 13" Reel | 7" Reel          | 13" Reel |
|                |           |                        | Paper Quantity |          | Plastic Quantity |          |

Package quantity based on finished chip thickness specifications.



## Soldering Process

### Recommended Soldering Technique:

- Solder wave or solder reflow for EIA case sizes 0603, 0805 and 1206
- All other EIA case sizes are limited to solder reflow only

### Recommended Reflow Soldering Profile:

KEMET's families of surface mount multilayer ceramic capacitors (SMD MLCCs) are compatible with wave (single or dual), convection, IR or vapor phase reflow techniques. Preheating of these components is recommended to avoid extreme thermal stress. KEMET's recommended profile conditions for convection and IR reflow reflect the profile conditions of the IPC/J-STD-020 standard for moisture sensitivity testing. These devices can safely withstand a maximum of three reflow passes at these conditions.

| Profile Feature                                       | Termination Finish |                    |
|-------------------------------------------------------|--------------------|--------------------|
|                                                       | SnPb               | 100% Matte Sn      |
| <b>Preheat/Soak</b>                                   |                    |                    |
| Temperature Minimum ( $T_{Smin}$ )                    | 100°C              | 150°C              |
| Temperature Maximum ( $T_{Smax}$ )                    | 150°C              | 200°C              |
| Time ( $t_s$ ) from $T_{Smin}$ to $T_{Smax}$          | 60 – 120 seconds   | 60 – 120 seconds   |
| Ramp-Up Rate ( $T_L$ to $T_P$ )                       | 3°C/second maximum | 3°C/second maximum |
| Liquidous Temperature ( $T_L$ )                       | 183°C              | 217°C              |
| Time Above Liquidous ( $t_L$ )                        | 60 – 150 seconds   | 60 – 150 seconds   |
| Peak Temperature ( $T_P$ )                            | 235°C              | 260°C              |
| Time Within 5°C of Maximum Peak Temperature ( $t_p$ ) | 20 seconds maximum | 30 seconds maximum |
| Ramp-Down Rate ( $T_P$ to $T_L$ )                     | 6°C/second maximum | 6°C/second maximum |
| Time 25°C to Peak Temperature                         | 6 minutes maximum  | 8 minutes maximum  |



Note 1: All temperatures refer to the center of the package, measured on the capacitor body surface that is facing up during assembly reflow.


**Table 4 – Performance & Reliability: Test Methods and Conditions**

| Stress                 | Reference                       | Test or Inspection Method                                                                                                                                                                                                                         |
|------------------------|---------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Terminal Strength      | JIS-C-6429                      | Appendix 1, Note: Force of 1.8 kg for 60 seconds.                                                                                                                                                                                                 |
| Board Flex             | JIS-C-6429                      | Appendix 2, Note: Standard termination system – 2.0 mm (minimum) for all except 3 mm for C0G. Flexible termination system – 3.0 mm (minimum).                                                                                                     |
| Solderability          | J-STD-002                       | Magnification 50 X. Conditions:                                                                                                                                                                                                                   |
|                        |                                 | a) Method B, 4 hours @ 155°C, dry heat @ 235°C                                                                                                                                                                                                    |
|                        |                                 | b) Method B @ 215°C category 3                                                                                                                                                                                                                    |
|                        |                                 | c) Method D, category 3 @ 260°C                                                                                                                                                                                                                   |
| Temperature Cycling    | JESD22 Method JA-104            | 1,000 Cycles (-55°C to +125°C). Measurement at 24 hours +/- 2 hours after test conclusion.                                                                                                                                                        |
| Biased Humidity        | MIL-STD-202 Method 103          | Load Humidity: 1,000 hours 85°C/85% RH and rated voltage. Add 100 K ohm resistor. Measurement at 24 hours +/- 2 hours after test conclusion.                                                                                                      |
|                        |                                 | Low Volt Humidity: 1,000 hours 85°C/85% RH and 1.5 V. Add 100 K ohm resistor. Measurement at 24 hours +/- 2 hours after test conclusion.                                                                                                          |
| Moisture Resistance    | MIL-STD-202 Method 106          | t = 24 hours/cycle. Steps 7a and 7b not required. Unpowered. Measurement at 24 hours +/- 2 hours after test conclusion.                                                                                                                           |
| Thermal Shock          | MIL-STD-202 Method 107          | -55°C/+125°C. Note: Number of cycles required – 300, maximum transfer time – 20 seconds, dwell time – 15 minutes. Air – Air.                                                                                                                      |
| High Temperature Life  | MIL-STD-202 Method 108 /EIA-198 | 1,000 hours at 125°C (85°C for X5R, Z5U and Y5V) with 2 X rated voltage applied.                                                                                                                                                                  |
| Storage Life           | MIL-STD-202 Method 108          | 150°C, 0 VDC for 1,000 hours.                                                                                                                                                                                                                     |
| Vibration              | MIL-STD-202 Method 204          | 5 g's for 20 min., 12 cycles each of 3 orientations. Note: Use 8" X 5" PCB 0.031" thick 7 secure points on one long side and 2 secure points at corners of opposite sides. Parts mounted within 2" from any secure point. Test from 10 – 2,000 Hz |
| Mechanical Shock       | MIL-STD-202 Method 213          | Figure 1 of Method 213, Condition F.                                                                                                                                                                                                              |
| Resistance to Solvents | MIL-STD-202 Method 215          | Add aqueous wash chemical, OKEM Clean or equivalent.                                                                                                                                                                                              |

## Storage and Handling

Ceramic chip capacitors should be stored in normal working environments. While the chips themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. In addition, packaging materials will be degraded by high temperature– reels may soften or warp and tape peel force may increase. KEMET recommends that maximum storage temperature not exceed 40°C and maximum storage humidity not exceed 70% relative humidity. Temperature fluctuations should be minimized to avoid condensation on the parts and atmospheres should be free of chlorine and sulfur bearing compounds. For optimized solderability chip stock should be used promptly, preferably within 1.5 years of receipt.

## Construction



## Capacitor Marking (Optional):

Laser marking option is not available on:

- C0G, Ultra Stable X8R and Y5V dielectric devices
- EIA 0402 case size devices
- EIA 0603 case size devices with Flexible Termination option.
- KPS Commercial and Automotive grade stacked devices.

These capacitors are supplied unmarked only.

## Tape & Reel Packaging Information

KEMET offers multilayer ceramic chip capacitors packaged in 8, 12 and 16 mm tape on 7" and 13" reels in accordance with EIA Standard 481. This packaging system is compatible with all tape-fed automatic pick and place systems. See Table 2 for details on reeling quantities for commercial chips.



**Table 5 – Carrier Tape Configuration – Embossed Plastic & Punched Paper (mm)**

| EIA Case Size     | Tape Size (W)* | Pitch (P <sub>1</sub> )* |
|-------------------|----------------|--------------------------|
| 01005 – 0402      | 8              | 2                        |
| 0603 – 1210       | 8              | 4                        |
| 1805 – 1808       | 12             | 4                        |
| ≥ 1812            | 12             | 8                        |
| KPS 1210          | 12             | 8                        |
| KPS 1812 & 2220   | 16             | 12                       |
| Array 0508 & 0612 | 8              | 4                        |

\*Refer to Figures 1 & 2 for W and P<sub>1</sub> carrier tape reference locations.

\*Refer to Tables 6 & 7 for tolerance specifications.

**Figure 1 – Embossed (Plastic) Carrier Tape Dimensions****Table 6 – Embossed (Plastic) Carrier Tape Dimensions**

Metric will govern

| Constant Dimensions — Millimeters (Inches) |                                       |                                  |                              |                             |                              |                           |                                  |                                                 |                           |
|--------------------------------------------|---------------------------------------|----------------------------------|------------------------------|-----------------------------|------------------------------|---------------------------|----------------------------------|-------------------------------------------------|---------------------------|
| Tape Size                                  | D <sub>0</sub>                        | D <sub>1</sub> Minimum<br>Note 1 | E <sub>1</sub>               | P <sub>0</sub>              | P <sub>2</sub>               | R Reference<br>Note 2     | S <sub>1</sub> Minimum<br>Note 3 | T<br>Maximum                                    | T <sub>1</sub><br>Maximum |
| 8 mm                                       | 1.5 +0.10/-0.0<br>(0.059 +0.004/-0.0) | 1.0<br>(0.039)                   | 1.75 ±0.10<br>(0.069 ±0.004) | 4.0 ±0.10<br>(0.157 ±0.004) | 2.0 ±0.05<br>(0.079 ±0.002)  | 25.0<br>(0.984)           | 0.600<br>(0.024)                 | 0.600<br>(0.024)                                | 0.100<br>(0.004)          |
| 12 mm                                      |                                       | 1.5<br>(0.059)                   |                              |                             |                              | 30<br>(1.181)             |                                  |                                                 |                           |
| 16 mm                                      |                                       |                                  |                              |                             |                              |                           |                                  |                                                 |                           |
| Variable Dimensions — Millimeters (Inches) |                                       |                                  |                              |                             |                              |                           |                                  |                                                 |                           |
| Tape Size                                  | Pitch                                 | B <sub>1</sub> Maximum<br>Note 4 | E <sub>2</sub><br>Minimum    | F                           | P <sub>1</sub>               | T <sub>2</sub><br>Maximum | W<br>Maximum                     | A <sub>0</sub> ,B <sub>0</sub> & K <sub>0</sub> |                           |
| 8 mm                                       | Single (4 mm)                         | 4.35<br>(0.171)                  | 6.25<br>(0.246)              | 3.5 ±0.05<br>(0.138 ±0.002) | 4.0 ±0.10<br>(0.157 ±0.004)  | 2.5<br>(0.098)            | 8.3<br>(0.327)                   | Note 5                                          |                           |
| 12 mm                                      | Single (4 mm) &<br>Double (8 mm)      | 8.2<br>(0.323)                   | 10.25<br>(0.404)             | 5.5 ±0.05<br>(0.217 ±0.002) | 8.0 ±0.10<br>(0.315 ±0.004)  | 4.6<br>(0.181)            | 12.3<br>(0.484)                  |                                                 |                           |
| 16 mm                                      | Triple (12 mm)                        | 12.1<br>(0.476)                  | 14.25<br>(0.561)             | 7.5 ±0.05<br>(0.138 ±0.002) | 12.0 ±0.10<br>(0.157 ±0.004) | 4.6<br>(0.181)            | 16.3<br>(0.642)                  |                                                 |                           |

- The embossment hole location shall be measured from the sprocket hole controlling the location of the embossment. Dimensions of embossment location and hole location shall be applied independent of each other.
- The tape with or without components shall pass around R without damage (see Figure 6).
- If  $S_1 < 1.0$  mm, there may not be enough area for cover tape to be properly applied (see EIA Standard 481 paragraph 4.3 section b).
- $B_1$  dimension is a reference dimension for tape feeder clearance only.
- The cavity defined by  $A_0$ ,  $B_0$  and  $K_0$  shall surround the component with sufficient clearance that:
  - the component does not protrude above the top surface of the carrier tape.
  - the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.
  - rotation of the component is limited to 20° maximum for 8 and 12 mm tapes and 10° maximum for 16 mm tapes (see Figure 3).
  - lateral movement of the component is restricted to 0.5 mm maximum for 8 and 12 mm wide tape and to 1.0 mm maximum for 16 mm tape (see Figure 4).
  - for KPS Series product,  $A_0$  and  $B_0$  are measured on a plane 0.3 mm above the bottom of the pocket.
  - see Addendum in EIA Standard 481 for standards relating to more precise taping requirements.

**Figure 2 – Punched (Paper) Carrier Tape Dimensions****Table 7 – Punched (Paper) Carrier Tape Dimensions**

Metric will govern

| Constant Dimensions — Millimeters (Inches) |                                         |                                        |                                       |                                       |                         |                 |                    |
|--------------------------------------------|-----------------------------------------|----------------------------------------|---------------------------------------|---------------------------------------|-------------------------|-----------------|--------------------|
| Tape Size                                  | $D_0$                                   | $E_1$                                  | $P_0$                                 | $P_2$                                 | $T_1$ Maximum           | G Minimum       | R Reference Note 2 |
| 8 mm                                       | $1.5 +0.10 -0.0$<br>(0.059 +0.004 -0.0) | $1.75 \pm 0.10$<br>(0.069 $\pm$ 0.004) | $4.0 \pm 0.10$<br>(0.157 $\pm$ 0.004) | $2.0 \pm 0.05$<br>(0.079 $\pm$ 0.002) | 0.10<br>(0.004) Maximum | 0.75<br>(0.030) | 25<br>(0.984)      |
| Variable Dimensions — Millimeters (Inches) |                                         |                                        |                                       |                                       |                         |                 |                    |
| Tape Size                                  | Pitch                                   | E2 Minimum                             | F                                     | $P_1$                                 | T Maximum               | W Maximum       | $A_0 B_0$          |
| 8 mm                                       | Half (2 mm)                             | 6.25<br>(0.246)                        | $3.5 \pm 0.05$<br>(0.138 $\pm$ 0.002) | $2.0 \pm 0.05$<br>(0.079 $\pm$ 0.002) | 1.1<br>(0.098)          | 8.3<br>(0.327)  | Note 1             |
| 8 mm                                       | Single (4 mm)                           |                                        |                                       | $4.0 \pm 0.10$<br>(0.157 $\pm$ 0.004) |                         | 8.3<br>(0.327)  |                    |

- The cavity defined by  $A_0$ ,  $B_0$  and  $T$  shall surround the component with sufficient clearance that:
  - the component does not protrude beyond either surface of the carrier tape.
  - the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.
  - rotation of the component is limited to 20° maximum (see Figure 3).
  - lateral movement of the component is restricted to 0.5 mm maximum (see Figure 4).
  - see Addendum in EIA Standard 481 for standards relating to more precise taping requirements.
- The tape with or without components shall pass around R without damage (see Figure 6).

## Packaging Information Performance Notes



- 1. Cover Tape Break Force:** 1.0 Kg minimum.
- 2. Cover Tape Peel Strength:** The total peel strength of the cover tape from the carrier tape shall be:

| Tape Width   | Peel Strength                    |
|--------------|----------------------------------|
| 8 mm         | 0.1 to 1.0 Newton (10 to 100 gf) |
| 12 and 16 mm | 0.1 to 1.3 Newton (10 to 130 gf) |

The direction of the pull shall be opposite the direction of the carrier tape travel. The pull angle of the carrier tape shall be 165° to 180° from the plane of the carrier tape. During peeling, the carrier and/or cover tape shall be pulled at a velocity of 300 ±10 mm/minute.

- 3. Labeling:** Bar code labeling (standard or custom) shall be on the side of the reel opposite the sprocket holes. *Refer to EIA Standards 556 and 624.*


## Figure 3 – Maximum Component Rotation



## Figure 4 – Maximum Lateral Movement



## Figure 5 – Bending Radius



**Figure 6 – Reel Dimensions**

Note: Drive spokes optional; if used, dimensions B and D shall apply.

**Table 8 – Reel Dimensions**

Metric will govern

| Constant Dimensions — Millimeters (Inches) |                                                                   |                                       |                                        |                                                      |
|--------------------------------------------|-------------------------------------------------------------------|---------------------------------------|----------------------------------------|------------------------------------------------------|
| Tape Size                                  | A                                                                 | B Minimum                             | C                                      | D Minimum                                            |
| 8 mm                                       | 178 ±0.20<br>(7.008 ±0.008)<br>or<br>330 ±0.20<br>(13.000 ±0.008) | 1.5<br>(0.059)                        | 13.0 +0.5/-0.2<br>(0.521 +0.02/-0.008) | 20.2<br>(0.795)                                      |
| 12 mm                                      |                                                                   |                                       |                                        |                                                      |
| 16 mm                                      |                                                                   |                                       |                                        |                                                      |
| Variable Dimensions — Millimeters (Inches) |                                                                   |                                       |                                        |                                                      |
| Tape Size                                  | N Minimum                                                         | W <sub>1</sub>                        | W <sub>2</sub> Maximum                 | W <sub>3</sub>                                       |
| 8 mm                                       | 50<br>(1.969)                                                     | 8.4 +1.5/-0.0<br>(0.331 +0.059/-0.0)  | 14.4<br>(0.567)                        | Shall accommodate tape width<br>without interference |
| 12 mm                                      |                                                                   | 12.4 +2.0/-0.0<br>(0.488 +0.078/-0.0) | 18.4<br>(0.724)                        |                                                      |
| 16 mm                                      |                                                                   | 16.4 +2.0/-0.0<br>(0.646 +0.078/-0.0) | 22.4<br>(0.882)                        |                                                      |

## Figure 7 – Tape Leader & Trailer Dimensions



## Figure 8 – Maximum Camber



## Bulk Cassette Packaging (Ceramic Chips Only)

Meets Dimensional Requirements IEC-286 and EIAJ 7201

Unit mm \*Reference



## Capacitor Dimensions for Bulk Cassette

Cassette Packaging – Millimeters

| EIA Size Code | Metric Size Code | L Length   | W Width    | B Bandwidth | S Separation Minimum | T Thickness | Number of Pieces/Cassette |
|---------------|------------------|------------|------------|-------------|----------------------|-------------|---------------------------|
| 0402          | 1005             | 1.0 ± 0.05 | 0.5 ± 0.05 | 0.2 to 0.4  | 0.3                  | 0.5 ± 0.05  | 50,000                    |
| 0603          | 1608             | 1.6 ± 0.07 | 0.8 ± 0.07 | 0.2 to 0.5  | 0.7                  | 0.8 ± 0.07  | 15,000                    |

## **KEMET Corporation World Headquarters**

2835 KEMET Way  
Simpsonville, SC 29681

Mailing Address:  
P.O. Box 5928  
Greenville, SC 29606

www.kemet.com  
Tel: 864-963-6300  
Fax: 864-963-6521

**Corporate Offices**  
Fort Lauderdale, FL  
Tel: 954-766-2800

## **North America**

### **Southeast**

Lake Mary, FL  
Tel: 407-855-8886

### **Northeast**

Wilmington, MA  
Tel: 978-658-1663

### **Central**

Novi, MI  
Tel: 248-306-9353

### **West**

Milpitas, CA  
Tel: 408-433-9950

### **Mexico**

Guadalajara, Jalisco  
Tel: 52-33-3123-2141

## **Europe**

### **Southern Europe**

Paris, France  
Tel: 33-1-4646-1006

Sasso Marconi, Italy  
Tel: 39-051-939111

### **Central Europe**

Landsberg, Germany  
Tel: 49-8191-3350800

Kamen, Germany  
Tel: 49-2307-438110

### **Northern Europe**

Bishop's Stortford, United Kingdom  
Tel: 44-1279-460122

Espoo, Finland  
Tel: 358-9-5406-5000

## **Asia**

### **Northeast Asia**

Hong Kong  
Tel: 852-2305-1168

Shenzhen, China  
Tel: 86-755-2518-1306

Beijing, China  
Tel: 86-10-5829-1711

Shanghai, China  
Tel: 86-21-6447-0707

Taipei, Taiwan  
Tel: 886-2-27528585

### **Southeast Asia**

Singapore  
Tel: 65-6586-1900

Penang, Malaysia  
Tel: 60-4-6430200

Bangalore, India  
Tel: 91-806-53-76817

*Note: KEMET reserves the right to modify minor details of internal and external construction at any time in the interest of product improvement. KEMET does not assume any responsibility for infringement that might result from the use of KEMET Capacitors in potential circuit designs. KEMET is a registered trademark of KEMET Electronics Corporation.*

## Disclaimer

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed.

All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.