




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		A1	ECR-15-010494	20JUN2015	DW	CW
			B	ECR-15-013292	24SEP2015	DL	CW
			B1	ECR-15-017530	02DEC2015	GY	CW
			B2	ECR-16-015492	12NOV2016	QY	CW





4X M3 SCREW RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝, 推荐锁紧力矩0.5Nm


M4 SCREW RECOMMENDED
TIGHTENING TORQUE 1.2Nm
M4 螺丝, 推荐锁紧力矩1.2Nm



- NOTES:
- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250 V
RATED CURRENT: 10 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT
 - CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T20200X10XX000)



- 注释:
- 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 4 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.14-2.5 mm² (26-14 AWG)
接线类型: 冷压接
 - 端子需要单独订购.
(订货号参考图面: T20200X10XX000)








PANEL CUT FOR INSERTS FOR USE
WITHOUT HOODS/ HOUSINGS
不用防护外壳时芯件的安装开孔图

TYPE-1,T2020642101-000,TE LOGO
类型-1,T2020642101-000,TE LOGO

TYPE-2,T2020642101-001,STAINLESS STEEL SCREW,TE LOGO
类型-2,T2020642101-001,不锈钢螺丝,TE LOGO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	30OCT2014	 TE Connectivity		
		CHK	30OCT2014			
		APVD	30OCT2014	NAME		
		PRODUCT SPEC	108-137042	HD-064-M		
		APPLICATION SPEC	114-137042			
		WEIGHT	-	SIZE	CAGE CODE	DRAWING NO
		Customer Drawing		A300779	©-T2020642101000	RESTRICTED TO
		SCALE	1:1	SHEET	1 OF 2	REV
						B2

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		-	SEE SHEET 1	-	-	-




NOTE:
SEE SHEET 1

注释:
见页 1

TYPE-3,T2020642101-002,STAINLESS STEEL SCREW,NO LOGO
类型-3,T2020642101-002,不锈钢螺丝,无LOGO

T2020642101-002	HD-064-M	HD-064 MALE INSERT, STAINLESS STEEL SCREW,NO LOGO HD-064 公插,不锈钢螺丝,无LOGO	TYPE-3 类 型-3
T2020642101-001	HD-064-M	HD-064 MALE INSERT,STAINLESS STEEL SCREW HD-064 公插,不锈钢螺丝	TYPE-2 类 型-2
T2020642101-000	HD-064-M	HD-064 MALE INSERT HD-064 公插	TYPE-1 类 型-1
PART NUMBER 料 号	PART DESCRIPTION 描 述		TYPE 类 型

ALL DIMENSIONS ARE SAME AS TYPE 1,
EXCEPT THOSE DEFINED IN THIS TYPE.
除了在本类型中定义的尺寸外,其它尺寸同类型1

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN David Wang 30OCT2014	 TE Connectivity		
			CHK Chris Wang 30OCT2014			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	APVD Xiang Xu 30OCT2014	NAME HD-064-M		
			PRODUCT SPEC 108-137042			
			APPLICATION SPEC 114-137042			
			WEIGHT -			
			MATERIAL -	FINISH -		
Customer Drawing			SIZE A3	CAGE CODE 00779	DRAWING NO C-T2020642101000	RESTRICTED TO -
			SCALE 1:1	SHEET 2	OF 2	REV B2