



The 1D1304-6 is a low profile 6dB directional coupler in an easy to use surface mount package covering the AMPS and GSM bands. The 1D1304-6 is ideal for inline split/combine¹ amplifiers and for power injection and can be used in most high power designs. Parts have been subjected to rigorous qualification testing and units are 100% tested. They are manufactured using materials with x and y thermal expansion coefficients compatible with common substrates such as FR4, G-10 and polyamide.


ELECTRICAL SPECIFICATIONS**

- **800 - 1200 MHz**
- **Low loss**
- **High Directivity**
- **Surface Mountable**
- **Tape And Reel**
- **Convenient Package**
- **100% Tested**

Frequency	Mean Coupling	Insertion Loss	VSWR	Freq. Sensitivity
<i>MHz</i>	<i>dB</i>	<i>dB Max</i>	<i>Max:1</i>	<i>dB Max</i>
815 - 960	6.0 ± 1.0	0.25	1.17	±0.40
800 - 1200	6.0 ± 1.0	0.25	1.17	±0.60
Directivity	Power Handling	⊙JC	Operating Temp.	
<i>dB Min</i>	<i>Watts</i>	<i>°C / Watt</i>	<i>°C</i>	
20	150	9.8	-55 to +85	
20	150	9.8	-55 to +85	

**Specification based on performance of unit properly installed on microstrip printed circuit boards with 50 Ω nominal impedance. Specifications subject to change without notice.


Outline Drawing




Dimensions are in Inches [Millimeters]
1D1304-6 Rev A Mechanical Outline

Part Is Symmetric About All Axis

Typical Performance: 700 MHz. to 1300 MHz.



Pin Configuration




Directional Coupler Pin Configuration


	Pin 1	Pin 2	Pin 3	Pin 4
Configuration #1	Input	Output	Isolated	Coupled
Configuration #2	Output	Input	Coupled	Isolated
Configuration #3	Isolated	Coupled	Input	Output
Configuration #4	Coupled	Isolated	Output	Input

Mounting Footprint

To ensure proper electrical and thermal performance there must be a ground plane with 100% solder connection underneath the part



Part Is Symmetric About All Axis



Dimensions are in Inches [Millimeters]
1D1304-6 Rev A Mounting Footprint

USA/Canada: (315) 432-8909
Toll Free: (800) 544-2414
Europe: +44 2392-232392

Available on Tape and Reel For Pick and Place Manufacturing.



Anaren
What'll we think of next