




Features

- Recommended for reflow processing
- Rotor design compatible with pick and place and automatic adjustment equipment
- Supplied in 8 mm embossed tape, compatible with automatic assembly equipment
- Rear adjust version available
- 3 mm size meets EIA/EIAJ standard trimmer footprint
- RoHS compliant* - see [processing information](#) on RoHS compliant surface mount trimmers
- For trimmer applications/processing guidelines, [click here](#)

3303 - 3 mm SMD Trimpot® Trimming Potentiometer

Electrical Characteristics

Standard Resistance Range100 ohms to 1 megohm
(see standard resistance table)
Resistance Tolerance $\pm 25\%$ std.
Absolute Minimum Resistance
≤ 1K Ohms 20 ohms max.
> 1K Ohms 2 % max. of TR
Contact Resistance Variation . 5 % max.
Resolution Infinite
Adjustment Angle $260^\circ \pm 20^\circ$

Environmental Characteristics

Resistance to Soldering Heat
... 260°C , 10 seconds, TRS max. 5 %
Power Rating (50 VDC max.)
70 °C 0.15 watt
Temperature Range ... -40°C to $+125^\circ\text{C}$
Temperature Coefficient ... ± 250 ppm/ $^\circ\text{C}$
Humidity 95 %RH
500 hours
TRS max. $\pm 5\%$
Load Life
.....@ 70°C rated power 500 hours
TRS $\pm 5\%$
Rotational Cycling 20 turns
TRS $\pm 15\%$

Physical Characteristics

Torque 20-200 g-cm max.
Mechanical Angle Continuous
Marking Part marking code
Standard Packaging
..... 2000 pcs./7 " reel
Adjustment Tool H-90

Aqueous cleaning not recommended.

How To Order

Model **3303 X - 3 - 103 E**
Style _____
Orientation of Parts In Tape:
• Styles W, C - Terminals Toward Sprocket Holes
• Styles X, D - Terminals Away From Sprocket Holes (preferred)
Standard or Modified
Product Indicator _____
-1 = Single Slot (C, D Pin Styles Only)
-3 = Cross Slot Low Profile (W, X Pin Styles Only)
Resistance Code _____
Embossed Tape Designator _____

Consult factory for other available options.

*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.


Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.


Users should verify actual device performance in their specific applications.

Product Dimensions


3303W, X-3
3mm Open Frame
for Reflow Soldering
3-Terminal
Low Profile





SUGGESTED PWB LAYOUT




DIMENSIONS: $\frac{\text{MM}}{\text{(INCHES)}}$
TOLERANCES: $\pm \frac{0.30}{(.012)}$ EXCEPT WHERE NOTED



3303C,D-1
3-Terminal
Both Sides Adjust



SUGGESTED PWB LAYOUT





DIMENSIONS: $\frac{\text{MM}}{\text{(INCHES)}}$
TOLERANCES: $\pm \frac{0.38}{(.015)}$ EXCEPT WHERE NOTED

3303 - 3 mm SMD Trimpot® Trimming Potentiometer

BOURNS®

Packaging Specifications



Meets EIA 481

Standard Resistance Table

Resistance (Ohms)	Part Marking Code	Resistance Code
100	12	101
200	22	201
500	52	501
1,000	13	102
2,000	23	202
5,000	53	502
10,000	14	103
20,000	24	203
50,000	54	503
100,000	15	104
200,000	25	204
500,000	55	504
1,000,000	16	105

Popular distribution resistance values listed in boldface. Special resistances available.

DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$

TOLERANCES: $\pm \frac{0.25}{(.010)}$ EXCEPT WHERE NOTED

REV. 04/14

"Trimpot" is a registered trademark of Bourns, Inc.
Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.
Users should verify actual device performance in their specific applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[3303X-3-103E](#) [3303X-3-105E](#) [3303W-3-105E](#) [3303X-3-101E](#) [3303W-3-101E](#) [3303C-1-201E](#) [3303C-1-202E](#)
[3303C-1-204E](#) [3303C-1-203E](#) [3303X-3-502E](#) [3303X-3-501E](#) [3303X-3-504E](#) [3303W-3-503E](#) [3303X-3-503E](#) [3303W-](#)
[3-501E](#) [3303W-3-502E](#) [3303C-1-501E](#) [3303C-1-503E](#) [3303C-1-502E](#) [3303C-1-102E](#) [3303W-3-202E](#) [3303X-3-202E](#)
[3303W-3-104E](#) [3303W-3-504E](#) [3303X-3-204E](#) [3303W-3-204E](#) [3303X-3-203E](#) [3303X-3-201E](#) [3303W-3-201E](#)
[3303W-3-203E](#) [3303X-3-302E](#) [3303D-1-103E](#) [3303C-1-101E](#) [3303C-1-105E](#) [3303C-1-104E](#) [3303C-1-103E](#) [3303D-](#)
[1-502E](#) [3303X-3-102E](#) [3303W-3-102E](#) [3303X-3-104E](#) [3303W-3-103E](#) [3303D-1-102E](#) [3303D-1-202E](#) [3303D-1-501E](#)
[3303D-1-104E](#) [3303D-1-203E](#) [3303C-1-504E](#)