




	10	9	8	7	6	5	4	3	2	19070	
	MATERIAL NO. LOOSE PIECE	ENG. NO.	MATERIAL NO. TAPE MOUNTED	ENG. NO.	STUD SIZE	±.003 "S"	"W" MAX.	"C" MIN.	"L" MAX.		
F	190700054	BB-218-10X	-----	-----	10	.198 (5.03)					
	190700057	BB-218-14X	190700058	BB-218-14XT	14	.265 (6.73)	.544 (13.82)	.535 (13.59)	1.261 (32.03)		
	190700059	BB-218-38X	190700061	BB-218-56XT	38	.390 (9.91)					
	190700063	BB-218-56X	190700064	BB-218-38XT	56	.328 (8.33)					
	190700065	BB-223-02X	190700066	BB-223-02XT	2	.094 (2.39)					
E	190700067	BB-223-04X	190700068	BB-223-04XT	4	.119 (3.02)	.260 (6.60)	.209 (5.31)	.785 (19.94)		
	190700069	BB-223-06X	190700070	BB-223-06XT	6	.146 (3.71)					
	190700071	BB-223-08X	190700072	BB-223-08XT	8	.173 (4.39)					
	190700073	BB-225-10X	190700074	BB-225-10XT	10	.198 (5.03)					
	190700075	BB-225-14X	190700076	BB-225-14XT	14	.265 (6.73)					
D	190700078	BB-225-56X	190700079	BB-225-56XT	56	.328 (8.33)	.477 (12.11)	.388 (9.86)	1.062 (26.97)		
	190700081	BB-237-04X	190700082	BB-237-04XT	4	.119 (3.02)					
	190700083	BB-237-06X	190700084	BB-237-06XT	6	.146 (3.71)					
	190700086	BB-237-08X	190700087	BB-237-08XT	8	.173 (4.39)					
	190700090	BB-237-10X	190700092	BB-237-10XT	10	.198 (5.03)					
	190700097	BB-239-06X	190700098	BB-239-06XT	6	.146 (3.71)	.352 (8.94)	.305 (7.75)	.921 (23.39)		
	190700099	BB-239-08X	190700100	BB-239-08XT	8	.173 (4.39)					
	190700102	BB-239-10X	190700104	BB-239-10XT	10	.198 (5.03)					

ENG. NO.
BB-218-***XT ONLY



SALES DRAWING

NOTE(S):

1. MATERIAL: COPPER (.031/0.79 THICK)
PLATING: ELECTROPLATE TIN
2. FERRULE: TIN-PLATED BRASS
3. INSULATION: BLUE MOLDED PVC.
4. MWID=MAXIMUM WIRE INSULATION DIA.
5. ALL DIMENSIONS IN INCHES (MM).
WIRE SIZE: 16-14 AWG
1.0 - 2.5 MM²
6. PARTS ARE ROHS COMPLIANT.

ADDED NOTE 6 EC NO: IPG2013-1831 DRWN: GROJAS01 2013/05/28 CHKD: JMACNEIL 2013/05/28 APPR: JMACNEIL 2013/06/06 REV A	QUALITY SYMBOLS ▽ = 0 ▽ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)	SCALE	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	REVISE ON CAD ONLY
A	DESCRIPTION	4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE IN/MM	DRAWN BY D.MYRICK CHECKED BY JMACNEIL APPROVED BY JMACNEIL	DATE 04/06/15 2013/05/28 2013/06/06	TITLE RING TONGUE TERMINAL INSULKRIMP 16-14 AWG MOLEX INCORPORATED SEE CHART
B	REV					SHEET NO. 1 OF 1