



JB6 Jumper Bars

Terminal Blocks Accessories

Features and Benefits

Facilitate & secure your jumper bar assembly process:

- Screwless mounting,
- Pre-cut poles for various circuits configurations,
- Insulated,
- Positive locking.

Main Technical Data

	IEC	cULus - CSA	Ex e
Rated current	41 A	30 A	
Rated voltage	Standard use 1000 V	600 V	630 V
	Cut extremities 800 V	300 V	Not authorized
	Cut poles 400 V	300 V	Not authorized
Impulse withstand voltage	8000 V		
Protection	IP 20	NEMA 1	

Mounting Instructions

Screwless

Tool

Torque

Material Specifications	Insulating material	Polyamide	
	Flammability	V0	
	NF F 16 101	I2F2	
Ambient temperature min/max	Service IEC 60068-2-1	-55 +110 °C	-67 +230 F
	Storage	-55 +110 °C	-67 +230 F
	Installing	-5 +40 °C	-23 +104 F

Ordering Details


JB6 Jumper Bars

Description	Type	Order Code	Pack ^(ing) pieces	Weight g (1 pce)
6 mm 0.236 in spacing	2 poles	JB6-2	50	1.30
	3 poles	JB6-3	50	2.10
	4 poles	JB6-4	50	2.90
	5 poles	JB6-5	50	3.60
	10 poles	JB6-10	20	7.40
	50 poles	JB6-50	10	38.10

JB6 Accessories

Description	Type	Order Code	Pack ^(ing) pieces	Weight g (1 pce)
1 Circuit Separators	Dark Grey	CS	20	0.20

JB6 Mounting Instructions



- Caution:
use of 50 poles jumper bars or cut jumper bars is not allowed in Explosive atmospheres,

- Jumper bar with cut extremities:
when mounted on feed-through or ground terminal blocks: the circuit separator CS must be installed on the cut side,

- Jumper bar with cut poles:
for alternated jumpering between terminal blocks.