



							Tool 1 Werkzeug 1	Tool 2 Werkzeug 2
TE LOGO TE Logo							AMP	TE
Tool Number Werkzeugnummer								
Tool Cavity 1 Formnest 1							1	2.1
Tool Cavity 2 Formnest 2							2	2.2
Tool Cavity 3 Formnest 3							3	2.3
Tool Cavity 4 Formnest 4							4	2.4

0-1355348-1	A	/	1	1	SOCKET, HOUSING Buchsengehäuse	BLACK schwarz	1.7	4-1355350-1 3-1355350-1 2-1355350-1 1-1355350-1	NOT YET TOOLED
TE BESTELL-NR. ORDER NO.	REV. KOD.	POS.	QTY. STK.		DESCRIPTION BENENNUNG	OBERFLAECHEN SURFACE FARBE/COLOUR	GRAMM GEWICHT WEIGHT	SUITABLE FOR/PASSEND ZU: SHIELD/Abdeckkappe TE CONNECTIVITY	

-							-	-	-	-	-	-	-	-	-	-	-
-							-	-	-	-	-	-	-	-	-	-	-
-							-	-	-	-	-	-	-	-	-	-	-
-							-	-	-	-	-	-	-	-	-	-	-
CUSTOMER PART NO							PART NO	REV	PCS	MATERIAL	SURFACE COLOUR	DESCRIPTION					

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS)										DWN D.Frank	31JAN2000						
DIMENSIONS: MASSEINHEITEN: (mm)										REV B.Fieberling	31JAN2000						
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN										APVD	-						
9 PLC 1 PLC 2 PLC 3 PLC 4 PLC																NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN																MICRO QUADLOK SYSTEM, SOCKET HOUSING,18POS. Micro Quadlok System, Buchsengehäuse,18POS	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN																SIZE	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN																CAGE CODE	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN																DRAWING NO	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN																RESTRICTED TO NUR FÜR	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN																REV	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN																A4	

4805 (3/11)

Pro/ENGINEER DRAWING

4805 (3/11)

Pro/ENGINEER DRAWING