

1674A Coax - 50 Ohm Microwave Cable

For more Information
please call

1-800-Belden1



General Description:

M17/151 type, 29 AWG solid .011" silver-plated copper-covered steel conductor, TFE Teflon® insulation, copper-tin composite shield (100% coverage), unjacketed.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	29	Solid	SPCCS - Silver Plated Copper Covered Steel	.011

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Dia. (in.)
Teflon®	TFE - Tetrafluoroethylene	.034

Outer Shield

Outer Shield Material:

Layer #	Type	Outer Shield Material	Coverage (%)
1	Tape	Copper Foil	100
2	Braid	Tin-Filled Composite	100

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
Unjacketed

Overall Cable

Overall Nominal Diameter: 0.047 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-70°C To +200°C
UL Temperature Rating:	105°C (UL AWM Style 10245)
Non-UL Temperature Rating:	200°C
Bulk Cable Weight:	3 lbs/1000 ft.
Max. Recommended Pulling Tension:	20 lbs.
Min. Bend/Installation:	0.125 in.
Min. Flexing Radius:	0.375 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

AWM Specification:	UL Style 10245 (30 V 105°C)
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	No
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes
RG Type:	M17/151

Flame Test

Other Flame Test:	Horizontal Wire
-------------------	-----------------

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
50

Nom. Inductance:

Inductance (µH/ft)
.07

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
29.5

Nominal Velocity of Propagation:

VP (%)
69.5

Nominal Delay:

Delay (ns/ft)
1.46

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
205.0

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
8

Maximum VSWR:

Freq. (MHz)	Max. VSWR
500	1.16:1
1000	1.17:1
3000	1.20:1
5000	1.24:1
10000	1.33:1
15000	1.41:1
18000	1.50:1
20000	1.50:1

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
500	25.0
1000	36.7
2000	53.8
3000	67.3
5000	89.2
7000	107.5
10000	130.9
15000	163.8
18000	181.1
20000	192.0

Max. Power Rating:

Freq. (MHz)	Rating (W)
500	45
1000	31
2000	22
3000	18
5000	13
7000	11
10000	9.3
15000	7.6

1674A Coax - 50 Ohm Microwave Cable

18000	6.9
20000	6.5

Max. Operating Voltage - UL:

Voltage
30 V RMS (UL AWM Style 10245)

Max. Operating Voltage - Non-UL:

Voltage
1000 V RMS

Notes (Overall)

Notes: Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1674A TIN100	100 FT	0.200 LB	TIN - COLOR		#29 TFE BRD TINNED COAX
1674A TIN1000	1,000 FT	4.000 LB	TIN - COLOR		#29 TFE BRD TINNED COAX
1674A TIN50	50 FT	0.100 LB	TIN - COLOR		#29 TFE BRD TINNED COAX
1674A TIN500	500 FT	2.000 LB	TIN - COLOR		#29 TFE BRD TINNED COAX

Revision Number: 4 Revision Date: 01-15-2014

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.