



NOTES:




- 1. ALL DIMENSIONS IN MM [INCH]
- 2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
- 3. TERM. NOS. FOR REF. ONLY
- 4. RATING: 1A @120VAC or 28VDC.
- 5. ELECTRICAL LIFE: 50,000 make-and-break cycle
at full load.
- 6. INSULATION RESISTANCE: 1,000M ohm min.
- 7. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
- 8. OPERATING TEMP.: -40°C to 85°C.
- 9. ▲ DESIGNATE MAJOR DIMENSIONS.



P/N: 700 C2 BLK CAP (T700200)

1.85 [Ø.073] Typ.

RECOMMENDED PCB LAYOUT



CIRCUIT: SPDT
CONTACT CONFIGURATION

SWITCH FUNCTION	
DN	<DN>
1-3	1-2

()=MOVEMENTARY

E-SWITCH			
TITLE			
700 SP-7 B20 VS3 Q E /C2 BLK CAP			

A	10697	RELEASED FOR PRODUCTION	6/20/00	MM
REV.	ECN No.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				
SCALE		DATE	DR	DWG
2:1		6/20/00	MM	XT0074P
REV				A