

## High Speed Translator Buffer to LVDS

### FEATURES



- Differential LVDS output
- Single AC coupled input (min. 100mV swing).
- Input range from 0 to 1.0GHz.
- 2.5V to 3.3V operation.
- Available in 8-Pin SOP or 3x3mm QFN GREEN/RoHS compliant packaging.

### DESCRIPTION

The PL130-09 is a low cost, high performance, high speed, buffer that reproduces any input frequency from 0 to 1.0GHz. It provides a pair of differential LVDS output. Any input signal with at least 100mV swing can be used as reference signal. This chip is ideal for conversion from sine wave, TTL, CMOS, or PECL to LVDS.


### PIN CONFIGURATION

(TOP VIEW)



Note: ^ denotes internal pull up

### BLOCK DIAGRAM



## High Speed Translator Buffer to LVDS

### PIN DESCRIPTIONS

| Name     | Pin Number |                        | Type | Description                                                                                                              |
|----------|------------|------------------------|------|--------------------------------------------------------------------------------------------------------------------------|
|          | SOP-8L     | QFN-16L                |      |                                                                                                                          |
| GND      | 1,3,7      | 1,2,4,5,<br>9,13,14,15 | P    | Ground.                                                                                                                  |
| VDD      | 5,8        | 7,10,11,12             | P    | Power supply.                                                                                                            |
| REF_IN   | 2          | 3                      | I    | Reference input signal. The frequency of this signal will be reproduced at the output (after translation to LVDS level). |
| LVDS     | 4          | 6                      | O    | LVDS True output.                                                                                                        |
| LVDS_BAR | 6          | 8                      | O    | LVDS Complementary output.                                                                                               |
| OE       | N/A        | 16                     | I    | Output enable ('1' for enable). Internal pull-up (default is '1').                                                       |

### ELECTRICAL SPECIFICATIONS

#### 1. Absolute Maximum Ratings

| PARAMETERS                        | SYMBOL   | MIN. | MAX.         | UNITS |
|-----------------------------------|----------|------|--------------|-------|
| Supply Voltage                    | $V_{DD}$ |      | 4.6          | V     |
| Input Voltage, dc                 | $V_I$    | -0.5 | $V_{DD}+0.5$ | V     |
| Output Voltage, dc                | $V_O$    | -0.5 | $V_{DD}+0.5$ | V     |
| Storage Temperature               | $T_S$    | -65  | 150          | °C    |
| Ambient Operating Temperature*    | $T_A$    | -40  | 85           | °C    |
| Junction Temperature              | $T_J$    |      | 125          | °C    |
| Lead Temperature (soldering, 10s) |          |      | 260          | °C    |
| ESD Protection, Human Body Model  |          |      | 2            | kV    |

Exposure of the device under conditions beyond the limits specified by Maximum Ratings for extended periods may cause permanent damage to the device and affect product reliability. These conditions represent a stress rating only, and functional operations of the device at these or any other conditions above the operational limits noted in this specification is not implied. \*Operating temperature is guaranteed by design. Parts are tested to commercial grade only.

#### 2. General Electrical Specifications

| PARAMETERS              | SYMBOL   | CONDITIONS          | MIN.         | TYP. | MAX. | UNITS |
|-------------------------|----------|---------------------|--------------|------|------|-------|
| Supply Current, No Load | $I_{DD}$ | Fout = 200MHz, LVDS |              | 25   | 30   | mA    |
| Operating Voltage       | $V_{DD}$ |                     | 2.25         |      | 3.63 | V     |
| Output Clock Duty Cycle |          | @ 1.25V (LVDS)      | ±5% of input |      |      | %     |
| Short Circuit Current   |          |                     |              | ±50  |      | mA    |

## High Speed Translator Buffer to LVDS

### 3. AC Specifications

| PARAMETERS         | CONDITIONS   | MIN. | TYP. | MAX. | UNITS |
|--------------------|--------------|------|------|------|-------|
| Input Frequency    |              | 0    |      | 1000 | MHz   |
| Input signal swing | REF_IN input | 100  |      |      | mV    |
| Output Frequency   |              | 0    |      | 1000 | MHz   |


### 4. LVDS Electrical Characteristics

| PARAMETERS                   | SYMBOL          | CONDITIONS                               | MIN.  | TYP.    | MAX.     | UNITS   |
|------------------------------|-----------------|------------------------------------------|-------|---------|----------|---------|
| Output Differential Voltage  | $V_{OD}$        | $R_L = 100\ \Omega$<br>(see figure)      | 247   | 355     | 454      | mV      |
| $V_{DD}$ Magnitude Change    | $\Delta V_{OD}$ |                                          | -50   |         | 50       | mV      |
| Output High Voltage          | $V_{OH}$        |                                          |       | 1.4     | 1.6      | V       |
| Output Low Voltage           | $V_{OL}$        |                                          | 0.9   | 1.1     |          | V       |
| Offset Voltage               | $V_{OS}$        |                                          | 1.125 | 1.2     | 1.375    | V       |
| Offset Magnitude Change      | $\Delta V_{OS}$ |                                          | 0     | 3       | 25       | mV      |
| Power-off Leakage            | $I_{OXD}$       | $V_{out} = V_{DD}$ or GND, $V_{DD} = 0V$ |       | $\pm 1$ | $\pm 10$ | $\mu A$ |
| Output Short Circuit Current | $I_{OSD}$       |                                          |       | -5.7    | -8       | mA      |


### 5. LVDS Switching Characteristics

| PARAMETERS                   | SYMBOL | CONDITIONS                                            | MIN. | TYP. | MAX. | UNITS |
|------------------------------|--------|-------------------------------------------------------|------|------|------|-------|
| Differential Clock Rise Time | $t_r$  | $R_L = 100\ \Omega$<br>$C_L = 10\ pF$<br>(see figure) | 0.2  | 0.7  | 1.0  | ns    |
| Differential Clock Fall Time | $t_f$  |                                                       | 0.2  | 0.7  | 1.0  | ns    |


LVDS Levels Test Circuit



LVDS Switching Test Circuit



LVDS Transition Time Waveform




## High Speed Translator Buffer to LVDS

### PACKAGE DRAWINGS (GREEN PACKAGE COMPLIANT)


8 PIN SOP ( dimensions in mm )

| SOP-8L |          |      |
|--------|----------|------|
| Symbol | Min.     | Max. |
| A      | 1.47     | 1.73 |
| A1     | 0.10     | 0.25 |
| B      | 0.33     | 0.51 |
| C      | 0.19     | 0.25 |
| D      | 4.80     | 4.95 |
| E      | 3.80     | 4.00 |
| H      | 5.80     | 6.20 |
| L      | 0.38     | 1.27 |
| e      | 1.27 BSC |      |



VARIATIONS:

| QFN-16L |          |      |      |
|---------|----------|------|------|
| SYMBOL  | MIN      | NOM  | MAX  |
| e       | 0.50 BSC |      |      |
| b       | 0.18     | 0.23 | 0.30 |
| L       | 0.30     | 0.40 | 0.50 |
| ND      | 4        |      |      |
| NE      | 4        |      |      |



**High Speed Translator Buffer to LVDS****ORDERING INFORMATION (GREEN PACKAGE COMPLIANT)**

***For part ordering, please contact our Sales Department:***


2180 Fortune Drive, San Jose, CA 95131, USA

Tel: (408) 944-0800 Fax: (408) 474-1000

**PART NUMBER**

The order number for this device is a combination of the following:

Device number, Package type and Operating temperature range



| Part/Order Number | Marking    | Package Option                   |
|-------------------|------------|----------------------------------|
| PL130-09QC-R      | P130<br>09 | 16-pin QFN-16L - (Tape and Reel) |
| PL130-09SC        | P130-09    | 8-pin SOP-8L - (Tube)            |
| PL130-09SC-R      | P130-09    | 8-pin SOP-8L - (Tape and Reel)   |

*Micrel Inc., reserves the right to make changes in its products or specifications, or both at any time without notice. The information furnished by Micrel is believed to be accurate and reliable. However, Micrel makes no guarantee or warranty concerning the accuracy of said information and shall not be responsible for any loss or damage of whatever nature resulting from the use of, or reliance upon this product.*

**LIFE SUPPORT POLICY:** *Micrel's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of Micrel Inc.*